

10 9 8 7 6 5 4 3 2 1

F

E

D

C

B

A

F

E

D

C

B

A



トレードマーク
TRADE MARK

型番
ENG. NO.

回路番号
CIRCUIT NO.

注記
NOTE

1. 回路番号、製品番号表示は1極の場合、
表示なしとする
IN CASE OF CIRCUIT SIZE 1,
NO SHOWN CIRCUIT NO. & ENG.NO.



適合ターミナル: 5394T
APPLICABLE TERMINAL
5394T

基板取付穴推奨寸法 (基板厚: $t = 1.6\text{mm}$)
RECOMMENDED PC BOARD HOLE DIMENSION
(THICKNESS: $t = 1.6\text{mm}$)

MATERIAL

ナイロン66, UL94V-0
NYLON66, UL94V-0

7.5	10.8	5395-04	4
2.5	5.8	5395-02	2
B	A	MATERIAL NO.	極数 CKT.NO.

MODEL NO. 5395-N

THIRD ANGLE
PROJECTION

GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 5:1	DESIGN UNITS METRIC	TITLE 2.5 BOARD IN CONN HSG	
10 UNDER	± 0.2	DRAWN BY HIJIMA	DATE 1996/06/13	MOLEX INCORPORATED		SD-5395-001	
10 OVER 30 UNDER	± 0.25	CHECKED BY MFUKUSHI	DATE 1996/06/13				
30 OVER	± 0.3	APPROVED BY MENOMOTO	DATE 1996/06/13				
ANGULAR $\pm 3^\circ$		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		1 OF 1	