




High voltage power switch. Designed for horizontal deflection output stage of CTV receivers and high voltage, fast switching and industrial application

Features:

- Collector-emitter sustaining voltage - 100 mA
- $V_{CEO(sus)} = 400\text{ V}$ (minimum)
- Optimum drive condition curves

TO-3




Pin 1. Base
2. Emitter
Collector (Case)

Dimensions	Minimum	Maximum
A	37.75	39.96
B	19.28	22.23
C	7.96	9.28
D	11.18	12.19
E	25.20	26.67
F	0.92	1.09
G	1.38	1.62
H	29.9	30.4
I	16.64	17.3
J	3.88	4.36
K	10.67	11.18

Dimensions : Millimetres

NPN BUY69A

10 A
Silicon Power
Transistors
200 - 400 V
100 W



TO-3


Maximum Ratings

Characteristic	Symbol	BUY69A	Unit
Collector-Emitter Voltage ($V_{BE} = 0$)	V_{CBS}	1,000	V
Collector-Emitter Voltage	V_{CEO}	400	
Emitter-Base Voltage	V_{EBO}	8	
Collector Current-Continuous-Peak	I_C I_{CM}	10 15	A
Base Current-Peak	I_B	3	
Total Power Dissipation at $T_C = 25^\circ\text{C}$ Derate above 25°C	P_D	100 0.57	W W / $^\circ\text{C}$
Operating and Storage Junction Temperature Range	T_J, T_{STG}	65 to +200	$^\circ\text{C}$

Thermal Characteristics

Characteristic	Symbol	Maximum	Unit
Thermal Resistance Junction to Case	$R_{\theta jc}$	1.75	$^\circ\text{C} / \text{W}$

Power Derating



Electrical Characteristics ($T_C = 25^\circ\text{C}$ unless otherwise noted)

Characteristic	Symbol	Minimum	Maximum	Unit
Off Characteristics				
Collector-Emitter Sustaining Voltage (1) (I _C = 100 mA, I _B = 0)	BUY69A V _{CEO (sus)}	400	-	V
Collector-Base Voltage (I _C = 1 mA, I _E = 0)	BUY69A V _{CBO}	1,000	-	
Collector Cut off Current (V _{CE} = 1,000 V, V _{BE} = 0)	BUY69A I _{CES}	-	1	mA
Emitter-Base Cut off Current (V _{EB} = 8 V, I _C = 0)	I _{EBO}	-		
On Characteristics (1)				
DC Current Gain (V _{CE} = 10 V, I _C = 2.5 A)	h _{FE}	15	-	-
Collector-Emitter Saturation Voltage (I _C = 8 A, I _B = 2.5 A)	V _{CE (sat)}	-	3.3	V
Base-Emitter Saturation (I _C = 8 A, I _B = 2.5 A)	V _{BE (sat)}	-	2.2	
Dynamic Characteristics				
Current Gain-Bandwidth Product (2) (I _C = 500 mA, V _{CE} = 10 V, f = 1 MHz)	f _T	10	-	MHz

Switching Characteristics					
Rise Time	$V_{CC} = 250\text{ V}, I_C = 5\text{ A}$	t_r	-	0.3	μs
Storage Time	$I_{B1} = -I_{B2} = 1\text{ A}$	t_s	-	1.8	
Fall Time	-	t_f	-	1	

- (1) Pulse Test : Pulse Width = 300 μs , Duty Cycle $\leq 2\%$
(2) $f_T = |h_{fe}| \cdot f_{\text{test}}$

Part Number Table

Description	Part Number
Transistor, NPN, TO-3	BUY69A

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.