



FEATURES:

- Wide 2:1 input range
- Over Voltage Protection
- High efficiency up to 87%
- Low Ripple and Noise
- Operating temperature -40°C to + 85°C
- Input / Output isolation 1500 VDC
- Continuous short circuit protection



Models

Single output

Model	Input Voltage (V)	Output Voltage (V)	Output Current max(mA)	Isolation (VDC)	Efficiency (%)
AM6T-0505S-NZ	4.5-9	5	1200	1500	78
AM6T-0512S-NZ	4.5-9	12	500	1500	84
AM6T-0515S-NZ	4.5-9	15	400	1500	84
AM6T-0524S-NZ	4.5-9	24	250	1500	84
AM6T-1203S-NZ	9-18	3.3	1500	1500	75
AM6T-1205S-NZ	9-18	5	1200	1500	80
AM6T-1212S-NZ	9-18	12	500	1500	84
AM6T-1215S-NZ	9-18	15	400	1500	85
AM6T-1224S-NZ	9-18	24	250	1500	85
AM6T-2403S-NZ	18-36	3.3	1500	1500	78
AM6T-2405S-NZ	18-36	5	1200	1500	82
AM6T-2412S-NZ	18-36	12	500	1500	85
AM6T-2415S-NZ	18-36	15	400	1500	86
AM6T-2424S-NZ	18-36	24	250	1500	86
AM6T-4803S-NZ	36-75	3.3	1500	1500	79
AM6T-4805S-NZ	36-75	5	1200	1500	83
AM6T-4812S-NZ	36-75	12	500	1500	87
AM6T-4815S-NZ	36-75	15	400	1500	88
AM6T-4824S-NZ	36-75	24	250	1500	87

Models

Dual output

Model	Input Voltage (V)	Output Voltage (V)	Output Current max (mA)	Isolation (VDC)	Efficiency (%)
AM6T-0505D-NZ	4.5-9	±5	±600	1500	78
AM6T-0512D-NZ	4.5-9	±12	±250	1500	84
AM6T-0515D-NZ	4.5-9	±15	±200	1500	84
AM6T-0524D-NZ	4.5-9	±24	±125	1500	84
AM6T-1205D-NZ	9-18	±5	±600	1500	80
AM6T-1212D-NZ	9-18	±12	±250	1500	84
AM6T-1215D-NZ	9-18	±15	±200	1500	85
AM6T-1224D-NZ	9-18	±24	±125	1500	84
AM6T-2405D-NZ	18-36	±5	±600	1500	83
AM6T-2412D-NZ	18-36	±12	±250	1500	86
AM6T-2415D-NZ	18-36	±15	±200	1500	87
AM6T-2424D-NZ	18-36	±24	±125	1500	85
AM6T-4805D-NZ	36-75	±5	±600	1500	83
AM6T-4812D-NZ	36-75	±12	±250	1500	87
AM6T-4815D-NZ	36-75	±15	±200	1500	85
AM6T-4824D-NZ	36-75	±24	±125	1500	85

NOTE: All specifications in this datasheet are measured at an ambient temperature of 25°C, humidity<75%, nominal input voltage and at rated output load unless otherwise specified.

Input Specifications

Parameters	Nominal	Typical	Maximum	Units
Absolute Max Input Voltage (1 Sec. Max.)	5 Vin 12 Vin 24 Vin 48 Vin		16 25 50 100	VDC
Voltage range	5 12 24 48	4.5-9 9-18 18-36 36-75		VDC
Filter	π (Pi) Network			
Reflected ripple current	5 Vin Others	50 20		mA

Isolation Specifications

Parameters	Conditions	Typical	Maximum	Units
Tested I/O voltage	60 sec, 1mA	1500		VDC
Tested I/case, O/case voltage	60sec, 1mA	1500		VDC
Resistance	500 Vdc	> 1000		MOhm
Capacitance	100kV / 0.1V	1000		pF

Output Specifications

Parameters	Conditions	Typical	Maximum	Units
Voltage accuracy	5 Vin Vo1, 5% to 100% Load 5 Vin Vo2, 5% to 100% Load Other models, 5% to 100% Load	± 1 ± 1 ± 1	± 2 ± 3 ± 3	%
Short Circuit protection	Continuous			
Short circuit restart	Auto-recovery			
Line voltage regulation	Vo1, Full Load, LL-HL Vo2, Full Load, LL-HL	± 0.2 ± 0.5	± 0.5 ± 1	%
Load voltage regulation	5 Vin Vo1, 5% to 100% Load 5 Vin Vo2, 5% to 100% Load Other models Vo1, 5% to 100% Load Other models Vo1, 5% to 100% Load	± 0.5 ± 0.5	± 1 ± 1.5 ± 1 ± 1.5	%
Cross Regulation (dual)	Vo1 50% load, Vo2 10-100% load		± 5	%
Temperature coefficient		± 0.03		%/°C
Transient Recovery Time	25% load step	300	500	μ sec
Transient Response Deviation	3.3V, 5V, $\pm 5V_{out}$, 25% load step Others, 25% load step	± 5 ± 3	± 8 ± 5	%
Ripple & Noise	5% to 100% Load		100	mVp-p
Over Voltage Protection			110 to 160	%Vout
Over current protection		140	190	%Iout

General Specifications

Parameters	Conditions	Typical	Maximum	Units
Switching frequency*	100% load	300		KHz
Operating temperature	Derating above +71	-40 to +85		°C
Storage temperature		-55 to +125		°C
Max Case temperature			100	°C
Cooling	Free air convection			
Humidity			95	%
Case material	Black Anodized Aluminum			
Weight		12		g
Dimensions (L x W x H)		1.26 x 0.79 x 0.42inches (32.00 x 20.00 x 10.80mm)		
MTBF	>1 000 000 hrs (MIL-HDBK -217F, Ground Benign, t=+25°C)			

*Below 50% load the switching frequency decreases with the decrease of the load.

Environment Specifications

Test	Parameters	Conditions
Vibration	Test mode	10-150Hz
	Acceleration	5g, 30min, every axis tested


Safety Specifications

Parameters		
Standards	Designed to meet IEC/UL 60950-1	
	EMC - Radiated & Conducted emission	CISPR32 / EN55032, Class A (without external components)(Except 5Vin model), Class B (with recommended EMC circuit part B)(5Vin model with recommended circuit)
	Electrostatic Discharge Immunity	IEC61000-4-2, Contact $\pm 4\text{KV}$, Criteria B
	RF, Electromagnetic Field Immunity	IEC61000-4-3, 10V/m, Criteria A
	Electrical Fast Transient/Burst Immunity	IEC61000-4-4, $\pm 2\text{KV}$, Criteria B, (with recommended EMC circuit part A)
	Surge Immunity	IEC61000-4-5, L-L $\pm 2\text{KV}$, Criteria B, (with recommended EMC circuit part A)
	RF, Conducted Disturbance Immunity	IEC61000-4-6, 3Vrms, Criteria A


Pin Out Specifications

Pin	1500VDC	
	Single	Dual
2	-V Input	-V Input
3	-V Input	-V Input
9	No pin	Common
11	N.C.	-V Output
14	+V Output	+V Output
16	-V Output	Common
22	+V Input	+V Input
23	+V Input	+V Input

Dimensions




Recommended Circuit For Ripple & Noise reduction



External Capacitor Tables

Vin (VDC)	Cin (uF)	Cout (uF)
5/12/24	100	10
48	10 ~ 47	10


Recommended EMC Circuit



Model	MOV	C1	C2	C3	CY1/CY2
12 Vin	S14K20	1µF / 50V	100µF / 35V	1000µF / 35V	1nF/2KV
24 Vin	S20K30	1µF / 50V	100µF / 50V	1000µF / 50V	
48 Vin	S14K60	1µF / 100V	100µF / 100V	680µF / 100V	


Note: Fuse is user selectable
Part A for EMS, part B for EMI.

Recommended EMC Circuit for 5V input model



Part A for EMS, part B for EMI.

Derating



NOTE: 1. Datasheets are updated as needed and as such, specifications are subject to change without notice. Once printed or downloaded, datasheets are no longer controlled by Aimtec; refer to www.aimtec.com for the most current product specifications. 2. Product labels shown, including safety agency certifications on labels, may vary based on the date manufactured. 3. Mechanical drawings and specifications are for reference only. 4. All specifications are measured at an ambient temperature of 25°C, humidity < 75%, nominal input voltage and at rated output load unless otherwise specified. 5. Aimtec may not have conducted destructive testing or chemical analysis on all internal components and chemicals at the time of publishing this document. CAS numbers and other limited information are considered proprietary and may not be available for release. 6. This product is not designed for use in critical life support systems, equipment used in hazardous environments, nuclear control systems or other such applications which necessitate specific safety and regulatory standards other than the ones listed in this datasheet. 7. Warranty is in accordance with Aimtec's standard Terms of Sale available at www.aimtec.com.