





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AF	50		F	REVISED PER ECR-12-002864	24MAY12	KH PD


SUGGESTED MATING TAB




- 1
- MATL: 1/2H BRASS OR NICKEL PL STEEL.
- 2
- NO BURRS PERMISSIBLE AT HOLE.
- 3
- MUST BE FLAT WITHIN .003 OVER THIS LENGTH.
- 4
- HOLE MUST BE SYMMETRICAL ABOUT TAB $\varnothing$ WITHIN 0.076 [.003]
- *
- TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.




SECTION D-D



SECTION A-A
SCALE 8:1



SECTION B-B
SCALE 8:1



SECTION C-C
SCALE 8:1

1 CONTINUOUS STRIP ON REELS

F	.180	.188	F	.090	.077	14
					.066	16
					.059	18
TYPE	WIDTH	STRIP LENGTH ±.015	TYPE	WIDTH	±.002 HEIGHT	WIRE
INSUL BARREL CRIMP	WIRE BARREL CRIMP					

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .010 4 PLC ± - ANGLES ± -
MATERIAL TEMP 3 PHOS BRONZE	FINISH TIN

.161—.196		18—14		63524—1	
INSUL RANGE		WIRE SIZE		PART NUMBER	
DWN JR RUTH 1/3/90	TE Connectivity				
CHK MS FEHER 1/3/90					
APVD J GILLESPIE 1/3/90					
PRODUCT SPEC —					
APPLICATION SPEC —		RECEPTACLE, FASTON, TM LOCK—ON, 4.75 [.187] SERIES			
WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C-63524		RESTRICTED TO —
CUSTOMER DRAWING			SCALE 6:1	SHEET 1 of 1	REV F