

International
IR Rectifier

47CTQ020SPbF
47CTQ020-1PbF

SCHOTTKY RECTIFIER

40 Amp

$$I_{F(AV)} = 40\text{Amp}$$

$$V_R = 20\text{V}$$

Major Ratings and Characteristics

Characteristics	Values	Units
$I_{F(AV)}$ Rectangular waveform	40	A
V_{RRM}	20	V
I_{FSM} @tp = 5 μ s sine	1000	A
V_F @20 Apk, $T_J = 125^\circ\text{C}$	0.34	V
T_J	-55 to 150	$^\circ\text{C}$


Description/ Features

This center tap Schottky rectifier has been optimized for ultra low forward voltage drop specifically for 3.3V output power supplies. The proprietary barrier technology allows for reliable operation up to 150 $^\circ\text{C}$ junction temperature. Typical applications are in parallel switching power supplies, converters, reverse battery protection, and redundant power subsystems.

- 150 $^\circ\text{C}$ T_J operation
- Center tap configuration
- Optimized for 3.3V application
- Ultra low forward voltage drop
- High frequency operation
- Guard ring for enhanced ruggedness and long term reliability
- High purity, high temperature epoxy encapsulation for enhanced mechanical strength and moisture resistance
- Lead-Free ("PbF" suffix)


Case Styles

47CTQ020SPbF



D²PAK

47CTQ020-1PbF



TO-262

47CTQ020SPbF, 47CTQ020-1PbF

Bulletin PD-21038 rev. A 07/06

International
IR Rectifier

Voltage Ratings

Part number	47CTQ020SPbF, 47CTQ020-1PbF	
V _R Max. DC Reverse Voltage (V) @ 125° C		20
V _R Max. DC Reverse Voltage (V) @ 150° C		10

Absolute Maximum Ratings

Parameters	47CTQ	Units	Conditions
I _{F(AV)} Max. Average Forward (Per Device) Current (Per Leg)	40 20	A	50% duty cycle @ T _C = 135°C, rectangular wave form
I _{FSM} Max. Peak One Cycle Non-Repetitive Surge Current (Per Leg)	1000 250	A	5μs Sine or 3μs Rect. pulse 10ms Sine or 6ms Rect. pulse Following any rated load condition and with rated V _{RM} applied
E _{AS} Non-Repetitive Avalanche Energy (Per Leg)	18	mJ	T _J = 25 °C, I _{AS} = 3 Amps, L = 3 mH
I _{AR} Repetitive Avalanche Current (Per Leg)	3	A	Current decaying linearly to zero in 1 μsec Frequency limited by T _J max. V _A = 1.5 x V _R typical

Electrical Specifications

Parameters	47CTQ	Units	Conditions
V _{FM} Max. Forward Voltage Drop (Per Leg) (1)	0.45	V	@ 20A T _J = 25 °C
	0.51	V	@ 40A
	0.34	V	@ 20A T _J = 125 °C
	0.44	V	@ 40A
	0.31	V	@ 20A T _J = 150 °C
	0.42	V	@ 40A
I _{RM} Max. Reverse Leakage Current (Per Leg) (1)	3	mA	T _J = 25 °C
	310	mA	T _J = 125 °C
	60	mA	T _J = 125 °C V _R = rated V _R
	45	mA	T _J = 125 °C V _R = 5V
	306	mA	T _J = 150 °C V _R = 3.3V
V _{F(TO)} Threshold Voltage	0.188	V	T _J = T _J max. V _R = 10V
r _t Forward Slope Resistance	5.9	mΩ	
C _T Max. Junction Capacitance (Per Leg)	3000	pF	V _R = 5V _{DC} (test signal range 100Khz to 1Mhz) 25°C
L _S Typical Series Inductance (Per Leg)	5.5	nH	Measured lead to lead 5mm from package body
dv/dt Max. Voltage Rate of Change	10000	V/μs	(Rated V _R)

(1) Pulse Width < 300μs, Duty Cycle < 2%

Thermal-Mechanical Specifications

Parameters			47CTQ	Units	Conditions	
T _J	Max. Junction Temperature Range		-55 to 150	°C		
T _{stg}	Max. Storage Temperature Range		-55 to 150	°C		
R _{thJC}	Max. Thermal Resistance Junction to Case (Per Leg)		1.5	°C/W	DC operation	
R _{thJC}	Max. Thermal Resistance Junction to Case (Per Package)		0.75	°C/W	DC operation	
R _{thCS}	Typical Thermal Resistance, Case to Heatsink		0.50	°C/W	Mounting surface , smooth and greased (only for TO-220)	
wt	Approximate Weight		2 (0.07)	g (oz.)		
T	Mounting Torque	Min.	6 (5)	Kg-cm (lbf-in)		
		Max.	12 (10)			
Marking Device			47CTQ020S	Case style D ² Pak		
			47CTQ020-1	Case style TO-262		




Fig. 1 - Max. Forward Voltage Drop Characteristics (Per Leg)




Fig. 2 - Typical Values Of Reverse Current Vs. Reverse Voltage (Per Leg)




Fig. 3 - Typical Junction Capacitance Vs. Reverse Voltage (Per Leg)




Fig. 4 - Max. Thermal Impedance Z_{thJC} Characteristics (Per Leg)




Fig. 5 - Max. Allowable Case Temperature Vs. Average Forward Current (Per Leg)




Fig. 6 - Forward Power Loss Characteristics (Per Leg)




Fig. 7 - Max. Non-Repetitive Surge Current (Per Leg)






Fig. 8 - Unclamped Inductive Test Circuit

(2) Formula used: $T_c = T_j - (P_d + P_{d_{REV}}) \times R_{thJC}$

P_d = Forward Power Loss = $I_{F(AV)} \times V_{FM} @ (I_{F(AV)} / D)$ (see Fig. 6);

$P_{d_{REV}}$ = Inverse Power Loss = $V_{R1} \times I_{R1} (1 - D)$; $I_{R1} @ V_{R1} = 10$ V

Outlines Table



Part Marking Information

D²PAK

EXAMPLE: THIS IS A 47CTQ020S
LOT CODE 8024
ASSEMBLED ON WW 02, 2000

Note: "P" in assembly line position indicates "Lead-Free"

TO-262

EXAMPLE: THIS IS A 47CTQ020-1
LOT CODE 1789
ASSEMBLED ON WW 19, 2002

Note: "P" in assembly line position indicates "Lead-Free"

Tape & Reel Information

SECTION Y-Y

NOTES:

Ao	10.50 +/– 0.1
Bo	15.80 +/– 0.1
B2	10.25 +/– 0.1
Ko	4.90 +/– 0.1
F	11.50 +/– 0.1
P1	16.00 +/– 0.1
W	24.00 +/– 0.3

Dimensions in millimeters and (inches)

Ordering Information Table

Device Code							
	47	C	T	Q	020	S	TRL PbF
	1	2	3	4	5	6	7 8
1	-	Current Rating (40A)					
2	-	Circuit Configuration					
		C = Common Cathode					
3	-	T = TO-220					
4	-	Schottky "Q" Series					
5	-	Voltage Rating (020 = 20V)					
6	-	- S = D²Pak -1= TO-262					
7	-	- none = Tube (50 pieces) - TRL = Tape & Reel (Left Oriented - for D²Pak only) - TRR = Tape & Reel (Right Oriented - for D²Pak only)					
8	-	- none = Standard Production - PbF = Lead-Free					

Data and specifications subject to change without notice.
This product has been designed and qualified for Industrial Level and Lead-Free.
Qualification Standards can be found on IR's Web site.

International
IR Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105
TAC Fax: (310) 252-7309
Visit us at www.irf.com for sales contact information. 07/06