



REV. Status	TCA NO.	MODEL NO.	RATED CURRENT (AC)	INDUCTANCE (uH) MIN	DCR (mohm MAX)	OD	HT
REVISION - 04/08/98 TS	P-A4-12018-01	SKP4-40	5	40	30	26.0(1.02)	12.0(0.47)
REVISION A CHG'D CURRENT WAS DC 04/27/98 TS	P-A4-12018-02	SKP4-50	5	62	35	26.0(1.02)	12.0(0.47)
	P-A4-12018-03	SKP5-40	5	100	40	28.0(1.10)	15.0(0.59)
	P-A4-12018-04	SKP5-50	5	150	50	28.0(1.10)	15.0(0.59)

Schematic Diagram;





Country of origin



SKP3-30~SKP3-50

Mechanical Specifications;



SOLDER COATED 2 PLACES

Ø 1.0(0.039) 2 PLACES

TOLERANCES (mm)

≤ 4 ± 0.2
4 ≤ 20 ± 0.3
20 ≤ 50 ± 0.4

PREPARED BY:

D. Kelley

NOTE: Inductance is measured at 1 KHz, 1mA AC current

ENGINEER:

T. Shiozawa

DWG CONTROL NO. REV
P-A4-12019
ACAD\MISCX\A4120191.DWG A

POWER INDUCTOR FOR
SWITCH MODE POWER SUPPLIES

QUALITY CONTROL:

D. Kelley

CONTENTS OF THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT
PRIOR NOTICE

TAMURA CORPORATION OF AMERICA
43352 BUSINESS PARK DRIVE, TEMECULA, CA. 92590-6624
(909) 699-1270 FAX 9096769482

SKP4-40~5-50

MODEL SPECIFICATION

DIM: mm(in) SCL: NONE SH: 1 OF 1

APPROVED:

D. Suzuki

PROPRIETARY NOTICE: THIS DRAWING PRINT OR DOCUMENT AND SUBJECT MATTER DISCLOSED HEREIN ARE PROPRIETARY ITEMS TO WHICH TAMURA RETAINS THE EXCLUSIVE RIGHT OF DISSEMINATION, REPRODUCTION, MANUFACTURE AND SALE. THIS DRAWING, PRINT OR DOCUMENT IS SUBMITTED IN CONFIDENCE FOR CONSIDERATION BY THE RECIPIENT ALONE UNLESS PERMISSION FOR FURTHER DISCLOSURE IS EXPRESSLY GRANTED IN WRITING.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tamura:](#)

[SKP5-50](#)