


NOTES:

1. MATERIALS AND FINISHES:
BODY AND BAYONET SLEEVE - BRASS, NICKEL PLATING
OUTER CONTACT - BeCu, NICKEL PLATING
CONTACT - BRASS, GOLD PLATING
INSULATOR - PTFE
2. ELECTRICAL:
A. IMPEDANCE: 50 OHM
B. FREQUENCY RANGE: DC - 6 GHz
C. VSWR: 1.05 MAX @ 6 GHz
3. MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -65° C TO +165° C
4. PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED:
"AMPHENOLRF, APH-HDBNCP-SMAP DATE CODE"
U.S. PATENT NO. 7,553,177"

THIRD ANGLE PROJ.


REVISIONS

REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	08-Apr-13	49282	KR



SCALE 3.000

STUD LOCATING
AND INSTALLATION/
REMOVAL TOOL GROOVES



PROTECTED UNDER U.S. PATENT # 7,553,177

CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE:
<0.5mm ± 0.05mm 0.5 - 6mm ± 0.1mm 6 - 30mm ± 0.2mm 30 - 120mm ± 0.3mm ANGLES ± 1°

NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implicatioin or otherwise in any manner licensing, granting rights to permitting such holder or any other sperson to manufacture, use or sell any product, process or design, patented or otherwsie, that may in any way be related to or disclosed by said drawings, specifications, or other data.

MATERIAL	SEE NOTES
REFERENCE	EAR # 4800
CONFIGURATION LEVEL:	☐ ☐ ☐
FINISH	

DRAWN	S.L.I	DATE	08-Apr-13
ENGINEER	KARTHIK R	DATE	13-Jun-11
APPROVED	H.HE	DATE	10-Apr-13
CAD FILE			

TITLE	
50 OHM HD BNC PLUG TO SMA PLUG ADAPTER	
SCALE: 10.8:1.0	SHEET 2 OF 2
DWG SIZE	REV
B	A

Amphenol RF
www.amphenolrf.com
DRAWING NO.APH-HDBNCP-SMAP
ITEM NO.APH-HDBNCP-SMAP
PART NO.APH-HDBNCP-SMAP