



**TL1431**

## PROGRAMMABLE VOLTAGE REFERENCE

- ADJUSTABLE OUTPUT VOLTAGE :  
2.5 to 36V
- SINK CURRENT CAPABILITY : 1 to 100mA
- TYPICAL OUTPUT IMPEDANCE : 0.2Ω
- 0.4% AND 0.25% PRECISION

### DESCRIPTION

The TL1431 is a programmable shunt voltage reference with guaranteed temperature stability over the entire temperature range of operation.

The output voltage may be set to any value between 2.5V and 36V with two external resistors.


The TL1431 operates with a wide current range from 1 to 100mA with a typical dynamic impedance of 0.2Ω.

### ORDER CODE


| Part Number | Temperature Range | Package |   |
|-------------|-------------------|---------|---|
|             |                   | Z       | D |
| TL1431C/AC  | -20°C, +70°C      | •       | • |
| TL1431I/AI  | -40°C, +105°C     | •       | • |

Z = TO92 Plastic package - also available in Bulk (Z), Tape & Reel (ZT) and Ammo Pack (AP)

D = Small Outline Package (SO) - also available in Tape & Reel (DT)



### PIN CONNECTIONS (top view)



## TL1431

### ABSOLUTE MAXIMUM RATINGS

| Symbol    | Parameter                                              | Value        | Unit |
|-----------|--------------------------------------------------------|--------------|------|
| $V_{KA}$  | Cathode to Anode Voltage                               | 37           | V    |
| $I_K$     | Continuous Cathode Current Range                       | -100 to +150 | mA   |
| $I_{REF}$ | Reference Input Current Range                          | -0.05 to +10 | mA   |
| $p_d$     | Power Dissipation <sup>1)</sup><br>TO92<br>SO8 batwing | 625<br>960   | mW   |
| $T_{Stg}$ | Storage Temperature Range                              | -65 to +150  | °C   |
| $T_J$     | Junction temperature                                   | +150         | °C   |

1.  $p_d$  is calculated with  $T_{amb} = +25^{\circ}\text{C}$ ,  $T_J = +150^{\circ}\text{C}$  and  $R_{thja} = 200^{\circ}\text{C/W}$  for TO92 package  
 $= 130^{\circ}\text{C/W}$  for SO8 batwing package

### OPERATING CONDITIONS


| Symbol    | Parameter                                                        | Value                     | Unit |
|-----------|------------------------------------------------------------------|---------------------------|------|
| $V_{KA}$  | Cathode to Anode Voltage                                         | $V_{REF}$ to 36           | V    |
| $I_K$     | Cathode Current                                                  | 1 to 100                  | mA   |
| $T_{amb}$ | Operating Free-air Temperature Range<br>TL1431C/AC<br>TL1431I/AI | -20 to +70<br>-40 to +105 | °C   |

## ELECTRICAL CHARACTERISTICS


$T_{amb} = 25^{\circ}\text{C}$  (unless otherwise specified)

| Symbol                                 | Parameter                                                                                                                                                                       | TL1431C |          |          | TL1431AC |          |          | Unit                    |
|----------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------|----------|----------|----------|----------|----------|-------------------------|
|                                        |                                                                                                                                                                                 | Min.    | Typ.     | Max.     | Min.     | Typ.     | Max.     |                         |
| $V_{REF}$                              | Reference Input Voltage - (figure 1)<br>$V_{KA} = V_{REF}$ , $I_K = 10\text{ mA}$                                                                                               | 2.490   | 2.500    | 2.510    | 2.493    | 2.500    | 2.507    | V                       |
| $\Delta V_{REF}$                       | Reference Input Voltage Deviation Over Temperature Range - (figure 1, note 1)<br>$V_{KA} = V_{REF}$ , $I_K = 10\text{ mA}$ , $T_{MIN} \leq T_{AMB} \leq T_{MAX}$                |         | 3        | 20       |          | 3        | 20       | mV                      |
| $\frac{\Delta V_{REF}}{\Delta T}$      | Temperature Coefficient of Reference Input Voltage (note 2)<br>$V_{KA} = V_{REF}$ , $I_K = 10\text{ mA}$ , $T_{MIN} \leq T_{AMB} \leq T_{MAX}$                                  |         | $\pm 13$ | $\pm 90$ |          | $\pm 13$ | $\pm 90$ | ppm/ $^{\circ}\text{C}$ |
| $\frac{\Delta V_{REF}}{\Delta V_{KA}}$ | Ratio of Change in Reference Input Voltage to Change in Cathode to Anode Voltage - (figure 2)<br>$I_K = 10\text{ mA}$ , $\Delta V_{KA} = 36\text{V to } 3\text{V}$              | -2      | -1.1     |          | -2       | -1.1     |          | mV/V                    |
| $I_{REF}$                              | Reference Input Current - (figure 2)<br>$I_K = 10\text{ mA}$ , $R1 = 10\text{ k}\Omega$ , $R2 = \infty$<br>$T_{MIN} \leq T_{AMB} \leq T_{MAX}$                                  |         | 1.5      | 2.5<br>3 |          | 1.5      | 2.5<br>3 | $\mu\text{A}$           |
| $\Delta I_{REF}$                       | Reference Input Current Deviation Over Temperature Range - (figure 2)<br>$I_K = 10\text{ mA}$ , $R1 = 10\text{ k}\Omega$ , $R2 = \infty$<br>$T_{MIN} \leq T_{AMB} \leq T_{MAX}$ |         | 0.2      | 1.2      |          | 0.2      | 1.2      | $\mu\text{A}$           |
| $I_{MIN}$                              | Minimum Cathode Current for Regulation - (figure 1)<br>$V_{KA} = V_{REF}$                                                                                                       |         | 0.5      | 1        |          | 0.5      | 0.6      | mA                      |
| $I_{OFF}$                              | Off-State Cathode Current (figure 3)                                                                                                                                            |         | 180      | 500      |          | 180      | 500      | nA                      |
| $ Z_{KA} $                             | Dynamic Impedance ( note 3 )<br>$V_{KA} = V_{REF}$ , $\Delta I_K = 1\text{ to }100\text{ mA}$ , $f \leq 1\text{ kHz}$                                                           |         | 0.2      | 0.5      |          | 0.2      | 0.5      | $\Omega$                |

1)  $\Delta V_{REF}$  is defined as the difference between the maximum and minimum values obtained over the full temperature range  
 $\Delta V_{REF} = V_{REF\text{ max.}} - V_{REF\text{ min.}}$



2) The temperature coefficient is defined as the slopes (positive and negative) of the voltage vs temperature limits within which the reference is guaranteed.




3) The dynamic Impedance is defined as  $|Z_{KA}| = \frac{\Delta V_{KA}}{\Delta I_K}$

## ELECTRICAL CHARACTERISTICS


$T_{amb} = 25^{\circ}\text{C}$  (unless otherwise specified)

| Symbol                                 | Parameter                                                                                                                                                                     | TL1431I |          |           | TL1431AI |          |           | Unit                    |
|----------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------|----------|-----------|----------|----------|-----------|-------------------------|
|                                        |                                                                                                                                                                               | Min.    | Typ.     | Max.      | Min.     | Typ.     | Max.      |                         |
| $V_{REF}$                              | Reference Input Voltage -(figure 1)<br>$V_{KA} = V_{REF}$ , $I_K = 10\text{ mA}$                                                                                              | 2.490   | 2.500    | 2.510     | 2.493    | 2.500    | 2.507     | V                       |
| $\Delta V_{REF}$                       | Reference Input Voltage Deviation OverTemperature Range - ( figure 1, note 1)<br>$V_{KA} = V_{REF}$ , $I_K = 10\text{ mA}$ , $T_{MIN} \leq T_{AMB} \leq T_{MAX}$              |         | 7        | 30        |          | 7        | 30        | mV                      |
| $\frac{\Delta V_{REF}}{\Delta T}$      | Temperature Coefficient of Reference Input Voltage -( note 2)<br>$V_{KA} = V_{REF}$ , $I_K = 10\text{ mA}$ , $T_{MIN} \leq T_{AMB} \leq T_{MAX}$                              |         | $\pm 22$ | $\pm 100$ |          | $\pm 22$ | $\pm 100$ | ppm/ $^{\circ}\text{C}$ |
| $\frac{\Delta V_{REF}}{\Delta V_{KA}}$ | Ratio of Change in Reference Input Voltage to Change in Cathode to Anode Voltage - (figure 2)<br>$I_K = 10\text{mA}$ , $\Delta V_{KA} = 36\text{V to } 3\text{V}$             |         | -1.1     | -2        |          | -1.1     | -2        | mV/V                    |
| $I_{REF}$                              | Reference Input Current - (figure 2)<br>$I_K = 10\text{mA}$ , $R1 = 10\text{k}\Omega$ , $R2 = \infty$<br>$T_{MIN} \leq T_{AMB} \leq T_{MAX}$                                  |         | 1.5      | 2.5<br>3  |          | 1.5      | 2.5<br>3  | $\mu\text{A}$           |
| $\Delta I_{REF}$                       | Reference Input Current Deviation Over Temperature Range - (figure 2)<br>$I_K = 10\text{mA}$ , $R1 = 10\text{k}\Omega$ , $R2 = \infty$<br>$T_{MIN} \leq T_{AMB} \leq T_{MAX}$ |         | 0.5      | 1         |          | 0.8      | 1.2       | $\mu\text{A}$           |
| $I_{MIN}$                              | Minimum Cathode Current for Regulation - (figure1)<br>$V_{KA} = V_{REF}$                                                                                                      |         | 0.5      | 1         |          | 0.5      | 0.7       | mA                      |
| $I_{OFF}$                              | Off-State Cathode Current (figure 3)                                                                                                                                          |         | 180      | 500       |          | 180      | 500       | nA                      |
| $ Z_{KA} $                             | Dynamic Impedance - (note 3)<br>$V_{KA} = V_{ref}$ , $\Delta I_K = 1\text{ to }100\text{mA}$ , $f \leq 1\text{kHz}$                                                           |         | 0.2      | 0.5       |          | 0.2      | 0.5       | $\Omega$                |

1)  $\Delta V_{REF}$  is defined as the difference between the maximum and minimum values obtained over the full temperature range  
 $\Delta V_{REF} = V_{REF\text{ max.}} - V_{REF\text{ min.}}$




2) The temperature coefficient is defined as the slopes (positive and negative) of the voltage vs temperature limits within which the reference is guaranteed.




3) The dynamic Impedance is defined as  $|Z_{KA}| = \frac{\Delta V_{KA}}{\Delta I_K}$


**Figure 1 :** Test Circuit for  $V_{KA} = V_{REF}$




**Figure 2 :** Test Circuit for  $V_{KA} > V_{REF}$




**Figure 3 :** Test Circuit for  $I_{OFF}$




**Figure 4 :** Test Circuit for Phase Margin and Voltage Gain




**Figure 5 :** Block diagram of TL1431




**Figure 6 :** Test Circuit for Response time




Reference voltage vs Temperature




Reference voltage vs cathode current




Reference voltage vs cathode current




Reference current vs Temperature




Off-state cathode current vs Temperature




Ratio of change in  $V_{REF}$  to Change in  $V_{KA}$  vs Temperature




Drift of  $R_{KA}$  vs Temperature


Minimum operating current vs Temperature





Gain &amp; Phase vs Frequency




Stability behaviour with capacitive loads



Maximum power dissipation

Pulse response for  $I_K = 1 \text{ mA}$ 

**PACKAGE MECHANICAL DATA**  
8 PINS - BATWING PLASTIC MICROPACKAGE (SO)




| Dim. | Millimeters |      |      | Inches |       |       |
|------|-------------|------|------|--------|-------|-------|
|      | Min.        | Typ. | Max. | Min.   | Typ.  | Max.  |
| A    |             |      | 1.75 |        |       | 0.069 |
| a1   | 0.1         |      | 0.25 | 0.004  |       | 0.010 |
| a2   |             |      | 1.65 |        |       | 0.065 |
| a3   | 0.65        |      | 0.85 | 0.026  |       | 0.033 |
| b    | 0.35        |      | 0.48 | 0.014  |       | 0.019 |
| b1   | 0.19        |      | 0.25 | 0.007  |       | 0.010 |
| C    | 0.25        |      | 0.5  | 0.010  |       | 0.020 |
| c1   | 45° (typ.)  |      |      |        |       |       |
| D    | 4.8         |      | 5.0  | 0.189  |       | 0.197 |
| E    | 5.8         |      | 6.2  | 0.228  |       | 0.244 |
| e    |             | 1.27 |      |        | 0.050 |       |
| e3   |             | 3.81 |      |        | 0.150 |       |
| F    | 3.8         |      | 4.0  | 0.150  |       | 0.157 |
| L    | 0.4         |      | 1.27 | 0.016  |       | 0.050 |
| M    |             |      | 0.6  |        |       | 0.024 |
| S    | 8° (max.)   |      |      |        |       |       |



**PACKAGE MECHANICAL DATA**


3 PINS - PLASTIC PACKAGE TO92 (TAPE &amp; REEL)



| Dim.  | Millimeters |      |      | Inches |       |       |
|-------|-------------|------|------|--------|-------|-------|
|       | Min         | Typ. | Max. | Min.   | Typ.  | Max.  |
| AL    |             |      | 5.0  |        |       | 0.197 |
| A     |             |      | 5.0  |        |       | 0.197 |
| T     |             |      | 4.0  |        |       | 0.157 |
| d     |             | 0.45 |      |        | 0.018 |       |
| l1    | 2.5         |      |      | 0.098  |       |       |
| P     | 11.7        | 12.7 | 13.7 | 0.461  | 0.500 | 0.539 |
| PO    | 12.4        | 12.7 | 13   | 0.488  | 0.500 | 0.512 |
| P2    | 5.95        | 6.35 | 6.75 | 0.234  | 0.250 | 0.266 |
| F1/F2 | 2.4         | 2.5  | 2.8  | 0.094  | 0.098 | 0.110 |
| Δh    | -1          | 0    | 1    | -0.039 | 0     | 0.039 |
| ΔP    | -1          | 0    | 1    | -0.039 | 0     | 0.039 |
| W     | 17.5        | 18.0 | 19.0 | 0.689  | 0.709 | 0.748 |
| W0    | 5.7         | 6    | 6.3  | 0.224  | 0.236 | 0.248 |
| W1    | 8.5         | 9    | 9.75 | 0.335  | 0.354 | 0.384 |
| W2    |             |      | 0.5  |        |       | 0.020 |
| H     |             |      | 20   |        |       | 0.787 |
| H0    | 15.5        | 16   | 16.5 | 0.610  | 0.630 | 0.650 |
| H1    |             |      | 25   |        |       | 0.984 |
| DO    | 3.8         | 4.0  | 4.2  | 0.150  | 0.157 | 0.165 |
| L1    |             |      | 11   |        |       | 0.433 |

**PACKAGE MECHANICAL DATA**


3 PINS - PLASTIC PACKAGE TO92 (TAPE AMMO PACK)



| Dim.  | Millimeters |      |      | Inches |       |       |
|-------|-------------|------|------|--------|-------|-------|
|       | Min         | Typ. | Max. | Min.   | Typ.  | Max.  |
| AL    |             |      | 5.0  |        |       | 0.197 |
| A     |             |      | 5.0  |        |       | 0.197 |
| T     |             |      | 4.0  |        |       | 0.157 |
| d     |             | 0.45 |      |        | 0.018 |       |
| l1    | 2.5         |      |      | 0.098  |       |       |
| P     | 11.7        | 12.7 | 13.7 | 0.461  | 0.500 | 0.539 |
| PO    | 12.4        | 12.7 | 13   | 0.488  | 0.500 | 0.512 |
| P2    | 5.95        | 6.35 | 6.75 | 0.234  | 0.250 | 0.266 |
| F1/F2 | 2.4         | 2.5  | 2.8  | 0.094  | 0.098 | 0.110 |
| Δh    | -1          | 0    | 1    | -0.039 | 0     | 0.039 |
| ΔP    | -1          | 0    | 1    | -0.039 | 0     | 0.039 |
| W     | 17.5        | 18.0 | 19.0 | 0.689  | 0.709 | 0.748 |
| W0    | 5.7         | 6    | 6.3  | 0.224  | 0.236 | 0.248 |
| W1    | 8.5         | 9    | 9.75 | 0.335  | 0.354 | 0.384 |
| W2    |             |      | 0.5  |        |       | 0.020 |
| H     |             |      | 20   |        |       | 0.787 |
| H0    | 15.5        | 16   | 16.5 | 0.610  | 0.630 | 0.650 |
| H1    |             |      | 25   |        |       | 0.984 |
| DO    | 3.8         | 4.0  | 4.2  | 0.150  | 0.157 | 0.165 |
| L1    |             |      | 11   |        |       | 0.433 |

# **PACKAGE MECHANICAL DATA**

3 PINS - PLASTIC PACKAGE TO92 (BULK)



| Dim. | Millimeters |      |       | Inches |        |        |
|------|-------------|------|-------|--------|--------|--------|
|      | Min         | Typ. | Max.  | Min.   | Typ.   | Max.   |
| L    |             | 1.27 |       |        | 0.05   |        |
| B    | 3.2         | 3.7  | 4.2   | 0.126  | 0.1457 | 0.1654 |
| O1   | 4.45        | 5.00 | 5.2   | 0.1752 | 0.1969 | 0.2047 |
| C    | 4.58        | 5.03 | 5.33  | 0.1803 | 0.198  | 0.2098 |
| K    | 12.7        |      |       | 0.5    |        |        |
| O2   | 0.407       | 0.5  | 0.508 | 0.016  | 0.0197 | 0.02   |
| a    | 0.35        |      |       | 0.0138 |        |        |

Information furnished is believed to be accurate and reliable. However, STMicroelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of STMicroelectronics. Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. STMicroelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of STMicroelectronics.

© The ST logo is a registered trademark of STMicroelectronics

© 2002 STMicroelectronics - Printed in Italy - All Rights Reserved  
STMicroelectronics GROUP OF COMPANIES

Australia - Brazil - Canada - China - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia  
Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States

© <http://www.st.com>