


ZMY 1 ... ZMY 200 (1,3W)



Surface mount diode

Zener silicon diodes

ZMY 1...ZMY 200

Maximum Power Dissipation: 1,3 W

Nominal Z-voltage: 1 to 200 V

Features

- Max. solder temperature: 260°C
- Plastic material has UL classification 94V-0
- Standard Zener voltage tolerance is graded to the international E 24 (5%) standard. Other voltage tolerances and higher Zener voltages on request.

Mechanical Data

- Plastic case Melf / DO-213AB
- Weight approx.: 0.12 g
- Terminals: plated terminals solderable per MIL-STD-750
- Mounting position: any
- Standard packaging: 5000 pieces per reel

¹⁾ Mounted on P.C. board with 50 mm² copper pads at each terminal

²⁾ Tested with pulses

³⁾ The ZMY1 is a diode operated in forward. Hence, the index of all parameters should be "F" instead of "Z". The cathode, indicated by a white ring is to be connected to the negative pole.

Absolute Maximum Ratings T_c = 25 °C, unless otherwise specified			
Symbol	Conditions	Values	Units
P _{tot}	Power dissipation, T _A = 50 °C ¹⁾	1,3	W
P _{ZSM}	Non repetitive peak power dissipation, t < 10 ms	40	W
R _{thA}	Max. thermal resistance junction to ambient	45	K/W
R _{thT}	Max. thermal resistance junction to terminal	10	K/W
T _j	Operating junction temperature	- 50 ... + 150	°C
T _s	Storage temperature	- 50 ... + 175	°C

Type	Zener Voltage ²⁾ V _{Z@I_{ZT}}		Test curr. I _{ZT} mA	Dyn. Resistance Z _{ZT@I_{ZT}} Ω	Temp. Coeffiz. of V _Z a _{VZ} 10 ⁻⁴ /°C	I _R V _R μA V		Z- curr. ¹⁾ T _A = 50 °C I _{Zmax} mA
	V _{Zmin} V	V _{Zmax} V						
ZMY 1 ³⁾	0,71	0,82	100	0,5 (<1)	- 26 ... - 16			
ZMY 10	9,4	10,6	50	2 (<4)	+ 5 ... + 9	1	> 5	123
ZMY 11	10,4	11,6	50	4 (<7)	+ 5 ... + 10	1	> 5	112
ZMY 12	11,4	12,7	50	4 (<7)	+ 5 ... + 10	1	> 7	102
ZMY 13	12,4	14,1	50	5 (<10)	+ 5 ... + 10	1	> 7	92
ZMY 15	13,8	15,6	50	5 (<10)	+ 5 ... + 10	1	> 10	83
ZMY 16	15,3	17,1	25	6 (<15)	+ 6 ... + 11	1	> 10	76
ZMY 18	16,8	19,1	25	6 (<15)	+ 6 ... + 11	1	> 10	68
ZMY 20	18,8	21,2	25	6 (<15)	+ 6 ... + 11	1	> 10	61
ZMY 22	20,8	23,3	25	6 (<15)	+ 6 ... + 11	1	> 12	56
ZMY 24	22,8	25,6	25	7 (<15)	+ 6 ... + 11	1	> 12	51
ZMY 27	25,1	28,9	25	7 (<15)	+ 6 ... + 11	1	> 14	45
ZMY 30	28	32	25	8 (<15)	+ 6 ... + 11	1	> 14	41
ZMY 33	31	35	25	8 (<15)	+ 6 ... + 11	1	> 17	37
ZMY 36	34	38	10	16 (<40)	+ 6 ... + 11	1	> 17	34
ZMY 39	37	41	10	20 (<40)	+ 6 ... + 11	1	> 20	32
ZMY 43	40	46	10	24 (<45)	+ 7 ... + 12	1	> 20	28
ZMY 47	44	50	10	24 (<45)	+ 7 ... + 12	1	> 24	26
ZMY 51	48	54	10	25 (<60)	+ 7 ... + 12	1	> 24	24
ZMY 56	52	60	10	25 (<60)	+ 7 ... + 12	1	> 28	22
ZMY 62	58	66	10	25 (<80)	+ 8 ... + 13	1	> 28	20
ZMY 68	64	72	10	25 (<80)	+ 8 ... + 13	1	> 34	18
ZMY 75	70	79	10	30 (<100)	+ 8 ... + 13	1	> 34	16
ZMY 82	77	88	10	30 (<100)	+ 8 ... + 13	1	> 41	15
ZMY 91	85	96	5	40 (<200)	+ 9 ... + 13	1	> 41	14
ZMY 100	94	106	5	60 (<200)	+ 9 ... + 13	1	> 50	12
ZMY 110	104	116	5	80 (<250)	+ 9 ... + 13	1	> 50	11
ZMY 120	114	127	5	80 (<250)	+ 9 ... + 13	1	> 60	10
ZMY 130	124	141	5	90 (<300)	+ 9 ... + 13	1	> 60	9
ZMY 150	138	156	5	100(<300)	+ 9 ... + 13	1	> 75	8
ZMY 160	153	171	2,5	110(<350)	+ 9 ... + 13	1	> 75	8
ZMY 180	168	191	2,5	120(<350)	+ 9 ... + 13	1	> 90	7
ZMY 200	188	212	2,5	150(<350)	+ 9 ... + 13	1	> 90	6