




PLATING

1μ Ni + 0.4μmini Or

Part
number

SEE TABLE

8630-3098NLF	Power contact #8	4.40	5.00	3.90	8.98
8630-3056NLF	Power contact #12	2.80	3.65	2.40	3.18
8630-3060NLF	Power contact #14	2.10	3.00	1.70	1.91
8630-3064NLF	Power contact #16	1.70	2.60	1.50	1.34
part numbers	Designation	$\phi A^{+0.10}_0$	$\phi B^{\pm 0.10}$	ϕ ame mm	Section mm ²

CABLE

NOTE:RoHS INFORMATIONS

- The "LF" product meets European union Directives and other country regulations as described in GS-22-008.
- The product is not intended to be exposed to a manufacturing solder process.
- Packaging spec: see GS-14-920.

rev	ecn no	dr	date
A	LS06-0022	MPE	2006/03/11
B	LS06-0095	LGO	2006/06/23
C	F11-0326	APA	2011/10/28
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302	tolerance std ISO 406 ISO 1101	projection A3	mm
Dr	M.PESSON	2006/03/11	TOLERANCES UNLESS OTHERWISE SPECIFIED			size
Eng	M.PESSON	2006/03/11	ANGULAR	0.X	± 0.1	Scale
Chr	LEGARRE	2006/03/11	0.XX	± 0.1	ECN	5
Appr	LEGARRE	2006/03/11	0.XXX	± 0.1	F11-0326	
Product family			D-SUB			Spec ref -
FCI			PIN POWERS CONTACTS			Rev.
title			C01-8639-2160			C
catalog no			CUSTOMER			sheet 1 of 1

REV F - 2006-04-17

PDM: Rev:C

STATUS:Released

Printed: Nov 04, 2011