

14.2mm (0.56INCH) SINGLE DIGIT NUMERIC DISPLAY

Part Number: SC56-11SRWA Super Bright Red


Features

- 0.56 inch digit height.
- Low current operation.
- Excellent character appearance.
- Easy mounting on P.C. boards or sockets.
- Mechanically rugged.
- Standard : gray face, white segment.
- RoHS compliant.

Description

The Super Bright Red source color devices are made with Gallium Aluminum Arsenide Red Light Emitting Diode.

Package Dimensions& Internal Circuit Diagram







Notes

- 1. All dimensions are in millimeters (inches), Tolerance is ±0.25(0.01")unless otherwise noted.
- 2. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.

 SPEC NO: DSAA7778
 REV NO: V.15
 DATE: FEB/08/2011
 PAGE: 1 OF 6

 APPROVED: WYNEC
 CHECKED: Joe Lee
 DRAWN: D.M.Su
 ERP: 1301001099

Selection Guide

| Part No. | Dice | Lens Type | lv (ucd) [1] @ 10mA | | Description |
|-------------|---------------------------|----------------|------------------------|-------|--------------------------------------|
| | | | Min. | Тур. | |
| SC56-11SRWA | Super Bright Red (GaAlAs) | White Diffused | 14000 | 34000 | Common Cathode, Rt. Hand Decimal. |

Electrical / Optical Characteristics at TA=25°C

| | <u>'</u> | | | | | |
|--------|--------------------------|------------------|------|------|-------|--------------------|
| Symbol | Parameter | Device | Тур. | Max. | Units | Test Conditions |
| λpeak | Peak Wavelength | Super Bright Red | 660 | | nm | IF=20mA |
| λD [1] | Dominant Wavelength | Super Bright Red | 640 | | nm | I==20mA |
| Δλ1/2 | Spectral Line Half-width | Super Bright Red | 20 | | nm | IF=20mA |
| С | Capacitance | Super Bright Red | 45 | | pF | VF=0V;f=1MHz |
| VF [2] | Forward Voltage | Super Bright Red | 1.85 | 2.5 | V | I==20mA |
| lr | Reverse Current | Super Bright Red | | 10 | uA | V _R =5V |

Notes:

Absolute Maximum Ratings at TA=25°C


| Parameter | Super Bright Red | Units | | |
|---------------------------------|-----------------------|-------|--|--|
| Power dissipation | 75 | mW | | |
| DC Forward Current | 30 | mA | | |
| Peak Forward Current [1] | 155 | mA | | |
| Reverse Voltage | 5 | V | | |
| Operating / Storage Temperature | -40°C To +85°C | | | |
| Lead Solder Temperature[2] | 260°C For 3-5 Seconds | | | |

Notes: 1. 1/10 Duty Cycle, 0.1ms Pulse Width. 2. 2mm below package base.

SPEC NO: DSAA7778 **REV NO: V.15** DATE: FEB/08/2011 PAGE: 2 OF 6 APPROVED: WYNEC **CHECKED:** Joe Lee DRAWN: D.M.Su ERP: 1301001099

^{1.} Luminous intensity/ luminous Flux: +/-15%.


^{1.}Wavelength: +/-1nm. 2. Forward Voltage: +/-0.1V.





RELATIVE INTENSITY Vs. WAVELENGTH


Super Bright Red

SC56-11SRWA










SPEC NO: DSAA7778
APPROVED: WYNEC

REV NO: V.15 CHECKED: Joe Lee DATE: FEB/08/2011 DRAWN: D.M.Su PAGE: 3 OF 6 ERP: 1301001099




SPEC NO: DSAA7778 APPROVED: WYNEC REV NO: V.15 CHECKED: Joe Lee DATE: FEB/08/2011 DRAWN: D.M.Su PAGE: 4 OF 6 ERP: 1301001099

THROUGH HOLE DISPLAY MOUNTING METHOD


Lead Forming


Do not bend the component leads by hand without proper tools. The leads should be bent by clinching the upper part of the lead firmly such that the bending force is not exerted on the plastic body.



Installation


- 1. The installation process should not apply stress to the lead terminals.
- 2. When inserting for assembly, ensure the terminal pitch matches the substrate board's hole pitch to prevent spreading or pinching the lead terminals.





DISPLAY SOLDERING CONDITIONS

Wave Soldering Profile For Lead-free Through-hole LED.



NOTES:

- 1.Recommend the wave temperature 245°C~260°C.The maximum soldering temperature should be less than 260°C.
- 2.Do not apply stress on epoxy resins when temperature is over 85°C.
- 3. The soldering profile apply to the lead free soldering (Sn/Cu/Ag alloy).
- 4.During wave soldering , the PCB top-surface temperature should be kept below 105°C

5.No more than once.

 SPEC NO: DSAA7778
 REV NO: V.15
 DATE: FEB/08/2011
 PAGE: 5 OF 6

 APPROVED: WYNEC
 CHECKED: Joe Lee
 DRAWN: D.M.Su
 ERP: 1301001099

Soldering General Notes:


- a. Through—hole displays are incompatible with reflow soldering.
- b. If components will undergo multiple soldering processes, or other processes where the components may be subjected to intense heat, please check with Kingbright for compatibility.

CLEANING

- 1.Mild "no-clean" fluxes are recommended for use in soldering.
- 2. If cleaning is required, Kingbright recommends to wash components with water only. Do not use harsh organic solvents for cleaning, because they may damage the plastic parts .And the devices should not be washed for more than one minute.

CIRCUIT DESIGN NOTES

- 1.Protective current—limiting resistors may be necessary to operate the Displays.
- 2.LEDs mounted in parallel should each be placed in series with its own current—limiting resistor.



SPEC NO: DSAA7778
APPROVED: WYNEC

REV NO: V.15 CHECKED: Joe Lee DATE: FEB/08/2011 DRAWN: D.M.Su PAGE: 6 OF 6 ERP: 1301001099