



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	00		B	REV PER ECO 07-027471	1/16/2008	DW	JL



RECOMMENDED MOUNTING HOLE

			1060960-1
			PART NUMBER

ELECTRICAL	MECHANICAL	ENVIRONMENTAL
Nominal Impedance (Ohms) 50	Force to Engage: (Lbs) 3.4 MAX	TEMPERATURE RATING -65° TO +165°C Vibration MIL-STD-202, Method 204, Condition B Thermal Shock MIL-STD-202, Method 107, Condition B Moisture Resistance MIL-STD-202, Method 106 Corrosion - MIL-STD-202, Method 101, Condition B, 48 HRS XX.X = mm .XXX = in
Frequency Range (GHz) DC to 6		
Volt Rating (VRMS MAX) @ Sea Level 335	& Disengage: (Lbs) 1.77 MIN - 4.5 MAX	
VSWR N/A	Center Contact Captivation Designed to Maintain QSX Interface When Mating	
Insertion Loss N/A		
Corona, 70,000 Ft (VRMS MIN) 250		
Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1000		
Contact Resistance (Milliohms MAX) Center Contact 5.0 Outer Contact 1.0		
RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 670		
I.R.(Megohms MIN) 10,000		

XX.X = mm
.XXX = in

HOUSING MOUNTING NUT	BRASS PER ASTM-B-16, HALF HARD	NICKEL PLATE PER QQ-N-290
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204
LOCKWASHER	PHOSPHOR BRONZE PER QQ-B-750, GRADE B2 OR TIN BRASS PER ASTM-B-591	NICKEL PLATE PER QQ-N-290
COMPONENT	MATERIAL	FINISH
THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm [INCHES] TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.13 3 PLC ± - 4 PLC ± - ANGLES ± 1° FINISH - DWN M.M 8/22/94 CHK - APVD - PRODUCT SPEC - APPLICATION SPEC - WEIGHT - CUSTOMER DRAWING Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608 NAME MCX FRONT MOUNT BULKHEAD FEEDTHRU JACK RECEPTACLE SOLDER TERMINAL (5858-0000-10) SIZE A2 CAGE CODE 00779 DRAWING NO C=1060960-1 RESTRICTED TO - SCALE 10:1 SHEET 1 of 1 REV B		