





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50						
			AF2	REVISED PER ECO-13-007856	28MAY13	PB	YHM

- 1 OPERATION TEMPERATURE – 105°C MAX
- 2 RETENTION FORCE – 16 OUNCES MIN INITIALLY,
6 OUNCES MIN, AFTER 500 CYCLES.
- 3 REFER TO MOUNTING HOLE PATTERN
- 4 HOUSING NYLON TYPE 6/6
RECEPT & LEGS, BRASS
ASTM B36 ALLOY6



OBSOLETE	GOLD	NATURAL	6-582119-9
OBSOLETE	SILVER	NATURAL	5-582119-9
	GOLD	WHITE	3-582119-9
OBSOLETE	GOLD	GRAY	3-582119-8
OBSOLETE	GOLD	VIOLET	3-582119-7
OBSOLETE	GOLD	BLUE	3-582119-6
	GOLD	GREEN	3-582119-5
	GOLD	YELLOW	3-582119-4
OBSOLETE	GOLD	ORANGE	3-582119-3
	GOLD	RED	3-582119-2
OBSOLETE	GOLD	BROWN	3-582119-1
	GOLD	BLACK	3-582119-0
OBSOLETE	SILVER	WHITE	2-582119-9
OBSOLETE	SILVER	GRAY	2-582119-8
OBSOLETE	SILVER	VIOLET	2-582119-7
OBSOLETE	SILVER	BLUE	2-582119-6
OBSOLETE	SILVER	GREEN	2-582119-5
OBSOLETE	SILVER	YELLOW	2-582119-4
OBSOLETE	SILVER	ORANGE	2-582119-3
OBSOLETE	SILVER	RED	2-582119-2
OBSOLETE	SILVER	BROWN	2-582119-1
OBSOLETE	SILVER	BLACK	2-582119-0
LEGS & RECEPT FINISH		COLOR	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	17JUL08	Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: mm [INCHES]		CHK	17JUL08				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	17JUL08	NAME			
0 PLC ± -		PRODUCT SPEC					
1 PLC ± -		APPLICATION SPEC		TEST PROBE ASSEMBLY			
2 PLC ± 0.25 [.01]							
3 PLC ± -				SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
4 PLC ± -				A2	00779	C=582119	-
ANGLES ± -		WEIGHT	-	SCALE 5:1 SHEET 1 of 1 REV AF2			
FINISH		CUSTOMER DRAWING					
SEE TABLE							