



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	K3	REVISED PER ECO-11-005027	11MAR11	RK	HMR
	L	REVISED PER ECO-17-011181	04AUG2017	RS	MZ



- 1

NYLON, RED.
- 2

BRASS PER ASTM B36.
- 3

3.81 μ m [.000150] MIN TIN-LEAD OVER 2.54 μ m [.000100] MIN COPPER OR 1.27 μ m [.000050] MIN NICKEL.
- 4


0.76 μ m [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] MIN FROM MATING END, 3.81 μ m [.000150] MIN TIN-LEAD FOR A LENGTH OF 5.36 [.211] MIN FROM OPPOSITE END, BOTH OVER 1.27 μ m [.000050] MIN NICKEL.
- 5

3.81 μ m [.000150] MIN TIN OVER 2.54 μ m [.000100] MIN COPPER OR 1.27 μ m [.000050] MIN NICKEL.
- 6


0.76 μ m [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] A LENGTH MIN FROM MATING END, 3.81 μ m [.000150] MIN TIN FOR 1.27 μ m OF 5.36 [.211] MIN FROM OPPOSITE END, BOTH OVER [.000050] MIN NICKEL.
- 7

PRILIMINARY PART NUMBER.
- 8

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED PC BOARD LAYOUT



8	OBSOLETE	3.50 [.137]	6	1-207584-0
	OBSOLETE	7.52 [.296]	6	207584-9
8	OBSOLETE	4.72 [.186]	6	207584-8
		4.72 [.186]	5	207584-7
8	OBSOLETE	7.52 [.296]	4	207584-6
		4.72 [.186]	4	207584-3
8	OBSOLETE	4.72 [.186]	3	207584-1
		A	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	L.SIPE	07/21/92	TE Connectivity	
		CHK	R.STONE	7-24-92		
DIMENSIONS:		APVD	—	—	NAME	
mm [INCHES]		PRODUCT SPEC	—	—		
		APPLICATION SPEC	—	—	SIZE	
		—	—	—		
MATERIAL		WEIGHT	—	—	CAGE CODE	
HOUSING: 1		CUSTOMER DRAWING	—	—	DRAWING NO	
CONTACTS: 2		SCALE	2:1	—	SHEET	
		1 of 1	—	—	REV	
		L	—	—		