


Commercial Switches and Sensors



Pressure

Mass Airflow

Force

Humidity

Product solutions on the Interactive Catalogue

Temperature - RTDs

Temperature - Thermistors

Temperature - Probes

Thermostats - Commercial

Thermostats - Precision

Heaters

Combi-sensor

Thermal Cutoffs



Position

Infrared

Current

Liquid Level

Basic Switches



Interactive Catalog

www.honeywell.com/sensing

February 2004

COMMERCIAL SWITCHES AND SENSORS

Honeywell's Commercial Switches and Sensors offer a wide selection of products and technology capability for applications in medical devices and equipment; heating, ventilation, air-conditioning and refrigeration; information technology; home appliances; motor control and automotive passenger cars. This catalogue contains a selection of our most popular, established product listings – all tried and tested in field applications. To view our complete range of products, visit our website at www.honeywell.com/sensing.

How to use this catalogue

For each referenced listing, key specification parameters, descriptions and mounting drawing information are presented. These listings illustrate our capabilities while the specifications included allow easy differentiation between similar products. For products with no specific reference numbers, please contact your local Honeywell sales office.

There are, of course, many more product options available. Full product specification information may be accessed on our website (www.honeywell.com/sensing). At the Home page enter the catalogue listing reference in the SEARCH box and click GO! This will take you directly to the interactive catalogue/specification search tables for this listing. Alternatively, select and click the interactive catalogue icon on the Home page and then choose a product category against which to do a specification search.

Also on the website you can access installation instructions, application notes, Frequently Asked Questions (FAQs), selection guides and additional technical information.

Mounting dimensions

Mounting dimensions shown in each product section are for reference only. For exacting layout work, request an engineering drawing from your nearest Honeywell sales office. Where dual dimensions are shown on mounting drawings, the first or upper one is millimetres (mm) and the second or lower is inches (in). Where single dimensions are shown, they are millimetres (mm), unless otherwise stated.

To order these products

Simply contact your local Honeywell Distributor or your local Honeywell office. More information on Honeywell products and how to contact us can be found at <http://locator.micro.honeywell.com/>

System critical sensing solutions

A system is critical if the quality, reliability, delivery and customer service associated with a component part is essential to the performance of the operation or end product. If a sensor or switch is critical to the performance, cost effectiveness, delivery or safety of a product or operation, then it is system critical. It is therefore a defining element in the performance of the system under whatever conditions apply. Failure of the component – or failure of delivery of the component – results in lost productivity, increased costs or a catastrophic event such as a shutdown. Therefore selecting the right product is essential. It can make the difference between success and failure.

Honeywell – delivering excellence

To deliver the right products for our customers' applications we listen to them to understand their needs. Using techniques such as "Voice of the Customer" and "Concept Engineering" we make sure that the products and solutions we deliver are the right ones. As part of Honeywell we can use local knowledge and understanding combined with global expertise and resources to achieve this. We can deploy many key technologies to bring innovative solutions to customers' problems.

Our products are manufactured to work well and to last. We use Six Sigma Plus productivity to ensure this is the case. We have award winning manufacturing facilities around the world and recognised world class business excellence in manufacturing and supply chain management to deliver on time, anywhere in the world.

Our e-business approach offers instant access to product information, technical support and application knowledge through our Internet site. Check out our powerful new interactive catalogue that can search and find the right products for customers' needs and deliver a drawing ready for incorporation in a CAD system direct to your desk.

And of course, we manage our whole business for the benefit of our customers, using an acknowledged world-class business excellence approach that incorporates Six Sigma principles.



Interactive Catalog
www.honeywell.com/sensing

CONTENTS

Pressure Sensors	Page 4	Thermostats - Precision	Page 31
Absolute, differential, gauge, and vacuum gauge pressure sensors for media that are compatible with a silicon diaphragm. These sensors are ideal for low-cost commercial grade applications, such as printed circuit boards. Small and reliable, they offer excellent repeatability and high accuracy under varying environmental conditions.		Hermetic and non-hermetic thermostats in standard and custom packages for use in a wide variety of precision applications.	
Mass Airflow Sensors	Page 10	Heaters	Page 37
Amplified and unamplified microbridge mass airflow sensors provide a sensitive and fast response and high accuracy over a broad range of gas and air flows.		Wire-wound, chemically-etched, high temperature and transparent heaters in a variety of sizes and geometries.	
Force Sensors	Page 13	Combi-sensor	Page 39
Compact, extremely sensitive devices for precise, reliable performance in any application that requires precision force measurement.		Liquid pressure/temperature sensor that uses piezoresistive and thermistor sensing technology to measure water pressure and temperature.	
Humidity Sensors	Page 15	Thermal Cutoffs	Page 40
Relative humidity sensors with on-chip signal conditioning. Chemically resistant packaging to accommodate harsh environments. Sensor construction consists of a planar capacitor with a second polymer layer to protect against dirt, dust, oils and other hazards.		Dependable organic thermal cutoffs in temperatures ranging from 72 °C to 240 °C [162 °F to 464 °F]. They are available in various lead lengths and configurations.	
Temperature Sensors - RTDs	Page 16	Position Sensors	Page 42
Platinum and silicon-based thin film resistance temperature devices (RTDs) for applications that require small package size, accuracy and linear outputs.		Hall effect and magnetoresistive sensors for all applications that require accurate, reliable outputs.	
Temperature Sensors - Thermistors	Page 18	Infrared Products	Page 46
Precision Hi-Rel negative temperature coefficient (NTC) thermistors and positive temperature coefficient (PTC) thermistors for use in a broad variety of temperature measurement and control applications.		Optoelectronic standard infrared emitting diodes (IREDs), sensors and assemblies for object presence, limit and motion sensing, position encoding and movement encoding.	
Temperature Sensors - Probes	Page 24	Current Sensors	Page 52
A variety of customized probes for use in the automotive and other industries.		Adjustable linear null balance, digital and linear output current sensors for monitoring ac or dc current.	
Thermostats - Commercial	Page 27	Liquid Level Sensors	Page 56
Dependable bimetal thermostats include choice of automatic or manual reset, phenolic or ceramic housings, and a variety of mounting brackets and terminal options.		Sensitive sensors in a variety of housing types for detecting the presence or absence of a wide range of liquids.	
		Basic Switches	Page 57
		Standard, miniature and subminiature switches, available in a range of enclosures and with a variety of actuators. They are ideal for use alone or built into assemblies.	

⚠ WARNING**MISUSE OF DOCUMENTATION**

- The information presented in this product sheet (or catalogue) is for reference only. DO NOT USE this document as product installation information.
- Complete installation, operation and maintenance information is provided in the instructions supplied with each product.

Failure to comply with these instructions could result in death or serious injury.

⚠ WARNING**PERSONAL INJURY**

DO NOT USE these products as safety or emergency stop devices, or in any other application where failure of the product could result in personal injury

Failure to comply with these instructions could result in death or serious injury.

Pressure Sensors



24PC/26PC Series

Signal conditioning: Unamplified noncompensated - (24PC Series)
compensated - (26PC Series)

Supply voltage: 10 Vdc typ.
12 Vdc max. (24PC Series)
16 Vdc max. (26PC Series)

Operating temperature: -40 °C to 85 °C
-40 °F to 185 °F


Port style: Straight or Flow Through

Termination: PCB; 1 x 4; 0.600 in (Type 6)
PCB; 2 x 2; (Type 2)
1 x 4 with connector (Type 5)

OPTIONS


Differential

MOUNTING DIMENSIONS (for reference only) mm/in
DIFFERENTIAL SENSOR
1 X 4 Termination (Style 6) Port Style A, Straight (Only)



Gauge

MOUNTING DIMENSIONS (for reference only) mm/in
GAUGE SENSOR
1 x 4 Termination (Style 6) Port Style A, Straight
Pin 1 is notched, Pin 2 is next to Pin 1, etc.




24PC Series

MEASUREMENT TYPE	PRESSURE RANGE	REFERENCE
Gauge/Vacuum Gauge	1.0 psi	24PCAF6G
Differential/Vacuum Gauge	5.0 psi	24PCBFA6D
Gauge/Vacuum Gauge	5.0 psi	24PCBFA6G
Differential/Vacuum Gauge	15.0 psi	24PCCFA6D
Gauge/Vacuum Gauge	15.0 psi	24PCCFA6G
Differential/Vacuum Gauge	30.0 psi	24PCDFA6D
Gauge/Vacuum Gauge	30.0 psi	24PCDFA6G
Differential	0.5 psi	24PCEFA6D
Gauge	0.5 psi	24PCEFA6G
Differential	100 psi	24PCFFA6D
Gauge	100 psi	24PCFFA6G

26PC Series

MEASUREMENT TYPE	PRESSURE RANGE	REFERENCE
Differential/Vacuum Gauge	1.0 psi	26PCAF6D
Gauge/Vacuum Gauge	1.0 psi	26PCAF6G
Differential	5.0 psi	26PCBFA6D
Gauge	5.0 psi	26PCBFA6G
Differential/Vacuum Gauge	15.0 psi	26PCCFA6D
Gauge/Vacuum Gauge	15.0 psi	26PCCFA6G
Differential	30.0 psi	26PCDFA6D
Gauge	30.0 psi	26PCDFA6G
Gauge	100 psi	26PCFFA6G
Differential	250 psi	26PCGFA6D

Flow Through Type 6



24PC Series


MEASUREMENT TYPE	PRESSURE RANGE	REFERENCE
Flow Through/Vacuum Gauge	15.0 psi	24PCCFG6G
Flow Through/Vacuum Gauge	30.0 psi	24PCDFG6G

26PC Series

MEASUREMENT TYPE	PRESSURE RANGE	REFERENCE
Flow Through/Vacuum Gauge	1.0 psi	26PCAFG6G
Flow Through	15.0 psi	26PCCFG6G
Gauge/Vacuum Gauge	100 psi	26PCFFG6G

24PC/26PC Series (Continued)


Type 2



26PC Series

MEASUREMENT TYPE	PRESSURE RANGE	REFERENCE
Flow Through	30.0 psi	26PCDFG2G

Type 5



26PC Series

MEASUREMENT TYPE	PRESSURE RANGE	REFERENCE
Flow Through/Vacuum Gauge	100 psi	26PCFFU5G

24PC/26PC SMT (Surface Mount Technology)

Signal conditioning: Unamplified
noncompensated - (24PC SMT Series)
compensated - (26PC SMT Series)


Supply voltage: 10 Vdc typ.
12 Vdc max. (24PC SMT Series)
16 Vdc max. (26PC SMT Series)

Operating temperature: -40 °C to 85 °C
-40 °F to 185 °F

Port style: Straight, 1.88 mm Ø (0.74 in)

Termination: SMT solder

Measurement type: Gauge, Vacuum Gauge,
Differential, Wet/Wet Differential



OPTIONS

24PC SMT Series

PRESSURE RANGE	REFERENCE
0 psi to 1.0 psi	24PC01SMT
0 psi to 5.0 psi	24PC05SMT
0 psi to 15.0 psi	24PC15SMT

26PC SMT Series

PRESSURE RANGE	REFERENCE
0 psi to 1.0 psi	26PC01SMT
0 psi to 5.0 psi	26PC05SMT
0 psi to 15.0 psi	26PC15SMT

CPC/CPX Series Low Pressure

Signal conditioning: Unamplified
compensated - (CPC Series)
noncompensated - (CPX Series)


Supply voltage: 12 Vdc typ.
16 Vdc max.

Operating temperature: -25 °C to 85 °C
-13 °F to 185 °F

Port style: Barbed

Termination: PCB

Accuracy grade: Commercial (1.0 %)



OPTIONS

CPC Series

MEASUREMENT TYPE	PRESSURE RANGE	REFERENCE
Differential	(1.0 psi) 4.0 in H ₂ O	CPCL04DFC
Gauge	(1.0 psi) 4.0 in H ₂ O	CPCL04GFC
Differential	(1.0 psi) 10.0 in H ₂ O	CPCL10DFC

CPX Series


MEASUREMENT TYPE	PRESSURE RANGE	REFERENCE
Differential	4.0 in H ₂ O	CPXL04DF
Differential	10.0 in H ₂ O	CPXL10DF

DC Series, Low Pressure

Signal conditioning:	Amplified compensated unregulated (DC001NDC4) regulated (DC005NDR4)
Supply voltage:	5 Vdc typ., 5.1 Vdc max. (DC001NDC4) 7 Vdc to 35 Vdc (DC005NDR4)
Operating temperature:	-25 °C to 85 °C -13 °F to 185 °F
Port style:	Barbed
Termination:	PCB


OPTIONS

DC001NDC4



MEASUREMENT TYPE	PRESSURE RANGE	REFERENCE
Differential	1.0 in H ₂ O	DC001NDC4

DC005NDR4




MEASUREMENT TYPE	PRESSURE RANGE	REFERENCE
Differential	5.0 in H ₂ O	DC005NDR4

DCXL/DUXL Series, Low Pressure

Signal conditioning:	Unamplified compensated (DCXL) noncompensated (DUXL)
Supply voltage:	12 Vdc typ., 16 Vdc max. (DCXL) 4.5 Vdc min., 8 Vdc max. (DUXL)
Operating temperature:	-25 °C to 85 °C -13 °F to 185 °F
Port style:	Barbed
Termination:	PCB


OPTIONS

DCXL Series



MEASUREMENT TYPE	PRESSURE RANGE	REFERENCE
Differential	1.0 in H ₂ O	DCXL01DN
Differential	10.0 in H ₂ O	DCXL10DN

DUXL Series



MEASUREMENT TYPE	PRESSURE RANGE	REFERENCE
Differential	1.0 in H ₂ O	DUXL01D
Differential	10.0 in H ₂ O	DUXL10D


XCA Series

Signal conditioning:
Supply voltage:
Operating temperature:

Amplified compensated
 5 Vdc typ., 16 Vdc max.
 -25 °C to 85 °C
 -13 °F to 185 °F
 Barbed
 PCB

Port style:
Termination:

Unamplified compensated
 12 Vdc typ., 16 Vdc max.
 -25 °C to 85 °C
 -13 °F to 185 °F
 Barbed
 PCB
 Commercial (1.0 %)



MEASUREMENT TYPE	PRESSURE RANGE	REFERENCE
Absolute	15.0 psia	XCA415AN


XCX Series

Signal conditioning:
Supply voltage:
Operating temperature:

Unamplified compensated
 12 Vdc typ., 16 Vdc max.
 -25 °C to 85 °C
 -13 °F to 185 °F

Port style:
Termination:
Accuracy grade:

Barbed
 PCB
 Commercial (1.0 %)




MEASUREMENT TYPE	PRESSURE RANGE	ACCURACY GRADE	REFERENCE
Differential	1.0 psi		XCX01DNC
Differential	1.0 psi	High (0.50 %)	XCX01DNH
Differential	15.0 psi		XCX15DNC

XPC Series


Signal conditioning:
Supply voltage:
Operating temperature:

Port style:
Termination:
Accuracy grade:

DF Housing



DT Housing




MEASUREMENT TYPE	PRESSURE RANGE	PORT STYLE	REFERENCE
Differential	1.0 psi	Axial	XPC01DFC
Differential	15.0 psi	Radial	XPC15DTC

XSX Series, Low pressure

Signal conditioning:
Supply voltage:
Operating temperature:

Port style:
Termination:
Accuracy grade:

Unamplified uncompensated
 12 Vdc typ., 16 Vdc max.
 -25 °C to 85 °C [-13 °F to 185 °F]
 Button
 PCB
 Commercial (1.0 %)




MEASUREMENT TYPE	PRESSURE RANGE	REFERENCE
Gauge	4.0 in H ₂ O	XSXL04GF

ASDX Series


Signal conditioning: Amplified compensated
Supply voltage: 4.75 Vdc to 5.25 Vdc
Operating temperature: -20 °C to 105 °C [-4 °F to 221 °F]
Port style: Taper 2,29 mm [0.090 in]
Termination: PCB
Accuracy grade: ±2.0 %

A2 Package




MEASUREMENT TYPE	PRESSURE RANGE	REFERENCE
Absolute	0 psi to 15 psi	ASDX015A24R
Absolute	0 psi to 30 psi	ASDX030A24R
Absolute	0 psi to 100 psi	ASDX100A24R

D4 Package



MEASUREMENT TYPE	PRESSURE RANGE	REFERENCE
Differential/gauge	0 psi to 1 psi	ASDX001D44R
Differential/gauge	0 psi to 5 psi	ASDX005D44R
Differential/gauge	0 psi to 15 psi	ASDX015D44R
Differential/gauge	0 psi to 30 psi	ASDX030D44R
Differential/gauge	0 psi to 100 psi	ASDX100D44R


G2 Package



MEASUREMENT TYPE	PRESSURE RANGE	REFERENCE
Gauge	0 psi to 1 psi	ASDX001G24R
Gauge	0 psi to 5 psi	ASDX005G24R
Gauge	0 psi to 15 psi	ASDX015G24R
Gauge	0 psi to 30 psi	ASDX030G24R
Gauge	0 psi to 100 psi	ASDX100G24R

40PC Series, Miniature Signal Conditioned

Signal conditioning: Amplified
Supply voltage: 5 Vdc ± 0.25 Vdc
Operating temperature: -45 °C to 125 °C
Port style: Straight for O-ring interface
Termination: PCB, unformed



MEASUREMENT TYPE	PRESSURE RANGE	REFERENCE
Bi-Directional Gauge/Vacuum Gauge	± 50 mm HG	40PC001B1A
Gauge	0 to 300 mm HG	40PC006G1A
Vacuum	0 to -15.0 psi	40PC015V1A
Gauge	15.0 psi	40PC015G1A
Gauge	30.0 psi	40PC030G1A
Gauge	100 psi	40PC100G1A
Gauge	150 psi	40PC150G1A
Gauge	250 psi	40PC250G1A
Gauge	500 psi	40PC500G1A

140PC Series

Signal conditioning:


Supply voltage:

Operating temperature:

Port style:

Termination:

Amplified
8 Vdc typ., 16 Vdc max.
-40 °C to 85 °C
-40 °F to 185 °F
Straight
PCB



Note: Dimensions shown apply to Differential and Absolute versions. Gauge units are identical, except the P1 port is absent.

MEASUREMENT TYPE	PRESSURE RANGE	TERMINATION	REFERENCE
Gauge/Vacuum Gauge	-15 psi		141PC15G
Differential/Vacuum Gauge	1.0 psi		142PC01D
Gauge	1.0 psi		142PC01G
Gauge	2.0 psi		142PC02G
Differential/Vacuum Gauge	5.0 psi		142PC05D
Differential/Vacuum Gauge	-39 in H ₂ O to 55 in H ₂ O		142PC05D97
Gauge	5.0 psi		142PC05G
Absolute	15 psia		142PC15A
Absolute	15 psia	Leadwire	142PC15AW95
Gauge	15 psi		142PC15G
Differential/Vacuum Gauge	± 2.5 psi		143PC03D
Differential/Vacuum Gauge	± 5.0 psi	Leadwire	143PC05DW

160PC Series, Low Pressure

Signal conditioning:


Supply voltage:

Operating temperature:

Port style:

Termination:

Amplified
8 Vdc typ., 16 Vdc max.
-40 °C to 85 °C
-40 °F to 185 °F
Straight
PCB



Note: Dimensions shown apply to Differential and Absolute versions. Gauge units are identical, except the P1 port is absent.

MEASUREMENT TYPE	PRESSURE RANGE	SUPPLY VOLTAGE	REFERENCE
Differential/Vacuum Gauge	0 to 27.68 in H ₂ O		162PC01D
Differential/Vacuum Gauge	± 5.0 in H ₂ O		163PC01D36
Differential/Vacuum Gauge	-20 cm to 120 cm H ₂ O		163PC01D48
Differential/Vacuum Gauge	-20 cm to 120 cm H ₂ O	5 Vdc	163PC01D61
Differential/Vacuum Gauge	± 2.5 in H ₂ O		163PC01D75
Differential/Vacuum Gauge	10.0 in H ₂ O		164PC01D37
Differential/Vacuum Gauge	5.0 in H ₂ O		164PC01D76

Mass Airflow Sensors



Mass Airflow sensors contain a thin-film, thermally isolated bridge structure containing heater and temperature sensing elements. The bridge structure provides a sensitive and fast response to the flow of air or other gas over the chip.

State-of-the-art chip design and manufacturing techniques allow the microbridge to be remarkably sensitive, fast, small. Used wherever airflow needs to be measured.

Supply voltage:

Operating temperature:

Media compatibility:

8 Vdc to 15 Vdc

-25 °C to 85 °C (-13 °F to 185 °F)

Dry gas only


AWM2000 Series

The AWM2000 Series microbridge mass airflow sensor is a passive device comprised of two Wheatstone bridges and has bidirectional sensing capability. The heater control circuit is required for operation per specifications. The sensing bridge supply circuit is also required for operation per specifications. These two circuits are not on board the package and must be supplied in the application. The differential amplifier is a useful interface for the sensing bridge. It can be used to introduce gain and to voltage offsets to the sensor output.

Signal conditioning: Unamplified (-44,5 mVdc to 44,5 mVdc)

Port style: Straight

Sensor resistance: 5 kOhm



FLOW/PRESSURE RANGE	REFERENCE
± 200 sccm	AWM2100V
± 4.0 in H ₂ O (10 mBar)	AWM2200V
± 1000 sccm (1 SLPM)	AWM2300V

AWM3000 Series


Like the AWM2000 Series, the dual Wheatstone bridges control airflow measurement. The AWM3000 Series is amplified; therefore, it can be used to increase the gain and to introduce voltage offsets to the sensor output. The heater control circuit and the sensing bridge supply circuit are on board the package.

Signal conditioning:

Amplified (1 Vdc to 5 Vdc)

Port style:

Straight



FLOW/PRESSURE RANGE	REFERENCE
± 200 sccm	AWM3100V
+ 2.0 in H ₂ O (5 mBar)	AWM3200V
± 1000 sccm (1 SLPM)	AWM3300V


AWM40000 Series

The microbridge mass airflow sensor operates on the theory of heat transfer. Mass airflow is directed across the surface of the sensing elements. Output voltage varies in proportion to the mass air or other gas flow through the inlet and outlet ports of the package. The specially designed housing precisely directs and controls the airflow across the microstructure sensing element. Mechanical design of the package allows it to be easily mounted to printed circuit boards.

The microbridge mass airflow sensor has a unique silicon chip based on advanced microstructure technology. It consists of a thin-film, thermally isolated bridge structure containing heater and temperature sensing elements. The bridge structure provides a sensitive and fast response to the flow of air or other gas over the chip. Dual sensing elements positioned on both sides of a central heating element indicate flow direction as well as flow rate. Laser trimmed thick film and thin film resistors provide consistent interchangeability from one device to the next.

Port style:

Manifold



SIGNAL CONDITIONING	FLOW/PRESSURE RANGE	REFERENCE
Unamplified (8.5 mV)	± 25 sccm	AWM42150VH
Unamplified (54.7 mV)	± 1000 sccm (1 SLPM)	AWM42300V
Amplified (1 Vdc to 5 Vdc)	± 1000 sccm (1 SLPM)	AWM43300V
Amplified (1 Vdc to 5 Vdc)	+ 6 SLPM	AWM43600V

AWM5000 Series - High flow

AWM5000 Series Microbridge Mass Airflow Sensors feature a Venturi type flow housing. They measure flow as high as 20 standard liters per minute (SLPM) while inducing a maximum pressure drop of 2.25 inches H₂O. The microbridge chip is in direct contact with the flow stream, greatly reducing error possibilities due to orifice or bypass channel clogging.

The rugged plastic package has been designed to withstand common mode pressures up to 50 psi, and the small sensing element allows 100 g of shock without compromising performance. The included "AMP" compatible connector provides reliable connection in demanding applications.


Each AWM5000 sensor contains circuitry which performs amplification, linearization, temperature compensation, and gas calibration. A 1 to 5 Vdc linear output is possible for all listings regardless of flow range (5, 10, 15, or 20 SLPM) or calibration gas (nitrogen, carbon dioxide, nitrous oxide, or argon). All calibration is performed by active laser.

Signal conditioning:

Amplified (1 Vdc to 5 Vdc)

Port style:

Threaded, 1/4" NPT



FLOW/PRESSURE RANGE

0 SLPM to 5 SLPM (N₂ calibration)
0 SLPM to 10 SLPM (N₂ calibration)
0 SLPM to 20 SLPM (CO₂ calibration)
0 SLPM to 20 SLPM (N₂ calibration)

REFERENCE

AWM5101VN
AWM5102VN
AWM5104VC
AWM5104VN

AWM700 Series


AWM700 Series microbridge mass airflow sensors provide in-line flow measurement with a specially designed bypass flow housing. The sensors measure flow as high as 200 standard liters per minute (SLPM) while inducing a pressure drop of 1 inch H₂O, typically. The AWM700 has a high flow range capability in a small package.

Signal conditioning:

Amplified (1 Vdc to 5 Vdc)

Port style:

Tapered, 22 mm



FLOW/PRESSURE RANGE

+ 200 SLPM

REFERENCE

AWM720P1

CAUTION

PRODUCT DAMAGE

AWM Series Microbridge Mass Airflow Sensors are not designed to sense liquid flow and will be damaged by liquid flow through the sensor.

Failure to comply with these instructions could result in product


AWM90000 Series

The AWM90000 Series microbridge mass airflow sensors are available in two versions, mass flow and differential pressure. The AWM92100V has a flow range of ±200 sccm with a pressure drop of only 0.49 mBar, typically. The AWM92200V is a differential pressure version that has a range of ±2 in H₂O.

The AWM90000 Series has a 1 ms response time, operates with a supply voltage from 8.0 Vdc to 15.0 Vdc, while consuming only 50 mW of power. The compact plastic package will withstand a maximum overpressure of 25 psi without compromising performance.

Signal Conditioning:
Port Style:

Unamplified
Straight



FLOW RANGE (FULL SCALE)	PRESSURE RANGE	REFERENCE
±200 sccm	—	AWM92100V
—	±2.0 H ₂ O (5 mBar)	AWM92200V

NOTICE

LAMINAR FLOW

Due to the fast response time of the sensor, these specifications were generated using laminar flow. Airflow instability or “turbulence” present in the airstream will result in an increase in measurement uncertainty.

The turbulent flow problem can be corrected by either straightening the airflow using flow laminarizing or by slowing the response of the sensor using a simple RC time constant on the output of the sensor. This, of course, slows down the sensor response time. The values needed depend on the amount of turbulence present in the application.

Several techniques for laminarizing the flow include adding hex shaped honeycombs, foam, screen materials or adding constrictors (frits) to the flow stream. There are various commercial laminar flow elements that can be purchased. Unfortunately the greater the efficiency of the laminarizer, the greater the increase in pressure drop in order to establish a given flow rate. Plastic honeycomb material probably gives the most improvement for the least pressure drop. In any test fixture, the avoidance of sharp radii is an absolute requirement.

CAUTION

PRODUCT DAMAGE

AWM Series Microbridge Mass Airflow Sensors are not designed to sense liquid flow and will be damaged by liquid flow through the sensor.

Failure to comply with these instructions could result in product

Force Sensors


Force sensors operate on the principle that the resistance of silicon implanted piezoresistors will increase when the resistors flex under any applied force. The sensor concentrates force from the application, through the stainless steel plunger, directly to the silicon sensing element. The amount of resistance changes in proportion to the amount of force being applied. This change in circuit resistance results in a corresponding mV output level.



FSG Series

Plunger actuator - Force range 1500 g

Supply voltage: 360 mV span @ 10 Vdc
Operating temperature: -40 °C to 85 °C
 -40 °F to 185 °F
Sensitivity: 0.20 mV/g min., 0.24 mV/g typ., 0.28 mV/g max.
Overforce: 5500 g




Non-compensated

REFERENCE
FSG15N1A

FSL Series

Ball bearing actuator - Force range 500 g

Supply voltage: 60 mV span @ 5 Vdc
Operating temperature: -40 °C to 85 °C
 -40 °F to 185 °F
Sensitivity: 0.10 mV/g min., 0.12 mV/g typ., 0.14 mV/g max.
Overforce: 4500 g



Non-compensated

REFERENCE
FSL05N2C

Model 1865 Force/Pressure Transducer

The Model 1865 is a high-performance transducer specifically designed to address the needs of medical and specialized OEM applications. Offering laser-trimmed compensation, the Model 1865 may be specified to operate with either a constant current or voltage supply.

The Model 1865 employs a solid state piezoresistive pressure transducer mounted in a plastic package. For applications where force is applied by a flexible membrane to the sensor, such as found in infusion pumps, the Model 1865's precision height silicone diaphragm provides long life and is a reliable replacement for older force or load cell transducers. Utilizing a silicon rubber diaphragm, the 1865 is compatible with some liquid media applications. The Model 1865 may be operated in either current or voltage excitation, and its output may be amplified or signal conditioned, as required. The semiconductor-based sensor offers high resolution using its Wheatstone Bridge strain gauge design. The height of the unit's patented, poured-in-place silicon rubber diaphragm is controlled to ensure sensitivity to low pressure. This diaphragm is bonded to a plastic header and transmits force applied through a special silicone gel to the diaphragm of a silicon piezoresistive die. The back of the die is exposed to atmospheric pressure, which results in a gauge pressure output.

Pressure over-range protection: 3X span or 60 psi, whichever is least
Media/materials compatibility


Top side: Room atmosphere, directly applied force, and liquids compatible with dimethyl silicon, polyetherimide (Ultem)

Bottom side: Non-corrosive dry gasses and fluids compatible with silicon, pyrex, RTV silicone, and ceramic

Sensor: Gauge pressure

Diaphragm: Dimethyl silicone

Compensation: Laser trimmed normalised output



OPTIONS

Excitation 1.5 mA

PRESSURE	REFERENCE
0 psi to 5 psi	1865-01G-L-N
0 psi to 10 psi	1865-02G-L-N
0 psi to 15 psi	1865-03G-L-N
0 psi to 25 psi	1865-04G-L-N
0 psi to 30 psi	1865-05G-L-N

Excitation 10 Vdc

PRESSURE	REFERENCE
0 psi to 5 psi	1865-01G-K-N
0 psi to 10 psi	1865-02G-K-N
0 psi to 15 psi	1865-03G-K-N
0 psi to 25 psi	1865-04G-K-N
0 psi to 30 psi	1865-05G-K-N

Humidity Sensors



Relative Humidity/Temperature and Relative Humidity sensors are configured with integrated circuitry to provide on-chip signal conditioning. These sensors contain a capacitive sensing die set in thermoset polymers that interacts with platinum electrodes. The laser trimmed sensors have an interchangeability of + 5%RH, with stable, low drift performance.

Absorption based humidity sensors provide both temperature and %RH (Relative Humidity) outputs. On-chip signal processing ensures linear voltage output versus %RH. Sensor laser trimming offers + 5%RH accuracy, and achieves 2%RH accuracy with calibration. Packages are chemically resistant and operate in ranges of -40 °C to 85 °C (-40 °F to 185 °F) to accommodate harsh environments.

Supply voltage:

4.0 Vdc to 5.8 Vdc

Operating humidity range:

0 to 100% RH, non-condensing

Operating temperature range:

-40 °C to 85 °C (-40 °F to 185 °F)

HIH Series

OPTIONS


HIH-3610 Monolithic integrated circuit

The HIH-3610 humidity sensor is designed specifically for high volume OEM (Original Equipment Manufacturer) users. Direct input to a controller or other device is made possible by this sensor's linear voltage output. With a typical current draw of only 200 μ A, the HIH-3610 is ideally suited for low drain, battery powered systems. Tight sensor interchangeability reduces or eliminates OEM production calibration costs. Individual sensor calibration data is available.

The HIH-3610 delivers instrumentation quality RH sensing performance in a low cost, solderable SIP (Single In-line Package). Available in two lead spacing configurations, the RH sensor is a laser trimmed thermoset polymer capacitive sensing element with on-chip integrated signal conditioning.

Package style:

Solderable SIP



TERMINATION	NIST CERTIFICATION	REFERENCE
2.54 mm (0.100 in) Lead Pitch	None	HIH-3610-001
1.27 mm (0.050 in) Lead Pitch	None	HIH-3610-002
2.54 mm (0.100 in) Lead Pitch	NIST Calibration sensor-specific printout	HIH-3610-003
1.27 mm (0.050 in) Lead Pitch	NIST Calibration sensor-specific printout	HIH-3610-004

CAUTION

PRODUCT DAMAGE

The inherent design of this component causes it to be sensitive to the electrostatic discharge (ESD). To prevent ESD-induced damage and/or degradation, take normal ESD precautions when handling this product.

Failure to comply with these instructions could result in product damage

HIH-3602 Monolithic integrated circuit

HIH-3602-A and HIH-3602-C Relative Humidity (RH) sensors combine both relative humidity and temperature sensing in a TO-5 housing with a hydrophobic sintered stainless steel filter.

The temperature sensor is thermally connected with the RH sensor making the HIH-3602-A/C ideal for measuring dew point and other absolute moisture terms.

Package style:


TO-5 can

Termination:

0.46 mm (0.18 in)

NIST Certification:

NIST Calibration sensor-specific printout



INTERNAL PIN CONNECTIONS

0.46 mm [0.018 in] dia. lead gold plated (6 places)	
A, B	(HIH-3602-A) Thermistor for temperature compensation
A, B	(HIH-3602-C) RTD for temperature compensation
C	+VDC supply
D	(-) Power or ground
E	VDC out
F	Case ground

TEMPERATURE SENSOR

100 kOhm $\pm$ 5 % @ 25 °C, NTC 0-50 C
1000 Ohm $\pm$ 0.2 % @ 0 °C, platinum RTD

REFERENCE

HIH-3602-A
HIH-3602-C

HIH-3602-L Integrated circuit

The HIH-3602-L Relative Humidity (RH) sensor delivers instrumentation quality RH sensing performance in a rugged, low cost, slotted TO-39 housing.

On-board signal conditioning reduces product development times while a typical current draw of only 200 μ A makes the HIH-3602-L perfect for battery powered systems. This sensor should be shielded from bright light.

Package style:


TO-39 can

Termination:

0.46 mm (0.18 in)

NIST Certification:

None



INTERNAL PIN CONNECTIONS

0.46mm [0.018 in] dia. lead gold plated (6 places)	
A, B	No connection
C	+VDC supply
D	(-) Power or ground
E	VDC out
F	Case ground

REFERENCE

HIH-3602-L

Honeywell

www.honeywell.com/sensing

Temperature Sensors - RTDs



Honeywell's thin film RTD (Resistance Temperature Detector) temperature sensors feature two distinct series. These sensors are laser trimmed for accuracy and interchangeability. Linear outputs are stable and fast.

The TD Series Temperature Sensors are silicon-based RTDs. They offer 2000 Ohm nominal resistance at 20 °C. Temperature range of -40 °C to 150 °C.

The HEL Series Temperature Sensors are platinum RTDs, offering 100 Ohm or 1000 Ohm versions and temperature ranges of -200 °C to 540 °C.

HEL-700 Series 100/1000 Ohm platinum RTD

Supply voltage: 4 Vdc to 9 Vdc
Base resistance: 1000 ± 2 Ohm (± 0.2 %) @ 0 °C (Standard)
and interchangeability: 1000 ± 1 Ohm (± 0.1 %) @ 0 °C (Optional)


OPTIONS

HEL-700


Temperature range: -200 °C to 540 °C
-300 °F to 1000 °F

Packaging style/Termination: Radial chip/ribbon leads (Type A)
Radial chip/no leads (Type B)
SMT (Axial) flip chip/no leads (Type C)


Type A



Type B



Type C



100 Ohm (0.00385 Ohm/Ohm/°C DIN standard)

PACKAGING STYLE	BASE RESISTANCE AND INTERCHANGEABILITY	REFERENCE
Type A	Standard	HEL-700-T-0-A
Type A	Optional	HEL-700-T-1-A
Type B	Standard	HEL-700-T-0-B
Type B	Optional	HEL-700-T-1-B

1000 Ohm (0.00375 Ohm/Ohm/°C)

PACKAGING STYLE	BASE RESISTANCE AND INTERCHANGEABILITY	REFERENCE
Type A	Standard	HEL-700-U-0-A
Type A	Optional	HEL-700-U-1-A
Type B	Standard	HEL-700-U-0-B
Type B	Optional	HEL-700-U-1-B
Type C	Standard	HEL-700-U-0-C
Type C	Optional	HEL-700-U-1-C

CAUTION

PRODUCT DAMAGE


The inherent design of this component causes it to be sensitive to the electrostatic discharge (ESD). To prevent ESD-induced damage and/or degradation, take normal ESD precautions when handling this product.

Failure to comply with these instructions could result in product damage

HEL-700 Series 100/1000 Ohm platinum RTD (Continued)

HEL-705/707/711/712/716/717

Temperature range:	HEL-705/711/716	-200 °C to 260 °C -320 °F to 500 °F
	HEL-707/712/717	-75 °C to 540 °C -100 °F to 1000 °F
Packaging style:		Ceramic case
Termination:		12 in leadwires
NIST calibration:		None



100 Ohm (0.00385 Ohm/Ohm/°C DIN standard)

BASE RESISTANCE AND INTERCHANGEABILITY	REFERENCE
Standard	HEL-705-T-0-12-00
Optional	HEL-705-T-1-12-00
Standard	HEL-707-T-0-12-00
Optional	HEL-707-T-1-12-00
Standard	HEL-711-T-0-12-00
Optional	HEL-711-T-1-12-00
Standard	HEL-712-T-0-12-00
Optional	HEL-712-T-1-12-00
Standard	HEL-716-T-0-12-00
Optional	HEL-716-T-1-12-00
Standard	HEL-717-T-0-12-00
Optional	HEL-717-T-1-12-00

1000 Ohm (0.00375 Ohm/Ohm/°C)

BASE RESISTANCE AND INTERCHANGEABILITY	NIST CALIBRATION	REFERENCE
Standard		HEL-705-U-0-12-00
Optional		HEL-705-U-1-12-00
Standard		HEL-707-U-0-12-00
Optional		HEL-707-U-1-12-00
Standard		HEL-711-U-0-12-00
Optional		HEL-711-U-1-12-00
Standard		HEL-712-U-0-12-00
Optional		HEL-712-U-1-12-00
Standard		HEL-716-U-0-12-00
Optional		HEL-716-U-1-12-00
Optional	NIST @ 0 and 100 °C	HEL-716-U-1-12-C2
Standard		HEL-717-U-0-12-00
Optional		HEL-717-U-1-12-00


TD Series 2000 Ohm silicon RTD

Supply voltage:
Temperature range:

10 Vdc
-40 °C to 150 °C
-40 °F to 302 °F


OPTIONS

TD4A Liquid temperature sensor




PACKAGING STYLE	TERMINATION	REFERENCE
Threaded aluminium case	Leadwires	TD4A

TD5A Subminiature temperature sensor



PACKAGING STYLE	TERMINATION	REFERENCE
Plastic case	SIP	TD5A

Temperature Sensors - Thermistors



Thermistors change resistance with a change in temperature. They do not amplify, rectify, polarize or generate a signal. The thermistor temperature may be changed by the surrounding temperature or by self-heating the thermistor by passing a current through it.

Most applications such as temperature measurement and control or copper coil compensation require that the power dispersed in a thermistor be kept to a minimum so as not to perceptibly self-heat the thermistor. Other applications depend entirely on the self-heating effect. When the surrounding temperature is fixed, the resistance of a thermistor is largely a function of power being dispersed within it, raising its temperature above its environment. Under these operating conditions, the temperature may rise 100 °C to 200 °C [121 °F to 392 °F] and the resistance may be lowered to 1/1000th of its original value at low current.

This self-heating characteristic provides a whole field of uses for the thermistor. In the self-heat state it is thermally sensitive (its resistance will be changed) to any condition, changing the rate at which heat is conducted away from it. If the rate of heat removal is ideally fixed, then the thermistor is sensitive to power input and suited for use in voltage or power level control applications.

Glass Encapsulated Chip (GEC) Thermistors


The GECs are high-quality, hermetically-sealed, glass-encapsulated chip thermistors in an axial lead package. They cover the full temperature range of -60 °C to 300 °C [-76 °F to 572 °F]. These rugged sensors are designed for applications which demand reliability at low cost. The uniform dimensions are ideally suited for automated assembly.

Operating temperature:	-60 °C to 300 °C [-76 °F to 572 °F]
Encapsulation:	DO-35 glass
Lead material:	Tinned copper-clad steel
Dissipation constant (DC):	2.5 mW/°C in still air min.
Time constant (TC):	4 s in still air max.
Resistance range at 25 °C [77 °F]:	1 kOhm to 1 MOhm

OPTIONS

At 25 °C [77 °F]

OHM	% TOLERANCE	R/T CURVE	REFERENCE
1,000	10	10A	135-102DAG-J01
2,000	10	10	135-202FAG-J01
3,000	10	10	135-302FAG-J01
5,000	5	10	135-502FAF-J01
5,000	10	10	135-502FAG-J01
10,000	5	10	135-103FAF-J01
10,000	10	16	135-103FAG-J01
10,000	5	16	135-103LAF-J01
20,000	10	16	135-203LAG-J01
30,000	10	16	135-303KAG-J01
50,000	5	16	135-503LAF-J01
50,000	10	16	135-503LAG-J01
100,000	5	16	135-104LAF-J01
100,000	10	16	135-104LAG-J01
200,000	10	1	135-204QAG-J01
500,000	10	1	135-504QAG-J01
1 M	10	1	135-105QAG-J01



**Interchangeable R/T curve matched
±1 °C from 0 °C to 100 °C [32 °F to 212 °F]**

OHM	R/T CURVE	REFERENCE
10,000	16	135-103LFW-J01
20,000	16	135-203LFW-J01
30,000	16	135-303LFW-J01
50,000	16	135-503LFW-J01
100,000	16	135-104LFW-J01

Epoxy-coated or Uncoated Chip Thermistors

Epoxy-coated or Uncoated Chip thermistors are available in a broad range of custom resistance values and R/T curves. They are also available in two lead types:

- Uninsulated: 0,2032 mm [0.008 in] diameter, tinned copper for 1 kOhm or less, and tinned copper alloy for greater than 1 kOhm.
- Insulated: 0,254 mm [0.010 in] diameter, nickel wire, Teflon-insulated, 38,1 mm [1.5 in] long and furnished with 6,35 mm [0.25 in] stripped ends of 0,4064 mm [0.016 in] and 0,508 mm [0.020 in] tin-plated copper leads.

Operating temperature range: -40 °C to 125 °C* [-40 °F to 257 °F]*

Encapsulation: Epoxy-coated or uncoated

Lead material:

- Uninsulated: tinned copper/copper alloy
- Insulated: tinned copper/copper alloy with nickel wire Teflon

Dissipation constant (DC): 0.75 mW/°C in still air min.


Time constant (TC): 15 s in still air max.

Resistance range at 25 °C [77 °F]: 100 Ohm to 100 kOhm

*Very accurate (± 0.2 °C) when used between 0 °C to 70 °C [32 °F to 158 °F]. Other ranges and tolerances are available.

OPTIONS

Epoxy-coated chip




10 % Tolerance at 25 °C [77 °F], uninsulated leads

OHM	R/T CURVE	REFERENCE
100	17	197-101CAG-A01
300	17	197-301CAG-A01
500	10A	197-501DAG-A01
1,000	10A	197-102DAG-A01
2,000	16	197-202LAG-A01
3,000	16	197-302LAG-A01
5,000	16	197-502LAG-A01
10,000	16	197-103LAG-A01
20,000	16	197-203LAG-A01
30,000	18	197-303KAG-A01
50,000	1	197-503QAG-A01
100,000	1	197-104QAG-A01

10 % Tolerance at 25 °C [77 °F], insulated leads

OHM	R/T CURVE	REFERENCE
100	17	199-101CAG-A01
300	17	199-301CAG-A01
500	10A	199-501DAG-A01
1,000	10A	199-102DAG-A01
2,000	16	199-202LAG-A01
3,000	16	199-302LAG-A01
5,000	16	199-502LAG-A01
10,000	16	199-103LAG-A01
20,000	16	199-203LAG-A01
30,000	18	199-303KAG-A01
50,000	1	199-503QAG-A01
100,000	1	199-104QAG-A01

Uncoated chip



10 % Tolerance at 25 °C [77 °F], uninsulated leads

OHM	R/T CURVE	REFERENCE
100	17	195-101CAG-A01
300	17	195-301CAG-A01
500	10A	195-501DAG-A01
1,000	10A	195-102DAG-A01
2,000	16	195-202LAG-A01
3,000	16	195-302LAG-A01
5,000	16	195-502LAG-A01
10,000	16	195-103LAG-A01
20,000	16	195-203LAG-A01
30,000	18	195-303KAG-A01
50,000	1	195-503QAG-A01
100,000	1	195-104QAG-A01

10 % Tolerance at 25 °C [77 °F], insulated leads

OHM	R/T CURVE	REFERENCE
100	17	198-101CAG-A01
300	17	198-301CAG-A01
500	10A	198-501DAG-A01
1,000	10A	198-102DAG-A01
2,000	16	198-202LAG-A01
3,000	16	198-302LAG-A01
5,000	16	198-502LAG-A01
10,000	16	198-103LAG-A01
20,000	16	198-203LAG-A01
30,000	18	198-303KAG-A01
50,000	1	198-503QAG-A01
100,000	1	198-104QAG-A01

UNI-CURVE Interchangeable Thermistors

The UNI-CURVE Interchangeable thermistors are temperature-matched. They offer additional cost savings by eliminating the need for individual resistance temperature calibration, as well as standardization of circuit components and simplification of design and replacement problems.

Operating temperature range: -40 °C to 150 °C* [-40 °F to 302 °F]*

Encapsulation: Epoxy-coated


Lead material: Tinned copper alloy

Dissipation constant (DC): 0.75 mW/°C in still air min.

Time constant (TC): 15 s in still air max.

Resistance range at 25 °C [77 °F]: 1 kOhm to 100 kOhm

*Very accurate (± 0.2 °C) when used between 0 °C to 70 °C [32 °F to 158 °F]. Other ranges and tolerances are available.



OPTIONS

$\pm 0,2$ °C Tolerance at 25 °C [77 °F]

0 °C to 70 °C [32 °F to 158 °F]

OHM	R/T CURVE	REFERENCE
1,000	10A	192-102DET-A01
2,252	16	192-222LET-A01
3,000	16	192-302LET-A01
5,000	16	192-502LET-A01
10,000	16	192-103LET-A01
30,000	18	192-303KET-A01
30,000	1	192-303QET-A01
50,000	1	192-503QET-A01
100,000	1	192-104QET-A01

$\pm 0,5$ °C Tolerance at 25 °C [77 °F]

0 °C to 70 °C [32 °F to 158 °F]

OHM	R/T CURVE	REFERENCE
1,000	10A	192-102DEV-A01
2,252	16	192-222LEV-A01
3,000	16	192-302LEV-A01
5,000	16	192-502LEV-A01
10,000	16	192-103LEV-A01
30,000	18	192-303KEV-A01
30,000	1	192-303QEV-A01
50,000	1	192-503QEV-A01
100,000	1	192-104QEV-A01

$\pm 1,0$ °C Tolerance at 25 °C [77 °F]

0 °C to 70 °C [32 °F to 158 °F]

OHM	R/T CURVE	REFERENCE
1,000	10A	192-102DEW-A01
2,252	16	192-222LEW-A01
3,000	16	192-302LEW-A01
5,000	16	192-502LEW-A01
10,000	16	192-103LEW-A01
30,000	18	192-303KEW-A01
30,000	1	192-303QEW-A01
50,000	1	192-503QEW-A01
100,000	1	192-104QEW-A01

Disc Thermistors

Uncoated or epoxy-coated Disc thermistors are available in a broad range of custom resistance values and R/T curves. They are only available with uninsulated leads. Diameters range from 2,54 mm [0.1 in] to 10,16 mm [0.4 in]. They are ideally suited for low cost applications with a maximum temperature of 150 °C [302 °F]. They are also well suited for PC board mount and are available on tape and reel.

Operating temperature range: -60 °C to 150 °C [-76 °F to 302 °F]

Encapsulation: Epoxy-coated or uncoated

Lead material: Uninsulated: tinned copper/copper alloy

Dissipation constant (DC): Varies with size,

ranges from 3 mW/°C to 8 mW/°C


Time constant (TC): Varies with size,

ranges from 10 s to 32 s

Resistance range at 25 °C [77 °F]: 100 Ohm to 100 kOhm

OPTIONS

Epoxy-coated chip



10 % Tolerance at 25 °C [77 °F]

Lead diameter 0,4064 mm [0.016 in]

Lead spacing 2,54 mm [0.1 in]

OHM	R/T CURVE	DC MIN.	TC MAX.	REFERENCE
500	10	3	10	140-501FAG-RB1
1,000	10	4	10	140-102FAG-RB1
3,000	16	3	10	140-302LAG-RB1
5,000	16	4	10	140-502LAG-RB1
10,000	16	4	10	140-103LAG-RB1
50,000	1	3	10	140-503QAG-RB1
100,000	1	3	10	140-104QAG-RB1


10 % Tolerance at 25 °C [77 °F]

Lead diameter 0,508 mm [0.020 in]

Lead spacing 5,08 mm [0.2 in]

OHM	R/T CURVE	DC MIN.	TC MAX.	REFERENCE
100	10	4	16	143-101FAG-RC1
200	10	5	18	143-201FAG-RC1
300	10	6	20	143-501FAG-RC1
1,000	16	6	20	143-102LAG-RC1
3,000	16	6	22	143-302LAG-RC1
5,000	16	7	35	143-502LAG-RC1
10,000	1	4	20	143-103QAG-RC1
30,000	1	6	25	143-303QAG-RC1
50,000	1	7	30	143-503QAG-RC1

Uncoated chip



10 % Tolerance at 25 °C [77 °F]

Lead diameter 0,4064 mm [0.016 in]

Lead spacing 2,54 mm [0.1 in]

OHM	R/T CURVE	DC MIN.	TC MAX.	REFERENCE
500	10	3	10	142-501FAG-RB1
1,000	10	4	10	142-102FAG-RB1
3,000	16	3	10	142-302LAG-RB1
5,000	16	4	10	142-502LAG-RB1
10,000	16	4	10	142-103LAG-RB1
50,000	1	3	10	142-503QAG-RB1
100,000	1	3	10	142-104QAG-RB1

10 % Tolerance at 25 °C [77 °F]

Lead diameter 0,508 mm [0.020 in]

Lead spacing 5,08 mm [0.2 in]

OHM	R/T CURVE	DC MIN.	TC MAX.	REFERENCE
100	10	4	16	145-101FAG-RC1
200	10	5	18	145-201FAG-RC1
300	10	6	20	145-301FAG-RC1
500	10	6	25	145-501FAG-RC1
1,000	16	6	20	145-102LAG-RC1
3,000	16	6	22	145-302LAG-RC1
5,000	16	7	35	145-502LAG-RC1
10,000	1	4	20	145-103QAG-RC1
30,000	1	7	28	145-303QAG-RC1
50,000	1	8	32	145-503QAG-RC1

Standard Bead Thermistors

Standard Bead thermistors are hermetically-sealed in glass. These small units provide maximum stability when used to 300 °C [572 °F] for high temperature design requirements. They are ideally suited for the most stringent military, aerospace and oceanographic applications.

Operating temperature range: -60 °C to 300 °C [-76 °F to 572 °F]

Encapsulation: Glass hermetic seal

Lead material: Platinum iridium


Dissipation constant (DC): 0.4 mW/°C in still air min.

Time constant (TC): 4 s in still air max.

Resistance range at 25 °C [77 °F]: 200 Ohm to 1 MOhm

OPTIONS


Adjacent leads



20 % Tolerance at 25 °C [77 °F]

OHM	R/T CURVE	RATIO 0 °C/50 °C	REFERENCE
200	8	4.80	112-201BAJ-B01
1,000	11	7.04	112-102EAJ-B01
2,000	11	7.04	112-202EAJ-B01
5,000	11	7.04	112-502EAJ-B01
10,000	12	7.59	112-103FAJ-B01
20,000	13	9.11	112-203HAJ-B01
50,000	14	9.53	112-503JAJ-B01
100,000	15	10.45	112-104KAJ-B01
200,000	15	10.45	112-204KAJ-B01
500,000	4	11.78	112-504NAJ-B01
1 M	5	13.12	112-105PAJ-B01

Axial leads



20 % Tolerance at 25 °C [77 °F]

OHM	R/T CURVE	RATIO 0 °C/50 °C	REFERENCE
2,000	11	7.04	112-202EAJ-H01
5,000	11	7.04	112-502EAJ-H01
10,000	12	7.59	112-103FAJ-H01
100,000	15	10.45	112-104KAJ-H01
600,000	4	11.78	112-604NAJ-H01


Small Bead Thermistors

Small Bead thermistors feature relatively uniform size, offer ultra-fast time response and are highly sensitive to electric power. They are ideally suited for use in low heat capacity applications and their micro size makes them perfect for use in extremely small assemblies such as catheters and hypodermic needles. They are also used in self-heat applications such as gas analysis, gas flow measurement and thermal conductivity analysis.

Operating temperature range: -60 °C to 300 °C [-76 °F to 572 °F]
Encapsulation: Glass hermetic seal
Lead material: Platinum iridium
Dissipation constant (DC): 0.1 mW/°C in still air min.
Time constant (TC): 1 s in still air max.
Resistance range at 25 °C [77 °F]: 2 kOhm to 100 kOhm

OPTIONS


Adjacent leads



At 25 °C [77 °F]

OHM	% TOLERANCE	R/T CURVE	RATIO 0 °C/50 °C [32 °F/122 °F]	REFERENCE
2,000	25	9	5.50	111-202CAK-B01
8,000	20	11	7.04	111-802EAJ-B01
30,000	25	11	7.04	111-303EAK-B01

Axial leads



At 25 °C [77 °F]

OHM	% TOLERANCE	R/T CURVE	RATIO 0 °C/50 °C [32 °F/122 °F]	REFERENCE
2,000	25	9	5.50	111-202CAK-H01
8,000	20	11	7.04	111-802EAJ-H01
10,000	20	11	7.04	111-103EAJ-H01
100,000	25	13	9.11	111-104HAK-H01


Glass Probe Thermistors

Glass Probe thermistors are shock resistant, rugged, glass-encapsulated units that are ideally suited for immersion in fluid and convenient for mounting in air sensor assemblies. They are available in two configurations: standard and mini.

Operating temperature range: -60 °F to 300 °C [-72 °F to 572 °F]
Encapsulation: Glass
Lead material: Dumet (copper-clad Ni-Fe wire)
Dissipation constant (DC): • Standard: 1.0 mW/°C in still air min.
 • Mini: 0.7 mW/°C in still air min.
Time constant (TC): • Standard: 22 s in still air max.
 • Mini: 10 s in still air max.
Resistance range at 25 °C [77 °F]: 1 kOhm to 10 MOhm

OPTIONS

Standard




20 % Tolerance at 25 °C [77 °F]

dc 1.0 mW/°C min., TC 22 s max.

OHM	R/T CURVE	RATIO	REFERENCE
1,000	11	7.04	121-102EAJ-Q01
2,000	11	7.04	121-202EAJ-Q01
5,000	11	7.04	121-502EAJ-Q01
10,000	12	7.59	121-103FAJ-Q01
50,000	14	9.53	121-502JAJ-Q01
100,000	15	10.45	121-104KAJ-Q01
200,000	15	10.45	121-202KAJ-Q01
500,000	4	11.89	121-504NAJ-Q01
1 M	5	13.12	121-105PAJ-Q01
10 M	6	15.65	121-106QAJ-Q01

Mini



20 % Tolerance at 25 °C [77 °F]


dc 0.7 mW/°C min., TC 10 s max.

OHM	R/T CURVE	RATIO	REFERENCE
1,000	11	7.04	120-102EAJ-Q01
2,000	11	7.04	120-202EAJ-Q01
10,000	12	7.59	120-103FAJ-Q01
50,000	14	9.53	120-502JAJ-Q01
100,000	15	10.45	120-104KAJ-Q01

E-I Matched Bead Thermistors

E-I Matched Bead thermistors are designed for use in gas chromatography and other thermal conductivity gas analysis instruments. Each bead is mounted to a special hermetically-sealed header. For maximum sensitivity, the higher resistance units should be used at higher ambient temperatures.

Operating temperature range: -60 °C to 300 °C [-76 °F to 572 °F]
Encapsulation: Glass hermetic seal
Lead material: Tinned Ni-Fe



OPTIONS

Helium-matched assembly

Characteristics	115-802EDJ-801
Resistance at 25 °C [77 °F]	8000 Ohm ±25 %
Resistance at 0 °C [32 °F] (approx.)	23,200 Ohm
Resistance at 50 °C [122 °F] (approx.)	3,200 Ohm
Ratio of resistance 0 °C/50 °C	6.56 to 7.99
Beta nominal at 25 °C	3495 K
Temperature coefficient at 25 °C	-3.9 %/°C
Time constant (TC) still air max.	1 s
Dissipation constant (DC) still air min.	0.16 mW/°C
DC helium	0.5 mW/°C
Power rating (air)	45 mW
Power rating (helium)	140 mW
Max. ambient temperature	250 °C [482 °F]
Max. operating temperature (including self-heat)	300 °C [572 °F]
Resistance at max. operating temperature	25 Ohm

2 % resistance at 25 °C [77 °F]

DESCRIPTION	REFERENCE
Two 111-802EAJ-H01 each mounted on a glass hermetic seal and matched in helium to within 30 mV, 25 mV and 20 mV of each other at 2 mA, 5 mA, 10 mA and 15 mA.	115-802EDJ-801

Air-matched assembly

Characteristics	115-202CDK-801
Resistance at 25 °C [77 °F]	2000 Ohm ±25 %
Resistance at 0 °C [32 °F] (approx.)	4900 Ohm
Resistance at 50 °C [122 °F] (approx.)	890 Ohm
Ratio of resistance 0 °C/50 °C	4.95 to 6.95
Beta nominal at 25 °C	3000 K
Temperature coefficient at 25 °C	-3.4 %/°C
Time constant (TC) still air max.	1 s
Dissipation constant (DC) still air min.	0.16 mW/°C
DC helium	0.5 mW/°C
Power rating (air)	15 mW
Power rating (helium)	60 mW
Max. ambient temperature	100 °C [212 °F]
Max. operating temperature (including self-heat)	150 °C [302 °F]
Resistance at max. operating temperature	88 Ohm


5 % resistance at 25 °C [77 °F]

DESCRIPTION	REFERENCE
Two 111-202CAK-H01 each mounted on a glass hermetic seal and matched in air to within 15 mV of each other at 5 mA, 10 mA and 15 mA.	115-202CDK-801

ICL Inrush Current Limiter Thermistors

ICL Inrush Current Limiter thermistors are a cost-effective way of limiting the inrush of current that may damage components in a switching power supply and in other power devices when the equipment is turned on. These devices have solderable leads and are PC board mountable.

Operating temperature range: -40 °C to 185 °C [-40 °F to 365 °F]
Maximum steady state current: 1 A to 30 A
Encapsulation: Black silicone
Lead material: Tinned copper
Dissipation constant (DC): 12.7 mW/°C to 23 mW/°C
Time constant (TC): 32 s to 93 s
Resistance range at 25 °C [77 °F]: 0.5 Ohm to 220 Ohm ±20 %
Resistance at max. steady state current: 0.01 Ohm to 2.34 Ohm
Max. diameter 9.5 mm [0.374 in] to 32.0 mm [1.260 in]
Max. thickness 5.0 mm [0.204 in] to 8.0 mm [0.327 in]
Lead diameter 0.8 mm [0.032 in] to 1.0 mm [0.040 in]



OHM	MAX. STEADY STATE CURRENT (A)	RESISTANCE AT MAX. STEADY STATE CURRENT (OHM)	REFERENCE
0.5	30	0.01	ICL320R530-01
1	20	0.02	ICL221R020-01
1	30	0.02	ICL321R030-01
2	18	0.03	ICL222R018-01
2.5	8	0.07	ICL152R508-01
2.5	8	0.06	ICL122R508-01
2.5	15	0.03	ICL222R515-01
5	6	0.1	ICL155R006-01
5	7	0.07	ICL155R007-01
10	2	0.3	ICL1010002-01
10	3.2	0.18	ICL1010004-01
10	5	0.13	ICL1210005-01
10	6	0.15	ICL1510006-01
10	8	0.1	ICL2210008-01
12	4	0.26	ICL1512004-01
16	4	0.27	ICL1516004-01
20	2	0.5	ICL1220002-01
40	2	0.6	ICL1240002-01
50	2	0.72	ICL1250002-01
80	2.5	0.75	ICL1580003-01
120	3	0.9	ICL2212103-01
220	2	0.8	ICL1522102-01

Temperature Sensors - Probes




Temperature Sensor Probes are finished thermistor assemblies complete with thermistor housing, extension leads and sometimes a connector. A variety of customized packages are available.

NOTE: The products in this section do not follow the "how to use this catalogue" instructions provided in the catalogue introduction. Specific reference numbers are not given due to their custom nature. Please contact your local Honeywell sales office for ordering information.

ES120 Series Coolant/Oil Temperature Sensor Probes

The ES120 probe is a thermistor mounted into a plastic lead frame and assembled into a metal body. This subassembly is then overmolded to produce both the electrical connection system and the hexagonal shape for easy installation. The all-plastic design reduces heat loss through the sensor, thereby reducing wind chill effects.

Operating temperature range: -40 °C to 155 °C [-40 °F to 311 °F]
Encapsulation: NTC (Negative Temperature Coefficient) encapsulated in thermal epoxy
Lead material: Terminals are 2,8 mm x 0,8 mm [0.11 in x 0.03 in] brass with a copper flash protection layer with final plating to customer requirement (silver, tin, gold, etc.)
Dissipation constant: Tor values (time to reach 63.2 % of the difference between two temperatures) are typically 19 s rising temperature and 14 s falling temperature
Time constant: None
Resistance range at 25 °C [77 °F] 2.5 kOhm at 20 °C [68 °F] ±5 %




SERIES NAME
ES120 Coolant/Oil Temperature Sensor Probe

ES110 Series Inlet Air Temperature Sensor Probes

The ES110 probe is a thermistor mounted into a plastic lead frame and assembled into a metal body. This subassembly is then overmolded to produce both the electrical connection system and the hexagonal shape for easy installation. Two end configurations are available depending upon response required or degree of protection. The all-plastic design reduces heat loss through the sensor, thereby reducing wind chill effects.

Operating temperature range: -40 °C to 155 °C [-40 °F to 311 °F]
Encapsulation: Standard NTC (Negative Temperature Coefficient) epoxy protection
Lead material: Terminals are 2,8 mm x 0,8 mm [0.11 in x 0.03 in] brass with a copper flash protection layer with final plating to customer requirement (silver, tin, gold, etc.)
Dissipation constant: 0.85 mW/°C in still air at 25 °C [77 °F]
Time constant: 1 s in liquids, 12 s max. in still air
Resistance range at 25 °C [77 °F] 2.5 kOhm at 20 °C [68 °F] ±5 %




SERIES NAME
ES110 Inlet Air Temperature Sensor Probe

Air Conditioning Temperature Sensor Probes

A fully overmolded and protected sensor incorporating a specially developed NTC (Negative Temperature Coefficient) to withstand very aggressive, damp operating conditions. The housing is snap fit for easy assembly.

Operating temperature range: -30 °C to 100 °C [-22 °F to 212 °F]
Encapsulation: Special NTC epoxy coating
Lead material: Terminals are 2,8 mm x 0,8 mm [0.11 in x 0.03 in] brass with a copper flash protection layer with final plating to customer requirement (silver, tin, gold, etc.)
Dissipation constant: 2.5 mW/°C in still air
Time constant: 2 s in water, 15 s max. in still air
Resistance range at 25 °C [77 °F] 9 kOhm at 0 °C [32 °F] ±1.5 %




NAME
Air Conditioning Temperature Sensor Probe

Earth Return (Ground) Temperature Sensor Probes

An all-metal temperature sensor, with the body being the ground, incorporating a flat disc thermistor held flush on the base of the body by a spring-loaded pressure pad. This sensor provides a quick response to small variations in high temperature changes.

Operating Temperature Range: -40 °C to 155 °C [-40 °F to 311 °F]
Encapsulation: NTC (negative temperature coefficient) encapsulated in a silicone paste
Lead Material: Standard Lucar type or other variations
Dissipation Constant: 3 mW/°C in still air
Time Constant: 10 s in automotive coolant
Resistance Range at 25 °C [77 °F] Per customer requirements




NAME
Earth Return (Ground) Temperature Sensor Probe

Refrigerant Temperature Sensor Probes

A fully sealed, quick response temperature sensor suitable for use in HVAC systems.

Operating temperature range: -40 °C to 140 °C [-40 °F to 284 °F]
Encapsulation: NTC (Negative Temperature Coefficient) encapsulated in a thermal heat paste
Lead material: Terminals are 1,5 mm x 0,6 mm [0.06 in x 0.02 in] brass with a copper flash protection layer with final plating to customer requirement (silver, tin, gold, etc.)
Dissipation constant: Tor values (time to reach 63.2 % of the difference between two temperatures) are typically 10 s rising temperature and 6 s falling temperature
Time constant: None
Resistance range at 25 °C [77 °F] 2.5 kOhm at 20 °C [68 °F], calibrated at ±3 % at 100 °C [212 °F]




NAME
Refrigerant Temperature Sensor Probe

Surface Temperature Sensor Probes

Sensor assembly is designed to have good heat conductivity between the thermistor element and the area to be monitored. Time response is consistent with the thermal conductivity of the surface being measured. Multiple configurations allow sensor to be mounted, bolted, riveted or attached adhesively.

Operating temperature range: -60 °C to 150 °C [-76 °F to 302 °F]
Encapsulation: Thermally conductive epoxy used to pot discrete component into surface-style housing
Lead material: Insulated lead wires and terminals when required, other options available
Dissipation constant: 3.3 mW/°C to 12 mW/°C (varies with size and housing style)
Time constant: 1 s to 40 s (application dependent)
Resistance range at 25 °C [77 °F] Per customer requirements




NAME
Surface Temperature Sensor Probe

Air/Gas Temperature Sensor Probes

Air/Gas probes contain an exposed thermistor element because gas is not as good a heat conductor or thermal sink as a liquid, and because time response is normally an important consideration. The sensor housing may be composed of plastic or other thermally conductive materials to reduce conduction and heat from the gas circulating around the thermistor. Multiple configurations allow easy mounting.

- Operating temperature range: -60 °C to 150 °C [-76 °F to 302 °F]
- Encapsulation: None, sensing element is exposed
- Lead material: Insulated lead wires and terminals when required, other options available
- Dissipation constant: 0.1 mW/°C to 3 mW/°C (design specific)
- Time constant: 4 s to 150 s (application and design dependent)
- Resistance range at 25 °C [77 °F]: Per customer requirements




NAME
Air/Gas Temperature Sensor Probe

Immersion Temperature Sensor Probes

Custom designed and application specific, immersion probes are designed to be directly placed in the liquid medium to be measured. A large variety of housing alloys are available. Multiple configurations allow easy mounting.

- Operating temperature range: -60 °C to 300 °C [-76 °F to 572 °F]
- Encapsulation: NTC (Negative Temperature Coefficient) encapsulated in housing appropriate to the application
- Lead material: Insulated lead wires and terminals when required, other options available
- Dissipation constant: 5 mW/°C to 10 mW/°C (varies with size and housing style)
- Time constant: 1 s to 12 s (design dependent)
- Resistance range at 25 °C [77 °F]: Per customer requirements



NAME
Immersion Temperature Sensor Probe

Thermostats - Commercial



Commercial thermostats include products for use in a wide array of small and major appliances, automotive applications, office copy machines, heat and smoke detectors and HVAC equipment. These snap-action thermostats include automatic or manual reset options, phenolic or ceramic housings, and a variety of mounting brackets and terminal options.


NOTE: The products in this section do not follow the "how to use this catalogue" instructions provided in the catalogue introduction. Specific reference numbers are not given due to their custom nature. Please contact your local Honeywell sales office for ordering information.

2450R/2450HR/2455R Series Phenolic Automatic Reset Thermostats

A temperature-sensitive bimetal disc, electrically isolated from the switch, actuates the normally closed contacts. The contacts open when the surface or ambient temperatures increase to the operating snap point of the calibrated disc. Response to temperature changes is extremely rapid due to the inherently low mass of the disc and the small size of the product. These products are factory calibrated to the customer's specification.

Reset type:	Automatic
Amperage capacity:	15 A resistive max.
Housing material:	Phenolic
Operating temperature range:	0 °C to 150 °C [32 °F to 302 °F]
Environmental exposure range:	0 °C to 177 °C [32 °F to 350 °F]

2450HR




SERIES NAME
2450HR Phenolic Automatic Reset Thermostat

2450R



SERIES NAME
2450R Phenolic Automatic Reset Thermostat

2455R




SERIES NAME
2455R Phenolic Automatic Reset Thermostat

2450RC/2450RCH/2455RC Series Ceramic Automatic Reset Thermostats

A temperature-sensitive bimetal disc, electrically isolated from the switch, actuates the normally closed contacts. The contacts open when the surface or ambient temperatures increase to the operating snap point of the calibrated disc. Response to temperature changes is extremely rapid due to the inherently low mass of the disc and the small size of the product.


Reset type:	Automatic
Amperage capacity:	15 A resistive max.
Housing material:	Ceramic
Operating temperature range:	0 °C to 260 °C [32 °F to 500 °F]
Environmental exposure range:	-20 °C to 287 °C [0 °F to 550 °F]

2450RC




SERIES NAME
2450RC Ceramic Automatic Reset Thermostat

2450RCH



SERIES NAME
2450RCH Ceramic Automatic Reset Thermostat

2455RC




SERIES NAME
2455RC Ceramic Automatic Reset Thermostat

2450CM/2455RM Series Ceramic and Phenolic Manual Reset Thermostats

A temperature-sensitive bimetal disc, electrically isolated from the switch, actuates the normally closed contacts. The contacts open when the surface or ambient temperatures increase to the operating snap point of the calibrated disc. The circuit will stay open above room ambient temperature until the manual reset button is pressed. Response to temperature changes is extremely rapid due to the inherently low mass of the disc and the small size of the product.


Reset type:	Manual
Amperage capacity:	15 A resistive max.
Housing material:	Ceramic or phenolic
Operating temperature range:	52 °C to 232 °C [125 °F to 450 °F] (ceramic) 52 °C to 150 °C [125 °F to 302 °F] (phenolic)
Environmental exposure range:	10 °C to 260 °C [50 °F to 500 °F] (ceramic) 10 °C to 177 °C [50 °F to 350 °F] (phenolic)

2450CM



SERIES NAME
2450CM Ceramic Manual Reset Thermostat

2455RM




SERIES NAME
2455RM Phenolic Manual Reset Thermostat

2450A/2455A Series Heat Detection Thermostats

The gold contacts open or close on a temperature rise of 47 °C to 107 °C [117 °F to 225 °F].


Reset type: Automatic
Amperage capacity: 15 A resistive max.
Housing material: Phenolic, epoxy-sealed cap and terminal
Operating temperature range: 47 °C to 107 °C [117 °F to 225 °F]
Environmental exposure range: 0 °C to 150 °C [32 °F to 302 °F]

2450A



SERIES NAME
 2450A Heat Detection Thermostat

2455A




SERIES NAME
 2455A Heat Detection Thermostat

2455RBV Series Overmolded Automatic Reset Thermostats

A temperature-sensitive bimetal disc, electrically isolated from the switch, actuates the normally closed contacts. The contacts open when the surface or ambient temperatures increase to the operating snap point of the calibrated disc. Response to temperature changes is extremely rapid due to the inherently low mass of the disc and the small size of the product.

Reset type: Automatic
Amperage capacity: 15 A resistive max.
Housing material: Ceramic or phenolic, epoxy overmold
Operating temperature range: -12 °C to 105 °C [10 °F to 221 °F]
Environmental exposure range: -18 °C to 121 °C [0 °F to 250 °F]

2455RBV




SERIES NAME
 2455RBV Overmolded Automatic Reset Thermostat

2450R/2450RCH/2455R/2455RC Series "One-shot" ½ in Thermostats

Products are designed for high limit applications where automatic reset is not desired.


Reset type: None
Amperage capacity: 15 A resistive max.
Housing material: ceramic or phenolic
Operating temperature range: 52 °C to 260 °C [125 °F to 500 °F] (ceramic)
 52 °C to 150 °C [125 °F to 302 °F] (phenolic)
Environmental exposure range: 18 °C to 316 °C [0 °F to 600 °F] (ceramic)
 18 °C to 177 °C [0 °F to 350 °F] (phenolic)

2450R




SERIES NAME
 2450R Phenolic "One-shot" ½ in Thermostat

2450RCH




SERIES NAME
 2450RCH Ceramic "One-shot" ½ in Thermostat

2455R



SERIES NAME
 2455R Phenolic "One-shot" ½ in Thermostat

2455RC




SERIES NAME
 2455RC Ceramic "One-shot" ½ in Thermostat

2450R Series Annular Ring Cap Automatic Reset Thermostats

A temperature-sensitive bimetal disc, electrically isolated from the switch, actuates the normally closed contacts. The contacts open when the surface or ambient temperatures increase to the operating snap point of the calibrated disc. Response to temperature changes is extremely rapid due to the inherently low mass of the disc and the small size of the product.

Reset type:	Automatic
Amperage capacity:	15 A resistive, 12 Vdc
Housing material:	Phenolic, can be partially or totally sealed against water ingress
Operating temperature range:	-10 °C to 55 °C [14 °F to 131 °F]
Environmental exposure range:	-40 °C to 130 °C [-40 °F to 266 °F]
Life Cycle Capability:	300 K at 12 Vdc, 10 A
Low Temperature Differential:	Down to 8 °C [46 °F]
Switch Temperature Tolerance:	±3 °C




SERIES NAME

2450R Phenolic Annular Ring Cap Automatic Reset Thermostat

2450R/2455R Series Protected Thermostats

A temperature-sensitive bimetal disc, electrically isolated from the switch, actuates the normally closed contacts. The contacts open when the surface or ambient temperatures increase to the operating snap point of the calibrated disc. Basic thermostat is protected from the environment by sealing it in a metal housing or encapsulating it in epoxy.

Reset type:	Automatic
Amperage capacity:	15 A resistive, 12 Vdc
Housing material:	Brass, aluminium, stainless steel and epoxy
Operating temperature range:	15 °C to 130 °C [59 °F to 266 °F]
Environmental exposure range:	-40 °C to 155 °C [-40 °F to 311 °F]




SERIES NAME

2450R Protected Thermostat
2455R Protected Thermostat

2450R Series Fully Sealed Thermostats

A temperature-sensitive bimetal disc, electrically isolated from the switch, actuates the normally closed contacts. The contacts open when the surface or ambient temperatures increase to the operating snap point of the calibrated disc. Response to temperature changes is extremely rapid due to the inherently low mass of the disc and the small size of the product.

Reset type:	Automatic
Amperage capacity:	15 A resistive, 12 Vdc
Housing material:	Phenolic housing, aluminium cap totally encapsulated in water resistant epoxy
Operating temperature range:	-10 °C to 55 °C [14 °F to 131 °F]
Environmental exposure range:	-40 °C to 130 °C [-40 °F to 266 °F]
Life cycle capability:	300 K at 12 Vdc, 10 A
Low temperature differential:	Down to 8 °C [46 °F]
Switch temperature tolerance:	±3 °C



SERIES NAME

2450R Fully Sealed Thermostat

Thermostats - Precision




Precision snap-action thermostats include both hermetic and non-hermetic devices for use in a wide array of applications including computers, copy machines, aircraft, radar equipment, medical equipment and electronic control systems. We also offer custom-packaged thermostats for application flexibility and industrial-grade thermostats designed to operate in extreme environmental conditions.

NOTE: The products in this section do not follow the "how to use this catalogue" instructions provided in the catalogue introduction. Specific reference numbers are not given due to their custom nature. Please contact your local Honeywell sales office for ordering information.

3100/3106 Series Hermetic Thermostats

The 3100/3106 Series is a single pole, single throw switch activated by a snap-action bimetal disc. Temperature calibrations are pre-set at the factory and each unit is 100 % thermally and mechanically inspected. It is available to open or close on temperature rise. The case is laser welded to form a hermetically-sealed steel housing with a glass-to-metal seal at the terminal junction. It is manufactured and tested to meet or exceed critical commercial and industrial specifications. The 3106 Series has gold alloy contacts for low voltage applications.

Amperage:	0.5 A resistive (3106 Series) 7 A resistive (3100 Series)
Housing material:	Steel housing with glass-to-metal seal at terminal junction
Operating temperature range:	-29 °C to 260 °C [-20 °F to 500 °F] (3100 Series) -29 °C to 204 °C [-20 °F to 400 °F] (3106 Series)
Environmental exposure range:	-62 °C to 288 °C [-80 °F to 550 °F]
Dielectric strength:	MIL-STD-202, Method 301 1250 Vac 60 Hz terminal to case (3100, 3100U, 3106 Series) 1500 Vac 60 Hz terminal to case (3100UX Series)
Insulation resistance:	MIL-STD-202, Method 302, Condition B 50 MOhm, 500 Vdc applied
Contact resistance:	MIL-STD-202, Method 307 25 mOhm (3106 Series) 50 mOhm (3100 Series)
Hermetic seal:	MIL-STD-202, Method 112, Condition A 1x10 ⁻⁵ atm cc/s
Moisture resistance:	MIL-STD-202 Method 106




SERIES NAME

3100 Hermetic Thermostat
3100U Hermetic Thermostat
3100UX Hermetic Thermostat
3106 Hermetic Thermostat

3150/3156 Series Low Silhouette Hermetic Thermostats

The 3150/3156 Series is a single pole, single throw switch activated by a snap-action bimetal disc. Temperature calibrations are pre-set at the factory and each unit is 100% thermally and mechanically inspected. It is available to open or close on temperature rise. The case is laser welded to form a hermetically-sealed steel housing with a glass-to-metal seal at the terminal junction. The low silhouette and compact design make it especially well suited for applications that require miniaturization. The 3156 Series has gold alloy contacts for low voltage applications.

Amperage:	0.5 A resistive (3156 Series) 7 A resistive (3150 Series)
Housing material:	Steel housing with glass-to-metal seal at terminal junction
Operating temperature range:	-29 °C to 177 °C [-20 °F to 350 °F]
Environmental exposure range:	-62 °C to 260 °C [-80 °F to 500 °F]
Dielectric strength:	MIL-STD-202, Method 301 750 Vac 60 Hz terminal to case (3150, 3156 Series) 1250 Vac 60 Hz terminal to case (3150U, 3156U Series) 1500 Vac 60 Hz terminal to case (3150UX Series)
Insulation resistance:	MIL-STD-202, Method 302, Condition B 50 MOhm, 500 Vdc applied
Contact resistance:	MIL-STD-202, Method 307 25 mOhm (3156 Series) 50 mOhm (3150 Series)
Hermetic seal:	MIL-STD-202, Method 112, Condition A 1x10 ⁻⁵ atm cc/s
Moisture	Method 106




SERIES NAME

3150 Low Silhouette Hermetic Thermostat
3150U Low Silhouette Hermetic Thermostat
3150UX Low Silhouette Hermetic Thermostat
3156 Low Silhouette Hermetic Thermostat
3156U Low Silhouette Hermetic Thermostat

3800 Series Industrial-Grade Thermostats for Severe Duty Applications

The 3800 Series is used where high levels of vibration and mechanical shock are common but a military device is not required. It is easily customized for use in a variety of applications.

Amperage:	7 A resistive
Housing material:	Steel housing with glass-to-metal seal at terminal junction
Operating temperature range:	-29 °C to 260 °C [-20 °F to 500 °F]
Environmental exposure range:	-62 °C to 260 °C [-80 °F to 500 °F]
Dielectric strength:	MIL-STD-202, Method 301 1250 Vac terminal to case
Insulation resistance:	MIL-STD-202, Method 302, Condition B 50 MOhm min. terminal to case
Contact resistance:	MIL-STD-202, Method 307 50 mOhm max.
Hermetic seal:	MIL-STD-202, Method 112, Condition A 1 x 10 ⁻⁵ atm cc/s
Moisture resistance:	MIL-STD-202, Method 106
Vibration (random):	MIL-STD-202, Method 214 30 g, 20 Hz to 2,000 Hz
Vibration (sinusoidal):	MIL-STD-202, Method 204 Condition D 20 G, 20 Hz to 2,000 Hz
Mechanical shock:	MIL-STD-202, Method 213, 400 G
Thermal shock:	MIL-STD-202, Method 107, Condition B
Acceleration:	MIL-STD-202, Method 212, 20 G



SERIES NAME

3800 Industrial Grade Thermostat

3000 Series Custom-packaged Thermostats

The 3000 Series incorporates a Honeywell thermostat assembled in a custom package for use in a variety of applications that require flexibility in mounting and terminal configurations. A typical product includes a 3100 hermetic internal thermostat with a terminal selection, housing selection and customized part number. These custom package devices operate in extreme environmental conditions, including exposure to hazardous substances, dust particles and liquid immersion.


Amperage: 7 A resistive
Housing material: Stainless steel or brass
Operating temperature range: -29 °C to 260 °C [-20 °F to 500 °F]
Environmental exposure range: -62 °C to 288 °C [-80 °F to 550 °F]
Dielectric strength: MIL-STD-202, Method 301
 1250 Vac 60 Hz terminal to case

Insulation resistance: MIL-STD-202, Method 302
 50 MOhm to 500 MOhm
Contact resistance: MIL-STD-202, Method 307
 50 mOhm max.
Hermetic seal: MIL-STD-202, Method 112, Condition A
 1 x 10⁻⁵ atm cc/s
Moisture resistance: MIL-STD-202 Method 106

Terminations for 3000-45X* and 3000-55X* Housings

0

HERMETIC CONNECTOR
BAYONET
OR THREADED



1

WIRE LEADS,
LENGTHS
AS REQ'D.



2a

6,35 [0.25] MALE
QUICK CONNECTS




2b

6,35 [0.25] MALE
QUICK CONNECTS



3


WIRE LEADS,
LENGTHS
AS REQ'D.



1/2 - 14 NPT
THREAD

4a

6,35 [0.25] MALE
QUICK CONNECTS



1/2 - 14 NPT
THREAD

4b

6,35 [0.25] MALE
QUICK CONNECTS



1/2 - 14 NPT
THREAD

Housings

3000-45X*

25,4 [1.00]

3/4 - 16 UNF-3A
THREAD

PROBE LENGTH

SENSING SURFACE

3000-55X*

22,26 [0.875]

1/2 - 14 NPT
THREAD

PROBE LENGTH

SENSING SURFACE

Terminations for 3000-53X* and 3000-141 Housings

1

WIRE LEADS,
LENGTHS
AS REQ'D.



2a

6,35 [0.25] MALE
QUICK CONNECTS



2b

6,35 [0.25] MALE
QUICK CONNECTS



Housings

3000-53X*

22,26 [0.875]

1/2 - 14 NPT
THREAD

SENSING SURFACE

3000-141

25,4 [1.00]

3/4 - 16 UNF - 3A
THREAD

SENSING SURFACE

SERIES NAME


3000 Custom-packaged Thermostat

3450R/3450HR/3455R Series Phenolic Automatic Reset Thermostats

A temperature-sensitive bimetal disc, electrically isolated from the switch, actuates the normally closed contacts. The contacts open when the surface or ambient temperatures increase to the operating snap point of the calibrated disc. Response to temperature changes is extremely rapid due to the inherently low mass of the disc and the small size of the product. These products are factory calibrated to the customer's specification.


Reset type:	Automatic
Amperage capacity:	15 A resistive max.
Housing material:	Phenolic
Operating temperature range:	0 °C to 150 °C [32 °F to 302 °F]
Environmental exposure range:	0 °C to 177 °C [32 °F to 350 °F]

3450R




SERIES NAME
3450R Phenolic Automatic Reset Thermostat

3450HR



SERIES NAME
3450HR Phenolic Automatic Reset Thermostat

3455R




SERIES NAME
3455R Phenolic Automatic Reset Thermostat

3450RC/3450RCH/3455RC Series Ceramic Automatic Reset Thermostats

A temperature-sensitive bimetal disc, electrically isolated from the switch, actuates the normally closed contacts. The contacts open when the surface or ambient temperatures increase to the operating snap point of the calibrated disc. Response to temperature changes is extremely rapid due to the inherently low mass of the disc and the small size of the product.


Reset type:	Automatic
Amperage capacity:	15 A resistive max.
Housing material:	Ceramic
Operating temperature range:	0 °C to 260 °C [32 °F to 500 °F]
Environmental exposure range:	-20 °C to 287 °C [0 °F to 550 °F]

3450RC




SERIES NAME
3450RC Ceramic Automatic Reset Thermostat

3450RCH



SERIES NAME
3450RCH Ceramic Automatic Reset Thermostat

3455RC




SERIES NAME
3455RC Ceramic Automatic Reset Thermostat

3450CM/3455RM Series Ceramic and Phenolic Manual Reset Thermostats

A temperature-sensitive bimetal disc, electrically isolated from the switch, actuates the normally closed contacts. The contacts open when the surface or ambient temperatures increase to the operating snap point of the calibrated disc. The circuit will stay open above room ambient temperature until the manual reset button is pressed. Response to temperature changes is extremely rapid due to the inherently low mass of the disc and the small size of the product.

Reset type:	Manual
Amperage capacity:	15 A resistive max.
Housing material:	Ceramic or phenolic
Operating temperature range:	52 °C to 232 °C [125 °F to 450 °F] (ceramic) 52 °C to 150 °C [125 °F to 302 °F] (phenolic)
Environmental exposure range:	10 °C to 260 °C [50 °F to 500 °F] (ceramic) 10 °C to 177 °C [50 °F to 350 °F] (phenolic)

3450CM




SERIES NAME

3450CM Ceramic Manual Reset Thermostat

3455RBV Series Overmolded Automatic Reset Thermostats

A temperature-sensitive bimetal disc, electrically isolated from the switch, actuates the normally closed contacts. The contacts open when the surface or ambient temperatures increase to the operating snap point of the calibrated disc. Response to temperature changes is extremely rapid due to the inherently low mass of the disc and the small size of the product.


Reset type:	Automatic
Amperage capacity:	15 A resistive max.
Housing material:	Ceramic or phenolic, epoxy overmold
Operating temperature range:	-12 °C to 105 °C [10 °F to 221 °F]
Environmental exposure range:	-18 °C to 121 °C [0 °F to 250 °F]



SERIES NAME

3455RBV Overmolded Automatic Reset Thermostat

3455RM



SERIES NAME

3455RM Phenolic Manual Reset Thermostat


3450R/3450RC/3450RCH/3455R/3455RC

Series "One-shot" ½ in Thermostats

Products are designed for high limit applications where automatic reset is not desired.

Reset type:	None
Amperage capacity:	15 A resistive max.
Housing material:	Ceramic or phenolic
Operating temperature range:	52 °C to 260 °C [125 °F to 500 °F] (ceramic) 52 °C to 150 °C [125 °F to 302 °F] (phenolic)
Environmental exposure range:	18 °C to 316 °C [0 °F to 600 °F] (ceramic) 18 °C to 177 °C [0 °F to 350 °F] (phenolic)


3450R



SERIES NAME

3450R Phenolic "One-shot" ½ in Thermostat


3450RC



SERIES NAME

3450RC Ceramic "One-shot" ½ in Thermostat


3450RCH



SERIES NAME

3450RCH Ceramic "One-shot" ½ in Thermostat


3455R



SERIES NAME

3455R Phenolic "One-shot" ½ in Thermostat


3455RC



SERIES NAME

3455RC Ceramic "One-shot" ½ in Thermostat

Heaters




Heaters are resistive devices that are used in a variety of applications such as airborne valves, appliances, satellites and medical electronics. They are available in flat, molded-to-shape, spiral wrap, transparent, composite and high temperature configurations. Honeywell uses a variety of materials to manufacture its heaters. These include silicone, which can easily be vulcanized to metal parts; Kapton, noted for its thermal stability over a wide temperature range; as well as other flexible dielectric materials. Heaters are available with single, multiple or variable watt densities to customize heat output to unique application needs. They may also be bonded to other system parts or combined with Honeywell thermostats, thermistors, thermocouples, temperature sensors and thermal fuses to form custom-engineered heating systems. Optional PSA (Pressure Sensitive Adhesive) is available with all series.

NOTE: The products in this section do not follow the "how to use this catalogue" instructions provided in the catalogue introduction. Specific reference numbers are not given due to their custom nature. Please contact your local Honeywell sales office for ordering information.

3100 Series Silicone Wire-wound Heaters

The 3100 Series contains resistive wire encased between two layers of fiberglass-supported silicone rubber. All bonding adhesives are uncured silicone rubber. These heaters are cured under pressure and temperature during manufacturing. The multi-stranded resistance wires allow wire-wound heaters to conform to three dimensional shapes. Optional PSA (Pressure Sensitive Adhesive) is available with all series.

Maximum power: 40 W/in²
Operating/storage temperature range: 250 °C [482 °F] max.
 200 °C [392 °F] max. (UL)
Size constraints: None, virtually any size and shape
Geometry: Specific to customer requirements
Heater trace pattern: Specific to customer requirements




SERIES NAME
3100 Silicone Wire-wound Heater

3200 Series Silicone Chemically-etched Heaters

The 3200 Series contains resistive foil traces encased between two layers of fiberglass-supported silicone rubber. All bonding adhesives are uncured silicone rubber. These heaters are cured under pressure and temperature during their manufacturing. They are the optimal choice for multiple watt densities or varying trace geometry requirements.

Maximum power: 40 W/in²
Operating/storage temperature range: 250 °C [482 °F] max.
 200 °C [392 °F] max. (UL)
Size constraints: 0,61 m x 0,61 m [24 in x 24 in]
Geometry: Specific to customer requirements
Heater trace pattern: Specific to customer requirements




SERIES NAME
3200 Silicone Chemically-etched Heater

3400 Series Kapton or High Temperature Insulated Heaters

The 3400 Series contains etched, resistive foil encased between two layers of Kapton. The Kapton Insulated Heaters use an acrylic thermoset bonding adhesive, while the Kapton Insulated High Temperature Heaters use a Teflon™ bonding adhesive. Insulated heaters are used in applications where thin profile and or low material outgassing are important considerations.

Maximum power: 40 W/in²
Operating/storage temp. range: • Kapton insulated: 177 °C [350 °F] max.
 • Kapton high temperature insulated: 260 °C [500 °F] max.
Size constraints: 0,61 m x 0,61 m [24 in x 24 in]
Geometry: Specific to customer requirements within size constraints
Heater trace pattern: Specific to customer requirements




SERIES NAME
3400 Kapton or High Temperature Insulated Heater

78000 Series Transparent Heaters

The 78000 Series heater resistive element consists of a very thin layer of ITO (Indium Tin Oxide) electrically sputtered on PET polyester film. The electrical connection is made via silver ink or carbon bus bars laid on top of the ITO. Wire connections are made via ring terminals eyeleted to the silver or carbon bus bars or flexible tail/connector. Transparent heaters are used to warm liquid crystal displays (LCDs) in cold, moist environments.

Maximum power: 5 W/in²
Operating/storage temp. range: -40 °C to 85 °C [-40 °F to 185 °F]
Size constraints: 0,60 m x 0,43 m [22 in x 17 in]
Geometry: Specific to customer requirements within size constraints
Heater trace pattern: Continuous layer of ITO (Indium Tin Oxide) evenly sputtered across entire surface



SERIES NAME
78000 Transparent Heater




Combi-sensor



The Combi-sensor is a liquid pressure/temperature sensor that uses piezoresistive and thermistor sensing technology to measure water pressure and temperature. It is designed for use in boiler system water pressure and inflow temperature measurement applications.

Pressure range:	0 bar to 3.0 bar relative
Accuracy:	±2 % over full range
Response time:	<3 s
Operating temperature:	5 °C to 110 °C [41 °F to 203 °F]
Overpressure:	5 bar for 1 hour
Burst pressure:	9 bar for 1 min
Power supply:	5 Vdc ±10 %
Voltage output:	0.5 Vdc to 4.5 Vdc ratiometric to Vs
Maximum current limit:	250 mA (not self-limiting) (for reverse polarity)
NTC (Negative Temperature Coefficient) characteristics:	10 kOhm at 25 °C ±3 % beta(25/85) = 3998 K ±2 %
Connection:	Lumberg rast 2.5 edge connector ESL code 312-600

DESCRIPTION	REFERENCE
Combi-sensor	FS300-100



Thermal Cutoffs



Thermal Cutoffs include products for use in a wide array of small appliances, major appliances, office copy machines, automotive, and HVAC equipment. These devices are available in various lead lengths and configurations.

NOTE: The products in this section do not follow the "how to use this catalogue" instructions provided in the catalogue introduction. Specific reference numbers are not given due to their custom nature. Please contact your local Honeywell sales office for ordering information.

NOTICE


- To maximize product life, use a 30 °C [86 °F] min. differential between the operating ambient temperature at the fuse location and the specified functioning temperature of the fuse being used. Maintain a 40 °C [104 °F] min. differential between devices with functioning temperatures above 200 °C [392 °F].
- Under no condition should the thermal cutoff be exposed to a continuous normal temperature rating in excess of 200 °C [392 °F]. Only proper testing of the above will determine the selected thermal cutoff's suitability within the application.

D Series

The D Series responds to temperature by interrupting an electrical circuit when the operating and/or environmental temperature exceeds the thermal rating of the fuse. This is accomplished when the organic pellet experiences a phase change, allowing the spring activated contacts to permanently open the circuit.


Operating temperature range: 72 °C to 240 °C [162 °F to 464 °F]
Environmental exposure range: see notice

DXXX-001




NAME
DXXX-001

DXXX-002



NAME
DXXX-002

DXXX-003



NAME
DXXX-003

Honeywell

www.honeywell.com/sensing


RD Series

The RD Series responds to temperature by interrupting an electrical circuit when the operating and/or environmental temperature exceeds the thermal rating of the fuse. This is accomplished when the organic pellet experiences a phase change, allowing the spring activated contacts to permanently open the circuit.

The electrical resistance of an RD Series thermal cutoff is comparable to that found in an equal length of 18 gauge solid copper wire. With proper heat flow, heat generation below 15 A is minimal. Above 15 A, the upper limit on current capacity will depend on the environment for each specification


Operating temperature range: 72 °C to 240 °C [162 °F to 464 °F]
Environmental exposure range: see notice

RDXXX-001



NAME
RDXXX-001

RDXXX-002



NAME
RDXXX-002

Position Sensors




SS40/400 Series Hall effect digital position sensor

SS400 Series position sensors have a thermally balanced integrated circuit over full temperature range. The negative compensation slope is optimized to match the negative temperature coefficient of lower cost magnets. Bipolar, latching and unipolar magnetics are available.

Band gap regulation provides extremely stable operation over 3.8 Vdc to 30 Vdc supply voltage range.

Package style: Radial lead IC
Supply voltage: 3.8 Vdc to 30 Vdc
Operating temperature: -40 °C to 150 °C
-40 °F to 302 °F



OPTIONS

MAXIMUM Operating Point and MINIMUM Release Point are specified @ 25 °C

Bipolar - temperature compensated

OPERATING POINT (MAXIMUM)	RELEASE POINT (MINIMUM)	REFERENCE
60 Gauss	-60 Gauss	SS411A
140 Gauss	-140 Gauss	SS413A

Bipolar - non temperature compensated

Supply voltage: 4.5 to 24 Vdc
Operating temperature: -55 °C to 150 °C
-67 °F to 302 °F

OPERATING POINT (MAXIMUM)	RELEASE POINT (MINIMUM)	REFERENCE
150 Gauss	-140 Gauss	SS41

Unipolar - temperature compensated

OPERATING POINT (MAXIMUM)	RELEASE POINT (MINIMUM)	REFERENCE
115 Gauss	20 Gauss	SS441A
180 Gauss	75 Gauss	SS443A
390 Gauss	235 Gauss	SS449A

Bipolar latching- temperature compensated


OPERATING POINT (MAXIMUM)	RELEASE POINT (MINIMUM)	REFERENCE
85 Gauss	-85 Gauss	SS461A
180 Gauss	-180 Gauss	SS466A

SS49/490 Series Ratiometric hall effect linear position sensor

Package style: Radial lead IC
Supply voltage: 4.5 to 10.5 Vdc
Operating temperature: -40 °C to 150 °C
-40 °F to 302 °F
Magnetic range: -670 to 670 Gauss

OPTIONS

Temperature compensated



	PACKAGE STYLE	REFERENCE
High accuracy		SS495A
High accuracy	Surface mount	SS495A1
	Surface mount reel	SS495A1-S
		SS495A-SP

PACKAGE STYLE	REFERENCE
Radial lead IC	2SS52M
Surface Mount	2SS52M-S

OPERATING POINT (MAXIMUM)	RELEASE POINT (MINIMUM)	REFERENCE
85 Gauss	-85 Gauss	SR13R-A1

Technical drawing of the SR16C-J6 connector, showing two views with dimensions in millimeters (mm).

Top View Dimensions:

- Overall width: 24,6
- Distance between mounting holes: 19,0
- Mounting hole diameter: $2 \times \varnothing 1,375$
- Distance from mounting hole to center: 0,125
- Distance from center to edge: 0,75
- Overall height: 0,97
- Pin dimensions: $4 \times R 2,79$ and 0,11

Side View Dimensions:

- Overall height: 8,6
- Distance from base to top of mounting hole: 0,34
- Mounting hole width: 3,3
- Mounting hole depth: 0,13
- Distance from mounting hole to center: 12,4
- Distance from center to edge: 0,49
- Pin dimensions: $2 \times 3,5$ and 0,14
- Distance from center to edge: 2 x 11,9
- Distance from base to top of pin: 0,47
- Distance from base to bottom of pin: 3 x 7,6
- Distance from base to bottom of pin: 0,30
- Distance from base to bottom of pin: 4,1
- Distance from base to bottom of pin: 0,16

SR17 Series

Cost effective digital vane sensor

SR17 series competitively priced Hall-effect digital vane sensors are designed for position and speed sensing and are offered in a side-mount twin tower package.

Package style:

Supply voltage:

Operating temperature:

Side looker mounting


3.8 Vdc to 30 Vdc

-20 °C to 85 °C


-4 °F to 185 °F

OPTIONS

Type J6



Type J7



PACKAGE STYLE

Side mount wire exit

41 in wire leads and connector

REFERENCE

SR17C-J6

SR17C-J7




Infrared sensors are used for presence sensing, motion sensing, position encoding, limit sensing, movement detection and counting.

Infrared emitting diodes


OPTIONS

Metal package, end-emitting


Coaxial, lead case - SE1450/1470(L)




Miniature pill - SE2460/2470



TO-46, flat window - SE3455/3470



TO-46, dome lensed - SE5455/5470




Operating temperature: -55 °C to 125 °C (-67 °F to 257 °F)


OUTPUT WAVELENGTH (nm)	BEAM ANGLE (°)	POWER OUTPUT	REFERENCE
935	24	0.70 mW min.	SE1450-003L
880	24	1.10 to 4.50 mW/cm ²	SE1470-003L
935	18	1.00 mW min.	SE2460-003
880	18	6.0 mW/sr min.	SE2470-002
935	90	5.4 mW min.	SE3455-004
880	90	10.5 mW min.	SE3470-003
935	20	4.8 mW min.	SE5455-003
880	20	3.5 mW/cm ² min.	SE5470-004

Plastic package


T1, end-emitting - SEP8505/8705



Side-emitting - SEP8506/8706




Side-emitting - SEP8736



Operating temperature: -40 °C to 85 °C (-40 °F to 185 °F)

OUTPUT WAVELENGTH (nm)	BEAM ANGLE (°)	POWER OUTPUT	REFERENCE
935	15	2.0 to 4.0 mW/cm ²	SEP8505-003
935	50	0.33 to 0.52 mW/cm ²	SEP8506-002
880	15	2.7 to 7.8 mW/cm ²	SEP8705-003
880	10	1.7 to 3.0 mW/cm ²	SEP8736-003

Ceramic discrete surface mount - glass lens



This device can be mounted with the lens up or down, looking through PCB.

Operating temperature: -55 °C to 125 °C (-67 °F to 257 °F)


OUTPUT WAVELENGTH (NM)	BEAM ANGLE (°)	POWER OUTPUT	REFERENCE
880	24	0.60 mW/cm² min.	SME2470-021

Phototransistors


OPTIONS

Metal package


Coaxial, lead case - SD1440(L)




Miniature pill - SD2440



TO-46, flat window - SD3443



TO-46, dome lensed - SD5443




Operating temperature: -55 °C to 125 °C (-67 °F to 257 °F)


ANGULAR RESPONSE (°)	LIGHT CURRENT MINIMUM (mA)	REFERENCE
24	3.0	SD1440-003L
48	7.0	SD2440-004
90	2.0	SD3443-003
18	8.0	SD5443-003

Plastic package


T1, end-looking - SDP8405



Side-looking- SDP8406



Side-looking - SDP8436




Operating temperature: -40 °C to 85 °C (-40 °F to 185 °F)

ANGULAR RESPONSE (°)	LIGHT CURRENT MINIMUM (mA)	REFERENCE
20	12.0	SDP8405-003
50	1.80	SDP8406-002
18	7.0	SDP8436-003

Ceramic discrete surface mount - glass lens

Top-looking - SMD2420/2440



Note:

This device can be mounted with the lens up or down, looking through PCB.

Operating temperature: -55 °C to 125 °C (-67 °F to 257 °F)


ANGULAR RESPONSE (°)	LIGHT CURRENT MINIMUM (mA)	REFERENCE
28	3.0	SMD2440-012

Optoschmitt detectors

OPTIONS

Metal package

TO-46, dome lensed




Operating temperature: -40 °C to 100 °C (-40 °F to 212 °F)
 Supply voltage: 16.0 V
 Output: 10 kOhm Pull-up
 Angular response: 12°

OUTPUT LOGIC	TURN-ON THRESHOLD IRRADIANCE	REFERENCE
Buffer	2.5 mW/cm ² max.	SD5600-001
Inverter	2.5 mW/cm ² max.	SD5610-001
Buffer	0.25 mW/cm ²	SD5620-001
Inverter	0.25 mW/cm ²	SD5630-001

Plastic package

Side-looking



Operating temperature: -40 °C to 85 °C (-40 °F to 185 °F)
 Supply voltage: 16.0 V
 Output: 10 kOhm Pull-up
 Angular response: 50°


OUTPUT LOGIC	TURN-ON THRESHOLD IRRADIANCE	REFERENCE
Buffer	2.5 mW/cm ² max.	SDP8600-001

Encoder sensors


Operating temperature: -40 °C to 85 °C (-40 °F to 185 °F)
 Turn-on threshold irradiance: 0.05 mW/cm² to 2.0 mW/cm²
 Supply voltage: 4.5 Vdc to 5.5 Vdc
 Package style: Plastic, PC mount

OPTIONS

Side-looking - HLC2705



PC mount - HOA0901/0902



LEADS	HOA0901	HOA0902
1. Cathode	1. Cathode	1. Cathode
2. Anode	2. Anode	2. Anode
3. Output A	3. Speed	3. Speed
4. GND	4. GND	4. GND
5. Vcc	5. Vcc	5. Vcc
6. Output B	6. Direction	6. Direction

OUTPUT OPTION	REFERENCE
Speed and direction	HLC2705-001
Direction, inverting logic	HOA0901-011
Speed and direction, 2 tachometer	HOA0902-011

NOTICE


Housings are soluble in chlorinated hydrocarbons and ketones. Recommended cleaning agents are methanol and isopropanol.

Reflective sensors


OPTIONS

Metal components

Converging/focused optical axis - HOA1180



Converging/focused optical axis - HOA2498




Operating temperature: -55 °C to 100 °C (-67 °F to 212 °F)
Output: Transistor

ON-STATE COLLECTOR CURRENT	REFERENCE
0.16 mA	HOA1180-002
0.16 mA	HOA2498-002

Plastic package


HLC1395 Series, short distance detection




(1,0 mm/0,04 in) point of optimum response

HOA Series

Converging/focused optical axis - HOA0149




HOA1397



(1,27 mm/0,05 in) point of optimum response

Converging/focused optical axis - HOA1405



Operating temperature: -40 °C to 85 °C (-40 °F to 185 °F)
Output: Transistor

	ON-STATE COLLECTOR CURRENT	REFERENCE
Low profile	0.60 mA	HLC1395-002
	1.00 mA	HOA0149-001
	0.70 mA	HOA1397-002
	0.80 mA	HOA1405-002

NOTICE

Housings are soluble in chlorinated hydrocarbons and ketones. Recommended cleaning agents are methanol and isopropanol.


Transmissive sensors, Phototransistor output

OPTIONS

Metal components

HOA1877

Aperture (emitter and detector): $\varnothing 1,27 \text{ mm}$ (0.050 in)




Operating temperature: -55°C to 100°C (-67°F to 212°F)
Output: Transistor


ON-STATE COLLECTOR CURRENT	REFERENCE
0.1 mA	HOA1877-001

Plastic components

HOA086X/087X



HOA1879




NOTICE

Housings are soluble in chlorinated hydrocarbons and ketones. Recommended cleaning agents are methanol and isopropanol.

HOA1882

Aperture (emitter and detector): $\varnothing 1,52 \text{ mm}$ (0.060 in)





Plastic components, wire leads

HOA088X/089X

Wire colour code and functions

Red - IRED Anode
Black - IRED Cathode
White - Detector Collector
Green - Detector Emitter




HOA1870

Wire colour code and functions:

Orange - IRED Anode
Green - IRED Cathode
White - Detector Collector
Blue - Detector Emitter

Aperture (emitter and detector): 0.15 mm (0.006 in) wide



Operating temperature: -40°C to 85°C (-40°F to 185°F)
Output: Transistor

	ON-STATE COLLECTOR CURRENT	REFERENCE
Opaque housing	1.00 mA	HOA0866-T55
	0.50 mA	HOA0870-N51
	0.50 mA	HOA0880-P51
Opaque housing	0.50 mA	HOA0890-L55
	0.30 mA	HOA1870-031
	0.50 mA	HOA1879-015
	1.80 mA	HOA1882-012



Transmissive sensors, Optoschmitt output

OPTIONS

Plastic components

HOA096X/097X

HOA696X/697X



Plastic components, wire leads

HOA698X/699X

Wire colour code and functions:



Red - IRED Anode

Black - IRED Cathode

Green - Detector Ground


White - Detector Vcc

Blue - Detector Output



Plastic components, integral 3 pin connector

HOA7720/30



Operating temperature:

-40 °C to 70 °C (-40 °F to 158 °F)

	OUTPUT	OUTPUT LOGIC	HYSTERESIS	REFERENCE
Opaque housing	10 kOhm Pull-up	Buffer	10 %	HOA0961-N51
	10 kOhm Pull-up	Buffer	10 %	HOA0971-N51
	Open-Collector	Inverter	5 %	HOA6963-N51
Opaque housing	Totem-Pole	Inverter	5 %	HOA6972-N55
	Open-Collector	Buffer	5 %	HOA6981-L51
Opaque housing	Totem-Pole	Buffer	5 %	HOA6990-T51
	Totem-Pole	Inverter	5 %	HOA7720-M22
	Open-Collector	Inverter	5 %	HOA7730-M22

NOTICE

Housings are soluble in chlorinated hydrocarbons and ketones. Recommended cleaning agents are methanol and isopropanol.

Current Sensors

Current sensors monitor ac or dc current. Included are adjustable linear, null balance, digital, and linear current sensors.

Digital current sensors can sound an alarm, start a motor, open a valve or shut down a pump. The linear signal duplicates the waveform of the current being sensed, and can be used as a feedback element to control a motor or regulate the amount of work being done by a machine.

CSN Series Closed Loop Current Sensors



Closed loop current sensors measure ac, dc and impulse currents over 0-25, 0-50, 0-100, 0-600 and 0-1200 Amp ranges. The CSN series is based on the Hall effect principle and the null balance or zero magnetic flux method (feedback system). The magnetic flux in the sensor core is constantly controlled at zero. The amount of current required to balance zero flux is the measure of the primary current flowing through the conductor, multiplied by the ratio of the primary to secondary windings. This closed loop current is the output from the device and presents an image of the primary current reduced by the number of secondary turns at any time. This current can be expressed as a voltage by passing it through a resistor.

The CSN Series has a high overload capacity, a high level of electrical insulation between primary and secondary circuits and a rapid response rate. Lightweight and compact, and with no restriction on input current waveform, the sensors are ideal for variable speed drives, power supplies, feedback control systems, robotics/welding equipment and general overcurrent protection.

Sensed current type: ac or dc
EMC: EN 50082-2, EN 50081-2
Accuracy: $\pm 0.5\%$

OPTIONS


Multi turn PCB mounted

Housing material:


Bayblend KU2-1468 (UL94-V0)

Mounting:

PCB on 13 pins



SENSED CURRENT RANGE	COIL TURNS	SUPPLY VOLTAGE	REFERENCE
$\pm 36\text{ A}$	1000 (110 Ohm coil)	$\pm 15\text{ Vdc}$	CSNE151



SENSED CURRENT RANGE	NOMINAL CURRENT	COIL TURNS	SUPPLY VOLTAGE	REFERENCE
$\pm 90\text{ A}$	25 A	1000 (66 Ohm coil)	$\pm 12\text{ Vdc to }15\text{ Vdc}$	CSNE151-100
$\pm 90\text{ A}$	50 A	1000 (66 Ohm coil)	$\pm 12\text{ Vdc to }15\text{ Vdc}$	CSNE151-200


Small housed style

Housing material:


Bayblend FR 1440 (UL94-V0)

Mounting:

PCB on 3 pins



SENSED CURRENT RANGE	COIL TURNS	SUPPLY VOLTAGE	REFERENCE
± 70 A	1000 (90 Ohm coil)	± 15 Vdc	CSNA111
± 90 A	1000 (50 Ohm coil)	± 13 Vdc	CSNC241-500
± 100 A	2000 (160 Ohm coil)	± 15 Vdc	CSNB121
± 100 A	2000 (130 Ohm coil)	± 15 Vdc	CSNB131

Pinout style 'B'

SENSED CURRENT RANGE	COIL TURNS	SUPPLY VOLTAGE	REFERENCE
± 150 A	1000 (30 Ohm coil)	± 12 to ± 15 Vdc	CSNF161
± 180 A	2000 (100 Ohm coil)	± 12 to ± 15 Vdc	CSNF151
± 200 A	2000 (100 Ohm coil)	± 12 to ± 15 Vdc	CSNR151
± 200 A	1000 (30 Ohm coil)	± 12 to ± 15 Vdc	CSNR161


Small housed family

Housing material:


Bayblend KU2-1468 (UL94-V0)

Mounting:


PCB on 3 pins

Pinout style 'A'

SENSED CURRENT RANGE	COIL TURNS	SUPPLY VOLTAGE	REFERENCE
± 90 A	1000 (30 Ohm coil)	± 12 to ± 15 Vdc	CSNP661
± 150 A	2000 (100 Ohm coil)	± 12 to ± 15 Vdc	CSNT651
± 180 A	2000 (100 Ohm coil)	± 15 Vdc	CSNG251



SENSED CURRENT RANGE	COIL TURNS	SUPPLY VOLTAGE	REFERENCE
± 150 A	1000 (30 Ohm coil)	± 12 to ± 15 Vdc	CSNF161-002
± 200 A	2000 (100 Ohm coil)	± 12 to ± 15 Vdc	CSNR151-002
± 200 A	1000 (30 Ohm coil)	± 12 to ± 15 Vdc	CSNR161-002



SENSED CURRENT RANGE	COIL TURNS	SUPPLY VOLTAGE	REFERENCE
± 90 A	1000 (30 Ohm coil)	± 12 to ± 15 Vdc	CSNP661-002
± 150 A	2000 (100 Ohm coil)	± 12 to ± 15 Vdc	CSNT651-001

CSN Series

Closed Loop Current Sensors (Continued)


Mid range housed style

Housing material:

Bayblend KU2-1468 (UL94-V0)

Mounting:

Panel, spade terminals x 3



SENSED CURRENT RANGE	COIL TURNS	SUPPLY VOLTAGE	REFERENCE
± 600 A	2000 (25 Ohm coil)	± 12 to ± 18 Vdc	CSNJ481
± 600 A (fitted with busbar)	2000 (25 Ohm coil)	± 12 to ± 18 Vdc	CSNJ481-001


Large housed style

Housing material:

Bayblend KU2-1468 (UL94-V0)

Mounting:


Panel, spade terminals x 3



SENSED CURRENT RANGE	COIL TURNS	SUPPLY VOLTAGE	REFERENCE
± 1200 A	5000 (50 Ohm coil)	± 15 to ± 24 Vdc	CSNK591
± 1200 A (fitted with busbar)	5000 (50 Ohm coil)	± 15 to ± 24 Vdc	CSNK591-001

CSLA Series

Open Loop Current Sensors



CS series linear current sensors incorporate our 91SS12-2 and SS94A1 linear output Hall effect transducer (LOHET™). These sensors cover measuring ranges from 0-950 Amps. The sensing element is assembled in a printed circuit board mountable housing. This housing is available in four configurations. Normal mounting is with 0.375 inch long 4-40 screw and square nut (not provided) inserted in the housing or a 6-20 self-tapping screw. The combination of the sensor, flux collector, and housing comprises the holder assembly. These sensors are ratiometric.

Sensed current type:


ac or dc

Housing:

PBT Polyester

OPTIONS

PCB bottom mount




NOTES

- 1 - Air gap in toroid is 0.094
- 2 - Gauss level in air gap is 4.7 to 5.5 Gauss per NI
- 3 - Recommended mounting is 4-40 square nut & 0.375 long 4.40 screw
- 4 - See 91SS12-2 for electrical characteristics
- 5 - Conventional current flow in direction indicated will cause an increase in hall voltage


SENSED CURRENT RANGE	SUPPLY VOLTAGE	REFERENCE
0 to 75 A	8 to 16 Vdc	CSLA1DE
0 to 92 A	6 to 12 Vdc	CSLA2DE
0 to 150 A	6 to 12 Vdc	CSLA2DG
0 to 225 A	8 to 16 Vdc	CSLA1DJ
0 to 225 A	6 to 12 Vdc	CSLA2DJ
0 to 325 A	8 to 16 Vdc	CSLA1DK
0 to 400 A	6 to 12 Vdc	CSLA2DK

PCB bottom mount




SENSED CURRENT RANGE	SUPPLY VOLTAGE	REFERENCE
0 to 57 A	8 to 16 Vdc	CSLA1CD
0 to 72 A	6 to 12 Vdc	CSLA2CD
0 to 100 A	8 to 16 Vdc	CSLA1CF
0 to 150 A	8 to 16 Vdc	CSLA1CH

PCB bottom mount




SENSED CURRENT RANGE	SUPPLY VOLTAGE	REFERENCE
0 to 310 A	6 to 12 Vdc	CSLA2EJ
0 to 550 A	6 to 12 Vdc	CSLA2EL
0 to 625 A	8 to 16 Vdc	CSLA1EL
0 to 765 A	6 to 12 Vdc	CSLA2EM
0 to 950 A	6 to 12 Vdc	CSLA2EN

PCB side mount




SENSED CURRENT RANGE	SUPPLY VOLTAGE	REFERENCE
0 to 57 A	8 to 16 Vdc	CSLA1GD
0 to 72 A	6 to 12 Vdc	CSLA2GD

PCB side mount



SENSED CURRENT RANGE	SUPPLY VOLTAGE	REFERENCE
± 45 A	4.5 to 10.5 Vdc	CSLH3A45

Digital current sensor



OPERATE CURRENT	SUPPLY VOLTAGE	REFERENCE
3.5 A.t Nominal	6 to 16 Vdc	CSDA1BC

Liquid Level Sensors



Honeywell liquid level sensor components incorporate a voltage level switch which provides a digital output that denotes the presence or absence of liquid.


The mode of operation is derived from the principle of total internal reflection. An LED and detector are housed within a plastic dome at the head of the device. When no liquid is present, all light from the LED is totally internally reflected from the dome boundary to the detector. When liquid covers the dome, the effective refractive index at the dome/liquid boundary changes, allowing some light from the LED to escape. Thus the amount of light received by the voltage level switch is reduced and the output switches, denoting the presence of liquid. This method of liquid level sensing is very fast, and instantaneous for water.

The LL Series is a basic component which requires external circuit protection; this protection is incorporated in the LLE Series.

Housing:	Polysulphone
Termination:	250 mm lead wires
Supply voltage:	+5 Vdc
Pressure range:	0 to 5 bar


LL Series

Operating temperature:	
Standard	-20 °C to 85 °C -4 °F to 185 °F
High temperature	-40 °C to 125 °C -40 °F to 257 °F
Storage temperature:	
Standard	-40 °C to 100 °C -40 °F to 212 °F
High temperature	-50 °C to 150 °C -58 °F to 302 °F



Liquid Level Sensor - LL Series


Type 5



	SEAL WASHER	REFERENCE
High temperature	Nitrile rubber	LL105100

LLE Series


Operating temperature:	-25 °C to 80 °C -13 °F to 176 °F
Storage temperature:	-30 °C to 85 °C -22 °F to 185 °F



OPTIONS


OPTIONS

Type 2




	SEAL WASHER	REFERENCE
High temperature	Vamac	LL102101

Type 3




	SEAL WASHER	REFERENCE
Standard	Nitrile rubber	LL103000
High temperature	Vamac	LL103101

Type 2



	SEAL WASHER	REFERENCE
	Nitrile rubber	LLE102000

Type 5



	SEAL WASHER	REFERENCE
	Nitrile rubber	LLE105000

Basic Switches



These listings include standard size basics, miniature, subminiature, switches. The precision snap-action mechanisms are offered with a wide variety of actuators and operating characteristics. Basic switches are ideal for applications requiring compactness, light weight, accurate repeatability and long life.

They are best used for presence/absence detection where physical contact with object is permissible. Very economical.

BA/BE/BZ Series Basic Switches

BA/BE/BZ Series Standard Basic Switches are used for simple or precision on/off application needs.

As well as the catalogue listings presented here, we offer other versions with higher temperature ratings, different termination options, different electrical ratings and Single Pole, Single Throw (SPST) circuitry. Refer to our website for details.

Voltage: 250 Vac
Electrical rating: 16 A
Operating temperature: -55 °C to 85 °C
 -67 ° F to 185 ° F

Termination: Screw
Contact type: Silver
Approvals: CE, CSA, UL
Switching options: SPDT


Single Pole, Double Throw



OPTIONS

Note: BA/BE plunger position distance from mounting hole = 19 mm (0.75 in)


Top pin plunger



Approvals: BE-2R-A4 CSA, UL


ELECTRICAL RATING	TERMINATION	REFERENCE
25 A	Solder	BZ-R
	Screw	BZ-R-A2
	Solder	BZ-R169
	Screw	BZ-2R-A2
	Screw	BE-2R-A4

Overtravel plunger - standard




ELECTRICAL RATING	REFERENCE
20 A	BZ-2RD-A2
	BA-2RB-A2

Panel mount overtravel plunger



ELECTRICAL RATING	APPROVALS	REFERENCE
20 A	DEMKO	BZ-2RQ1-A2
		BA-2RQ1-A2


Overtravel plunger (splash resistant)



REFERENCE
BZ-2RDS-A2
BZ-2RDS-A2S

Stainless steel spring


Overtravel roller plunger



REFERENCE
BZ-2RQ18-A2


BA/BE/BZ Series
Basic Switches
(Continued)

Overtravel roller plunger,
perpendicular




REFERENCE
BZ-2RQ181-A2

Straight lever



ELECTRICAL RATING	APPROVALS	LEVER RADIUS	REFERENCE
20 A	DEMKO	No return spring 152.4 mm	BA-2RV-A2 BZ-2RW80-A2 BZ-2RW84-A2 BZ-2RW863-A2

Roller lever




TERMINATION	LEVER RADIUS	REFERENCE
Solder		BZ-2RW822-A2 BZ-2RW822 BZ-2RW8225551-A2 BZ-2RW826-A2
Splash resistant	One way, 32.1 mm 48.3 mm	BZ-2RW82-A2

DT Series Basic Switch


DT Series Standard Basic Switches consist of two independent single-pole double throw circuits in one housing actuated by one actuator. The terminals are separated by a non-conductive shield to reduce shorting.

Voltage:	250 Vac
Electrical rating:	10 A
Operating temperature:	-55 °C to 85 °C -67 ° F to 185 ° F
Termination:	Screw
Contact type:	Silver
Approvals:	CSA, UL
Switching options:	DPDT Double Pole, Double Throw



OPTIONS

Top pin plunger



REFERENCE
DT-2R-A7


Basic Switch Accessories

A range of accessories is available for BA, BE, BZ and DT switches, such as the 5PA2 terminal enclosure. For more information please contact your local sales office.

TB Series
Miniature Double-break
Basic Switch


TB Series Miniature Double-break Basic Switches are basic double-break units that offer a means of controlling isolated circuits. Each circuit may be driven by an independent voltage source.

Voltage:	250 Vac
Electrical rating:	10 A
Operating temperature:	-55 °C to 125 °C -67 ° F to 257 ° F
Termination:	Solder
Contact type:	Silver
Approvals:	CSA, UL
Switching options:	(SPDT DB) Single Pole, Double Throw, Double Break



OPTIONS

Top pin plunger



NOTE:
1- TERMINALS 1 & 2 NORMALLY CLOSED CIRCUIT
2- TERMINALS 3 & 4 NORMALLY OPEN CIRCUIT
3- TERMINALS ARE PLATED FOR SOLDERING


REFERENCE
1TB1-2

SM and SX Series Subminiature Basic Switches

SM and SX Series Subminiature Basic Switches are used for simple or precision on/off application needs. These switches combine small size and light weight with ample electrical capacity, precision operation and long life. The SX Series are small, precision, snap-action switches that are ideal where savings in space and weight are important.

Voltage: 250 Vac
Operating temperature: -55 °C to 125 °C
-67 °F to 257 °F

Termination: Solder
Contact type: Silver
Switching options: SPDT
Single Pole, Double Throw




SM Series

Approvals: CE, CSA, UL
Ampere rating: 5 A

OPTIONS


Top pin plunger



Approvals: 11SM601-H4 UL, CSA


TERMINATION	REFERENCE
Quick connect	11SM601-H4

Straight lever



REFERENCE
111SM1
Lever length 4,83 mm

Roller lever




REFERENCE
111SM2-T

SX Series

Approvals: CE, CSA, UL
Ampere rating: 5 A

OPTIONS


Top pin plunger



Approvals: 6SX7-T UL, CSA


CONTACTS	AMPERE RATING	REFERENCE
Silver	7 A	1SX1-T
Silver	3 A	11SX1-T
Gold	1 A	6SX7-T

Straight lever



REFERENCE
311SX2-T
Lever length 'A' 12,8 mm
311SX3-T
Lever length 'A' 24,5 mm

Simulated roller



REFERENCE
311SX5-T

ZM, ZX, ZV and ZW Series Subminiature Basic Switches

ZM, ZX, ZV and ZW Series Subminiature Basic Switches are cost-effective devices used for simple on/off applications. These switches combine small size and light weight with ample electrical capability and long life. Plastic lever capability is available on the ZV Series.


Electrical rating:	0.1 A, 3 A, 5 A or 10.1 A
Voltage:	125/250 Vac
Operating temperature:	25 °C to 85 °C [-13 °F to 185 °F]
Termination:	Quick connect, solder, PCB
Contact type:	Gold or silver
Switching options:	SPDT

ZM Series

Approvals:	UL/CSA
Electrical rating:	0.1 A, 5 A or 10.1 A


OPTIONS

Top pin plunger




TERMINATION	ELECTRICAL RATING	CONTACT TYPE	REFERENCE
Quick connect	5 A	silver	ZM50E70A01
Solder	5 A	silver	ZM50E10A01
PCB	10.1 A	silver	ZM90G20A01
Solder	0.1 A	gold	ZM10B10A01

Straight lever



TERMINATION	ELECTRICAL RATING	CONTACT TYPE	REFERENCE
Quick connect	5 A	silver	ZM50E70D01
Solder	5 A	silver	ZM50E10D01

Simulated roller lever




TERMINATION	ELECTRICAL RATING	CONTACT TYPE	REFERENCE
Quick connect	5 A	silver	ZM50E70E01
Solder	5 A	silver	ZM50E10E01

Approvals:
Electrical rating:


UL/CSA
0.1 A or 3 A

Top pin plunger




TERMINATION	ELECTRICAL RATING	CONTACT TYPE	REFERENCE
PCB	3 A	silver	ZX40E30A01
Solder	0.1 A	gold	ZX10C10A01

Straight lever



TERMINATION	ELECTRICAL RATING	CONTACT TYPE	REFERENCE
PCB	3 A	silver	ZX40E30C01
Solder	3 A	silver	ZX40E10C01

Simulated roller lever



TERMINATION	ELECTRICAL RATING	CONTACT TYPE	REFERENCE
PCB	3 A	silver	ZX40E30E01
Solder	3 A	silver	ZX40E10E01


ZV Series

Approvals:
Electrical rating:

UL/ENEC
0.1 A, 5 A or 10.1 A


OPTIONS

Top pin plunger




TERMINATION	ELECTRICAL RATING	CONTACT TYPE	REFERENCE
PCB	5 A	silver	ZV50E20A01
Solder	5 A	silver	ZV50E10A01
Quick connect	0.1 A	gold	ZV10B70A01

Straight lever



TERMINATION	ELECTRICAL RATING	CONTACT TYPE	REFERENCE
Solder	5 A	silver	ZV50E10B01
Quick connect	5 A	silver	ZV50E70C01

Roller lever



TERMINATION	ELECTRICAL RATING	CONTACT TYPE	REFERENCE
PCB	5 A	silver	ZV50E20F01
Quick connect	5 A	silver	ZV50E70F01


ZW Sealed Series

Approvals:
Electrical rating:

UL/ENEC
0.1 A or 5 A


OPTIONS

Top pin plunger




TERMINATION	ELECTRICAL RATING	CONTACT TYPE	REFERENCE
Solder	5 A	silver	ZW50F15AD1

Straight lever



TERMINATION	ELECTRICAL RATING	CONTACT TYPE	REFERENCE
Solder	0.1 A	gold	ZW10E15CD1

Roller lever



TERMINATION	ELECTRICAL RATING	CONTACT TYPE	REFERENCE
Wire leads	0.1 A	gold	ZW10E90FW1

V5 Series Miniature Basic Switches

V5 Series Basic Switches are used for simple or precision on/off, end of limit, presence/absence, pressure, temperature and manual operator interface application needs.

Voltage: 250 Vac

Operating temperature:
Standard -55 °C to 85 °C
-67 °F to 185 °F

High temperature -55 °C to 150 °C
-67 °F to 302 °F

Termination: 6,3 mm x 0,8 mm Quick connect (QC)


Contact type: Silver/silver cadmium oxide

Electrical rating:
V5A 20 A
V5B/P/R 16 A
V5C/D 10 A
V5S 22 A

Switching options: SPDT
Single Pole Double Throw

OPTIONS


Top pin plunger



APPROVALS	REFERENCE
CE, ENEC	V5A010CB
CE, CSA, ENEC, UL	V5B010CB3
CE, CSA, UL	V5B010FB3
CE, ENEC	V5B010TB
CE, ENEC	V5B210CB
CE, ENEC	V5C010BB
CE, CSA, ENEC, UL	V5C010EB3
CE, CSA, ENEC, UL	V5C010TB3
CE, ENEC	V5P010CB


APPROVALS	SWITCHING OPTIONS	REFERENCE
CE, ENEC	SPNO	V5D030BB
CE, ENEC	SPNO	V5R030CB
CE, BEAB	SPNC	V5S020CB
CE, BEAB	SPNO	V5S030CB

Straight lever Type B




APPROVALS	REFERENCE
CE, CSA, ENEC, UL	V5C010BB3B

Type C




APPROVALS	REFERENCE
CE, ENEC	V5B210CB1C

Type G




APPROVALS	REFERENCE
CE, ENEC	V5C010BB1G

Roller lever Type D



APPROVALS	REFERENCE
CE, CSA, ENEC, UL	V5B210CB3D
CE, CSA, ENEC, UL	V5C010BB3D

Type E



APPROVALS	REFERENCE
CE, CSA, ENEC, UL	V5A010CB4E
CE, ENEC	V5B210CB1E

V7 Series Miniature Basic Switches

V5 and V7 Series Basic Switches are used for simple or precision on/off, end of limit, presence/absence, pressure, temperature and manual operator interface application needs.

The V7 Series also offers listings with Single Pole, Single Throw circuitry (available in either normally open (NO) or normally closed (NC) configurations). Refer to our website for details.

Operating temperature:

Standard	-40 °C to 82 °C
	-40 °F to 180 °F
High temperature	-40 °C to 200 °C
	-40 °F to 350 °F

Termination:

	Quick connect (QC)
D8, E8 - 4,8 mm (0.187 in) x 0.5 mm (0.02 in)	
E9 - 6,35 mm (0.25 in) x 0.80 mm (0.032 in)	
	Printed circuit board (PCB)

	Electrical rating	Contact Type
V7-*A	5 A	Silver
V7-*B	11 A	Silver
V7-*C/W	15 A	Silver
V7-*D	1 A	Gold alloy
V7-*E	10 A	Silver
V7-*S	100 mA	Gold alloy
V7-*V	21 A	Silver alloy
V7-*Z	25 A	Silver cadmium oxide

Approvals:


V7-*C/D/W CSA, UL, ENEC CSA, UL

Switching options:


Single Pole Double Throw

AVAILABLE TERMINALS


Quick Connect (QC)



D8 terminals are European approved when used with electrical ratings A, B, D, E or S. International approving agencies require that switches with these terminals have insulated receptacles or connector.




E8 terminals are European approved when used with electrical ratings A, B, D, E or S.



E9 terminals are European approved when used with electrical ratings A, B, D, E, S, V or Z.

Printed circuit board (PO2)




These terminals interface with snap-on receptacles and other components from AMPNODU interconnection system.

PCB terminals are European approved when used with electrical ratings A, B, D, E, S.

OPTIONS

Top pin plunger




Note: The optional mounting hole dimensions shown above are standard on V5/V7 International Series switches.

VOLTAGE	TERMINATION	REFERENCE
250 Vac		V7-1A17D8
250 Vac	PCB	V7-1A17P02
250 Vac		V7-1B17D8
250 Vac		V7-1B19E9
250 Vac		V7-1C17D8
277 Vac		V7-1C17E9
277 Vac		V7-1C18E9
125 Vac		V7-1D10D8
277 Vac		V7-1E10D8
277 Vac	PCB	V7-1E17P02
277 Vac		V7-1E19E9
125 Vac		V7-1S17D8
277 Vac		V7-1V19E9
250 Vac		V7-1Z19E9
250 Vac		V7-2A17E9
250 Vac		V7-2B17D8
277 Vac		V7-2B17E9
277 Vac	PCB	V7-2B17P02
125 Vac		V7-2S17D8
250 Vac		V7-3A17D8
277 Vac		V7-3E10E8
277 Vac		V7-3E10E9
277 Vac		V7-3E17D8
277 Vac		V7-3E17E9
277 Vac		V7-3E19E9
125 Vac		V7-3S17E9
250 Vac		V7-4A17D8
250 Vac		V7-4A18E9
125 Vac		V7-4S17D8
125 Vac		V7-5D17E9
277 Vac		V7-6B19D8
277 Vac		V7-6C17D8
277 Vac		V7-7A19D8

Straight lever

Type -002




VOLTAGE	REFERENCE
277 Vac	V7-1C17D8-002
277 Vac	V7-1C17E9-002
277 Vac	V7-2B17E9-002
277 Vac	V7-6C18D8-002

V7 Series Miniature Basic Switches (Continued)


Straight lever

Type -022



VOLTAGE	REFERENCE
250 Vac	V7-1A17D8-022
277 Vac	V7-1B19D8-022
277 Vac	V7-1C17D8-022
277 Vac	V7-1C18E9-022
125 Vac	V7-1S17D8-022
250 Vac	V7-2A17D8-022
277 Vac	V7-2B17D8-022
125 Vac	V7-2S17D8-022
277 Vac	V7-3E17E9-022
125 Vac	V7-3S17D8-022
125 Vac	V7-3S17E9-022

Type -048




VOLTAGE	REFERENCE
277 Vac	V7-1B17D8-048
277 Vac	V7-1C17D8-048
277 Vac	V7-1V19E9-048
277 Vac	V7-2B17D8-048
277 Vac	V7-2B19E9-048
125 Vac	V7-3S17D8-048
277 Vac	V7-6C18D8-048
250 Vac	V7-9W1AE9-048

High temperature


Roller lever

Type -201



VOLTAGE	REFERENCE
277 Vac	V7-1C17D8-201
277 Vac	V7-1C17E9-201
125 Vac	V7-1S17D8-201
277 Vac	V7-2B17D8-201
125 Vac	V7-2S17D8-201
277 Vac	V7-7B17D8-201


Type -207



VOLTAGE	REFERENCE
277 Vac	V7-1B10E9-207
277 Vac	V7-1C17D8-207
277 Vac	V7-1C17E9-207
125 Vac	V7-1S17D8-207
277 Vac	V7-1V19E9-207
250 Vac	V7-2A17D8-207
277 Vac	V7-2B17D8-207
125 Vac	V7-7D17D8-207

Simulated roller lever

Type -263



VOLTAGE	REFERENCE
277 Vac	V7-1B17D8-263
277 Vac	V7-1C17D8-263
125 Vac	V7-1S17D8-263
125 Vac	V7-2S17D8-263
125 Vac	V7-3S17E9-263
277 Vac	V7-6C17D8-263
277 Vac	V7-7B19D8-263

Index

111-103EAJ-H01	22	135-502FAF-J01	18	1865-04G-L-N	14
111-104HAK-H01	22	135-502FAG-J01	18	1865-05G-L-N	14
111-202CAK-B01	22	135-503LAF-J01	18	1865-01G-K-N	14
111-202CAK-H01	22	135-503LAG-J01	18	1865-02G-K-N	14
111-303EAK-B01	22	135-503LFW-J01	18	1865-03G-K-N	14
111-802EAJ-B01	22	135-504QAG-J01	18	1865-04G-K-N	14
111-802EAJ-H01	22	140-102FAG-RB1	20	1865-05G-K-N	14
111SM1	59	140-103LAG-RB1	20	192-102DET-A01	20
111SM2-T	59	140-104QAG-RB1	20	192-102DEV-A01	20
11SM1	59	140-302LAG-RB1	20	192-102DEW-A01	20
11SM601-H4	59	140-501FAG-RB1	20	192-103LET-A01	20
11SX1-T	59	140-502LAG-RB1	20	192-103LEV-A01	20
112-102EAJ-B01	21	140-503QAG-RB1	20	192-103LEW-A01	20
112-103FAJ-B01	21	141PC15G	9	192-104QET-A01	20
112-103FAJ-H01	21	142-102FAG-RB1	21	192-104QEV-A01	20
112-104KAJ-B01	21	142-103LAG-RB1	21	192-104QEW-A01	20
112-104KAJ-H01	21	142-104QAG-RB1	21	192-222LET-A01	20
112-105PAJ-B01	21	142-302LAG-RB1	21	192-222LEV-A01	20
112-201BAJ-B01	21	142-501FAG-RB1	21	192-222LEW-A01	20
112-202EAJ-B01	21	142-502LAG-RB1	21	192-302LET-A01	20
112-202EAJ-H01	21	142-503QAG-RB1	21	192-302LEV-A01	20
112-203HAJ-B01	21	142PC01D	9	192-302LEW-A01	20
112-204KAJ-B01	21	142PC01G	9	192-303KET-A01	20
112-502EAJ-B01	21	142PC02G	9	192-303KEV-A01	20
112-502EAJ-H01	21	142PC05D	9	192-303KEW-A01	20
112-503JAJ-B01	21	142PC05D97	9	192-303QET-A01	20
112-504NAJ-B01	21	142PC05G	9	192-303QEV-A01	20
112-604NAJ-H01	21	142PC15A	9	192-303QEW-A01	20
115-202CDK-801	23	142PC15AW95	9	192-502LET-A01	20
115-802EDJ-801	23	142PC15G	9	192-502LEV-A01	20
120-102EAJ-Q01	22	143-101FAG-RC1	20	192-502LEW-A01	20
120-103FAJ-Q01	22	143-102LAG-RC1	20	192-503QET-A01	20
120-104KAJ-Q01	22	143-103QAG-RC1	20	192-503QEV-A01	20
120-202EAJ-Q01	22	143-201FAG-RC1	20	192-503QEW-A01	20
120-502JAJ-Q01	22	143-302LAG-RC1	20	195-101CAG-A01	19
121-102EAJ-Q01	22	143-303QAG-RC1	20	195-102DAG-A01	19
121-103FAJ-Q01	22	143-501FAG-RC1	20	195-103LAG-A01	19
121-104KAJ-Q01	22	143-502LAG-RC1	20	195-104QAG-A01	19
121-105PAJ-Q01	22	143-503QAG-RC1	20	195-202LAG-A01	19
121-106QAJ-Q01	22	143PC03D	9	195-203LAG-A01	19
121-202EAJ-Q01	22	143PC05DW	9	195-301CAG-A01	19
121-202KAJ-Q01	22	145-101FAG-RC1	21	195-302LAG-A01	19
121-502EAJ-Q01	22	145-102LAG-RC1	21	195-303KAG-A01	19
121-502JAJ-Q01	22	145-103QAG-RC1	21	195-501DAG-A01	19
121-504NAJ-Q01	22	145-201FAG-RC1	21	195-502LAG-A01	19
135-102DAG-J01	18	145-301FAG-RC1	21	195-503QAG-A01	19
135-103FAF-J01	18	145-302LAG-RC1	21	197-101CAG-A01	19
135-103FAG-J01	18	145-303QAG-RC1	21	197-102DAG-A01	19
135-103LAF-J01	18	145-501FAG-RC1	21	197-103LAG-A01	19
135-103LFW-J01	18	145-502LAG-RC1	21	197-104QAG-A01	19
135-104LAF-J01	18	145-503QAG-RC1	21	197-202LAG-A01	19
135-104LAG-J01	18	162PC01D	9	197-203LAG-A01	19
135-104LFW-J01	18	163PC01D36	9	197-301CAG-A01	19
135-105QAG-J01	18	163PC01D48	9	197-302LAG-A01	19
135-202FAG-J01	18	163PC01D61	9	197-303KAG-A01	19
135-203LAG-J01	18	163PC01D75	9	197-501DAG-A01	19
135-203LFW-J01	18	164PC01D37	9	197-502LAG-A01	19
135-204QAG-J01	18	164PC01D76	9	197-503QAG-A01	19
135-302FAG-J01	18	1865-01G-L-N	14	198-101CAG-A01	19
135-303KAG-J01	18	1865-02G-L-N	14	198-102DAG-A01	19
135-303LFW-J01	18	1865-03G-L-N	14	198-103LAG-A01	19

198-104QAG-A01	19	40PC015G1A	8	CPXL04DF	5
198-202LAG-A01	19	40PC015V1A	8	CSDA1BC	55
198-203LAG-A01	19	40PC030G1A	8	CSLA1CD	55
198-301CAG-A01	19	40PC100G1A	8	CSLA1CF	55
198-302LAG-A01	19	40PC150G1A	8	CSLA1CH	55
198-303KAG-A01	19	40PC250G1A	8	CSLA1DE	54
198-501DAG-A01	19	40PC500G1A	8	CSLA1DJ	54
198-502LAG-A01	19	6SX7-T	59	CSLA1DK	54
198-503QAG-A01	19	ASDX001D44R	8	CSLA1EL	55
199-101CAG-A01	19	ASDX001G24R	8	CSLA1GD	55
199-102DAG-A01	19	ASDX005D44R	8	CSLA2CD	55
199-103LAG-A01	19	ASDX005G24R	8	CSLA2DE	54
199-104QAG-A01	19	ASDX015A24R	8	CSLA2DG	54
199-202LAG-A01	19	ASDX015D44R	8	CSLA2DJ	54
199-203LAG-A01	19	ASDX015G24R	8	CSLA2DK	54
199-301CAG-A01	19	ASDX030A24R	8	CSLA2EJ	55
199-302LAG-A01	19	ASDX030D44R	8	CSLA2EL	55
199-303KAG-A01	19	ASDX030G24R	8	CSLA2EM	55
199-501DAG-A01	19	ASDX100A24R	8	CSLA2EN	55
199-502LAG-A01	19	ASDX100D44R	8	CSLA2GD	55
199-503QAG-A01	19	ASDX100G24R	8	CSLH3A45	55
1SX1-T	59	AWM2100V	10	CSNA111	53
1TB1-2	58	AWM2200V	10	CSNB121	53
24PC01SMT	5	AWM2300V	10	CSNB131	53
24PC05SMT	5	AWM3100V	10	CSNC241-500	53
24PC15SMT	5	AWM3200V	10	CSNE151	52
24PCAF6G	4	AWM3300V	10	CSNE151-100	52
24PCBFA6D	4	AWM42150VH	10	CSNE151-200	52
24PCBFA6G	4	AWM42300V	10	CSNF151	53
24PCCFA6D	4	AWM43300V	10	CSNF161	53
24PCCFA6G	4	AWM43600V	10	CSNF161-002	53
24PCCFG6G	4	AWM5101VN	11	CSNG251	53
24PCDFA6D	4	AWM5102VN	11	CSNJ481	54
24PCDFA6G	4	AWM5104VC	11	CSNJ481-001	54
24PCDFG6G	4	AWM5104VN	11	CSNK591	54
24PCEFA6D	4	AWM720P1	11	CSNK591-001	54
24PCEFA6G	4	AWM92100V	12	CSNP661	53
24PCFFA6D	4	AWM92200V	12	CSNP661-002	53
24PCFFA6G	4	BA-2RB-A2	57	CSNR151	53
26PC01SMT	5	BA-2RQ1-A2	57	CSNR151-002	53
26PC05SMT	5	BA-2RV-A2	58	CSNR161	53
26PC15SMT	5	BE-2R-A4	57	CSNR161-002	53
26PCAF6D	4	BZ-2R-A2	57	CSNT651	53
26PCAF6G	4	BZ-2RD-A2	57	CSNT651-001	53
26PCAFG6G	4	BZ-2RDS-A2	57	DC001NDC4	6
26PCBFA6D	4	BZ-2RDS-A2S	57	DC005NDR4	6
26PCBFA6G	4	BZ-2RQ181-A2	58	DCXL01DN	6
26PCCFA6D	4	BZ-2RQ18-A2	57	DCXL10DN	6
26PCCFA6G	4	BZ-2RQ1-A2	57	DT-2R-A7	58
26PCCFG6G	4	BZ-2RW80-A2	58	DUXL01D	6
26PCDFA6D	4	BZ-2RW82	58	DUXL10D	6
26PCDFA6G	4	BZ-2RW8225551-A2	58	DXXX-001	40
26PCDFG2G	5	BZ-2RW822-A2	58	DXXX-002	40
26PCFFA6G	4	BZ-2RW826-A2	58	DXXX-003	40
26PCFFG6G	4	BZ-2RW82-A2	58	FS300-100	39
26PCFFU5G	5	BZ-2RW84-A2	58	FSG15N1A	13
26PCGFA6D	4	BZ-2RW863-A2	58	FSL05N2C	13
2SS52M	44	BZ-R	57	Heaters	
2SS52M-S	44	BZ-R169	57	3100 Silicone Wire-wound	37
311SX2-T	59	BZ-R-A2	57	3200 Silicone Chemically-etched	37
311SX3-T	59	CPCL04DFC	5	3400 Kapton or High Temperature	38
311SX5-T	59	CPCL04GFC	5	78000 Transparent	38
40PC001B1A	8	CPCL10DF	5	HEL-700-T-0-A	16
40PC006G1A	8	CPCL10DFC	5	HEL-700-T-0-B	16

HEL-700-T-1-A	16	HOA7730-M22	51	SR17C-J6	45
HEL-700-T-1-B	16	ICL1010002-01	23	SR17C-J7	45
HEL-700-U-0-A	16	ICL1010004-01	23	SS41	42
HEL-700-U-0-B	16	ICL1210005-01	23	SS411A	42
HEL-700-U-0-C	16	ICL1220002-01	23	SS413A	42
HEL-700-U-1-A	16	ICL122R508-01	23	SS441A	42
HEL-700-U-1-B	16	ICL1240002-01	23	SS443A	42
HEL-700-U-1-C	16	ICL1250002-01	23	SS449A	42
HEL-705-T-0-12-00	17	ICL1510006-01	23	SS461A	42
HEL-705-T-1-12-00	17	ICL1512004-01	23	SS466A	42
HEL-705-U-0-12-00	17	ICL1516004-01	23	SS49	43
HEL-705-U-1-12-00	17	ICL1522102-01	23	SS495A	42
HEL-707-T-0-12-00	17	ICL152R508-01	23	SS495A1	42
HEL-707-T-1-12-00	17	ICL155R006-01	23	SS495A1-S	42
HEL-707-U-0-12-00	17	ICL155R007-01	23	SS495A-SP	42
HEL-707-U-1-12-00	17	ICL1580003-01	23	SS495B	43
HEL-711-T-0-12-00	17	ICL2210008-01	23	SS496B	43
HEL-711-T-1-12-00	17	ICL2212103-01	23	SS511AT	43
HEL-711-U-0-12-00	17	ICL221R020-01	23	SS513AT	43
HEL-711-U-1-12-00	17	ICL222R018-01	23	SS51T	43
HEL-712-T-0-12-00	17	ICL222R515-01	23	SS541AT	43
HEL-712-T-1-12-00	17	ICL320R530-01	23	SS543AT	43
HEL-712-U-0-12-00	17	ICL321R030-01	23	SS549AT	43
HEL-712-U-1-12-00	17	LL102101	56	SS561AT	43
HEL-716-T-0-12-00	17	LL103000	56	SS566AT	43
HEL-716-T-1-12-00	17	LL103101	56	SS94A1	43
HEL-716-U-0-12-00	17	LL105100	56	SS94A1F	43
HEL-716-U-1-12-00	17	LLE102000	56	SS94A2	43
HEL-716-U-1-12-C2	17	LLE105000	56	TD4A	17
HEL-717-T-0-12-00	17	RDXXX-001	41	TD5A	17
HEL-717-T-1-12-00	17	RDXXX-002	41	Temperature - Probes	
HEL-717-U-0-12-00	17	SD1440-003L	47	Air Conditioning	25
HEL-717-U-1-12-00	17	SD2440-004	47	Air/Gas	26
HIH-3602-A	15	SD3443-003	47	Earth Return (Ground)	25
HIH-3602-C	15	SD5443-003	47	ES110 Inlet Air	24
HIH-3602-L	15	SD5600-001	48	ES120 Coolant/Oil	24
HIH-3610-001	15	SD5610-001	48	Immersion	26
HIH-3610-002	15	SD5620-001	48	Refrigerant	25
HIH-3610-003	15	SD5630-001	48	Surface	25
HIH-3610-004	15	SDP8405-003	47	Thermostats - Commercial	
HLC1395-002	49	SDP8406-002	47	2450A Heat Detection	29
HLC2705-001	48	SDP8436-003	47	2450CM Ceramic Manual Reset	28
HOA0149-001	49	SDP8600-001	48	2450HR Phenolic Automatic Reset	27
HOA0866-T55	50	SE1450-003L	46	2450R Fully Sealed	30
HOA0870-N51	50	SE1470-003L	46	2450R Phenolic Annular Automatic Reset	30
HOA0880-P51	50	SE2460-003	46	2450R Phenolic Automatic Reset	27
HOA0890-L55	50	SE2470-002	46	2450R Phenolic "One-shot" ½ in	29
HOA0901-011	48	SE3455-004	46	2450R Protected	30
HOA0902-011	48	SE3470-003	46	2450RC Ceramic Automatic Reset	28
HOA0961-N51	51	SE5455-003	46	2450RCH Ceramic Automatic Reset	28
HOA0971-N51	51	SE5470-004	46	2450RCH Ceramic "One-shot" ½ in	29
HOA1180-002	49	SEP8505-003	46	2455A Heat Detection	29
HOA1397-002	49	SEP8506-002	46	2455R Phenolic Automatic Reset	27
HOA1405-002	49	SEP8705-003	46	2455R Phenolic "One-shot" ½ in	29
HOA1870-031	50	SEP8736-003	46	2455R Protected	30
HOA1877-001	50	SMD2440-012	47	2455RBV Overmolded Automatic Reset	29
HOA1879-015	50	SME2470-021	46	2455RC Ceramic Automatic Reset	28
HOA1882-012	50	SR13C-A1	44	2455RC Ceramic "One-shot" ½ in	29
HOA2498-002	49	SR13D-A1	44	2455RM Phenolic Manual Reset	28
HOA6963-N51	51	SR13F-A1	44	Thermostats - Precision	
HOA6972-N55	51	SR13R-A1	44	3000 Custom-packaged	33
HOA6981-L51	51	SR16C-J4	44	3100 Hermetic	31
HOA6990-T51	51	SR16C-J6	44	3100U Hermetic	31
HOA7720-M22	51	SR16C-N	44	3100UX Hermetic	31

3106 Hermetic	31	V7-1E10D8	65	ZM50E10E01	60
3150 Low Silhouette Hermetic	32	V7-1E17P02	65	ZM50E70A01	60
3150U Low Silhouette Hermetic	32	V7-1E19E9	65	ZM50E70D01	60
3150UX Low Silhouette Hermetic	32	V7-1S17D8	65	ZM50E70E01	60
3156 Low Silhouette Hermetic	32	V7-1S17D8-022	66	ZM90G20A01	60
3156U Low Silhouette Hermetic	32	V7-1S17D8-201	66	ZV10B70A01	61
3450CM Ceramic Manual Reset	35	V7-1S17D8-207	66	ZV50E10A01	61
3450HR Phenolic Automatic Reset	34	V7-1S17D8-263	66	ZV50E10B01	62
3450R Phenolic Automatic Reset	34	V7-1V19E9	65	ZV50E20A01	61
3450R Phenolic "One-shot" ½ in	36	V7-1V19E9-048	66	ZV50E20F01	62
3450RC Ceramic Automatic Reset	34	V7-1V19E9-207	66	ZV50E70C01	62
3450RC Ceramic "One-shot" ½ in	36	V7-1Z19E9	65	ZV50E70F01	62
3450RCH Ceramic Automatic Reset	34	V7-2A17D8-022	66	ZW10E15CD1	62
3450RCH Ceramic "One-shot" ½ in	36	V7-2A17D8-207	66	ZW10E90FW1	63
3455R Phenolic Automatic Reset	34	V7-2A17E9	65	ZW50F15AD1	62
3455R Phenolic "One-shot" ½ in	36	V7-2B17D8	65	ZX10C10A01	61
3455RBV Overmolded Automatic Reset ..	35	V7-2B17D8-022	66	ZX40E10C01	61
3455RC Ceramic Automatic Reset	34	V7-2B17D8-048	66	ZX40E10E01	61
3455RC Ceramic "One-shot" ½ in	36	V7-2B17D8-201	66	ZX40E30A01	61
3455RM Phenolic Manual Reset	35	V7-2B17D8-207	66	ZX40E30C01	61
3800 Industrial Grade	32	V7-2B17E9	65	ZX40E30E01	61
V5A010CB	64	V7-2B17E9-002	65		
V5A010CB4E	64	V7-2B17P02	65		
V5B010CB3	64	V7-2B19E9-048	66		
V5B010FB3	64	V7-2S17D8	65		
V5B010TB	64	V7-2S17D8-022	66		
V5B210CB	64	V7-2S17D8-201	66		
V5B210CB1C	64	V7-2S17D8-263	66		
V5B210CB1E	64	V7-3A17D8	65		
V5B210CB3D	64	V7-3E10E8	65		
V5C010BB	64	V7-3E10E9	65		
V5C010BB1G	64	V7-3E17D8	65		
V5C010BB3B	64	V7-3E17E9	65		
V5C010BB3D	64	V7-3E17E9-022	66		
V5C010EB3	64	V7-3E19E9	65		
V5C010TB3	64	V7-3S17D8-022	66		
V5D030BB	64	V7-3S17D8-048	66		
V5P010CB	64	V7-3S17E9	65		
V5R030CB	64	V7-3S17E9-022	66		
V5S020CB	64	V7-3S17E9-263	66		
V5S030CB	64	V7-4A17D8	65		
V7-1A17D8	65	V7-4A18E9	65		
V7-1A17D8-022	66	V7-4S17D8	65		
V7-1A17P02	65	V7-5D17E9	65		
V7-1B10E9-207	66	V7-6B19D8	65		
V7-1B17D8	65	V7-6C17D8	65		
V7-1B17D8-048	66	V7-6C17D8-263	66		
V7-1B17D8-263	66	V7-6C18D8-002	65		
V7-1B19D8-022	66	V7-6C18D8-048	66		
V7-1B19E9	65	V7-7A19D8	65		
V7-1C17D8	65	V7-7B17D8-201	66		
V7-1C17D8-002	65	V7-7B19D8-263	66		
V7-1C17D8-022	66	V7-7D17D8-207	66		
V7-1C17D8-048	66	V7-9W1AE9-048	66		
V7-1C17D8-201	66	XCA415AN	7		
V7-1C17D8-207	66	XCX01DNC	7		
V7-1C17D8-263	66	XCX01DNH	7		
V7-1C17E9	65	XCX15DNC	7		
V7-1C17E9-002	65	XPC01DFC	7		
V7-1C17E9-201	66	XPC15DTC	7		
V7-1C17E9-207	66	XSL04GF	7		
V7-1C18E9	65	ZM10B10A01	60		
V7-1C18E9-022	66	ZM50E10A01	60		
V7-1D10D8	65	ZM50E10D01	60		

Inside back
cover - blank

Warranty/Remedy

Honeywell warrants goods of its manufacture as being free of defective material and faulty workmanship. Contact your local sales office for warranty information. If warranted goods are returned to Honeywell during that period of coverage, Honeywell will repair or replace without charge those items it finds defective. **The foregoing is Buyer's sole remedy and is in lieu of all other warranties, expressed or implied, including those of merchantability and fitness for a particular purpose.**

While we provide application assistance, personally, through our literature and the Honeywell web site, it is up to the customer to determine the suitability of the product in the application.

Specifications may change at any time without notice. The information we supply is believed to be accurate and reliable as of this printing. However, we assume no responsibility for its use.

ASIA PACIFIC

Control Products

Asia Pacific Headquarters

Phone: +(65) 6355-2828
Fax: +(65) 6445-3033

Australia

Honeywell Limited
Phone: +(61) 2-9370-4500
FAX: +(61) 2-9370-4525
Toll Free 1300-36-39-36
Toll Free Fax: 1300-36-04-70

China – PRC - Beijing

Honeywell China Inc.
Phone: +(86-10) 8458-3280
Fax: +(86-10) 8458-3102

China – PRC - Shanghai

Honeywell China Inc.
Phone: +(86-21) 6237-0237
Fax: +(86-21) 6237-1237

China - Hong Kong S.A.R.

Honeywell Ltd.
Phone: +(852) 2953-6412
Fax: +(852) 2953-6767

Indonesia

Honeywell Indonesia Pte Ltd.
Phone: +(62) 21-535-8833
FAX: +(62) 21-5367 1008

India

TATA Honeywell Ltd.
Phone: +(91) 20 6870 445/
446
Fax: +(91) 20 681 2243/ 687
5992

Japan

Honeywell Inc.
Phone: +(81) 3 5440 1425
Fax: +(81) 3 5440 1368

South Korea

Honeywell Korea Co Ltd
Phone: +(822) 799-6167
Fax: +(822) 792-9013

Malaysia

Honeywell Engineering Sdn
Bhd
Phone: +(60-3) 7958-4988
Fax: +(60-3) 7958-8922

New Zealand

Honeywell Limited
Phone: +(64-9) 623-5050
Fax: +(64-9) 623-5060
Toll Free (0800) 202-088

Philippines

Honeywell Systems
(Philippines) Inc.
Phone: +(63-2) 636-1661/
1662
Fax: +(63-2) 638-4013

Singapore

Honeywell South East Asia
Phone: +(65) 6355-2828
Fax: +(65) 6445-3033

Thailand

Honeywell Systems (Thailand)
Ltd.
Phone: +(662) 693-3099
FAX: +(662) 693-3085

Taiwan R.O.C.

Honeywell Taiwan Ltd.
Phone: +(886-2) 2245-1000
FAX: +(886-2) 2245-3241

EUROPE

Austria

Honeywell Austria GmbH
Phone: +(43) 1 727 80 366/
246
FAX: +(43) 1 727 80 337

Belgium

Honeywell SA/NV
Phone: +(32) 2 728 2522
FAX: +(32) 2 728 2502

Bulgaria

Honeywell EOOD
Phone: +(359) 2 979 00 23
FAX: +(359) 2 979 00 24

Czech Republic

Honeywell spol. s.r.o.
Phone: +(420) 242 442 111
FAX: +(420) 242 442 182

Denmark

Honeywell A/S
Phone: +(45) 39 55 55 55
FAX: +(45) 39 55 55 58

Finland

Honeywell OY
Phone: +(358) 9 3480101
FAX: +(358) 9 34801375

France

Honeywell SA
Phone: +(33) 1 60 19 80 40
FAX: +(33) 1 60 19 81 73

Germany

Honeywell AG
Phone: +(49) 69 8064 444
FAX: +(49) 69 8064 442

Hungary

Honeywell Kft.
Phone: +(361) 451 43 00
FAX: +(361) 451 43 43

Sales and Service

Honeywell serves its customers through a worldwide network of sales offices, representatives and distributors. For application assistance, current specifications, pricing or name of the nearest Authorised Distributor, contact your local sales office or:

INTERNET: www.honeywell.com/sensing

E-mail: info.sc@honeywell.com

Italy

Honeywell S.p.A.
Phone: +(39) 02 92146 450/
456
FAX: +(39) 02 92146 490

The Netherlands

Honeywell B.V.
Phone: +(31) 20 565 69 11
FAX: +(31) 20 565 66 00

Norway

Honeywell A/S
Phone: +(47) 66 76 20 00
FAX: +(47) 66 76 20 90

Poland

Honeywell Sp. z o.o.
Phone: +(351 21) 424 50 64
FAX: +(48) 606 09 01

Portugal

Honeywell Portugal Lda
Phone: +(351 21) 424 50 00
FAX: +(351 21) 424 50 99

Romania

Honeywell Bucharest
Phone: +(40) 21 231 64 37/
38
FAX: +(40) 21 231 6439

Commonwealth of Independent States (CIS)

Z.A.O. Honeywell
Phone: +(7 095) 796 98 36
FAX: +(7 095) 797 99 06

Slovak Republic

Honeywell s.r.o.
Phone: +(421 2) 58 247 403
FAX: +(421 2) 58 247 415

South Africa (Republic of)

Honeywell Southern Africa
Honeywell S.A. Pty. Ltd
Phone: +(27) 11 695 8000
FAX: +(27) 11 805 1504

Spain

Honeywell S.A.
Phone: +(34) 91 313 6100
FAX: +(34) 91 313 6129

Sweden

Honeywell AB
Phone: +(46) 8 775 55 00
FAX: +(46) 8 775 56 00

Switzerland

Honeywell AG
Phone: +(41) 1 855 24 40
FAX: +(41) 1 855 24 45

Turkey

Honeywell Turkey A.S.
Phone: +(90) 216 5756620
FAX: +(90) 216 5756637

Ukraine

Honeywell
Phone: +(380) 44 201 44 74
FAX: +(380) 44 201 44 75

United Kingdom

Honeywell Control Systems
Ltd
Phone: +(44) 1698 481481
FAX: +(44) 1698 481676

Mediterranean & African Distributors

Honeywell SpA
Phone: +(39) 2 921 46 232
FAX: +(39) 2 921 46 233

Middle East Headquarters

Honeywell Middle East Ltd.
Phone: +(9712) 443 2119
FAX: +(9712) 443 2536

NORTH AMERICA

USA/Canada

Honeywell
Sensing and Control
Phone: 1-800-537-6945
1-815-235-6847
FAX: 1-815-235-6545
E-mail:
info.sc@honeywell.com

LATIN AMERICA

Honeywell Latin America Headquarters

Phone: 1-305-805-8188
FAX: 1-305-883-8257

Argentina

Honeywell S.A.I.C.
Phone: +(54-11) 4383-3637
FAX: +(54-11) 4325-6470

Brazil

Honeywell Do Brasil & Cia
Phone: +(55-11) 4166-1900
FAX: +(55-11) 4166-1901

Chile

Honeywell Chile, S.A.
Phone: +(56-2) 425-8400
FAX: +(56-2) 425-8410

Mexico

Honeywell S.A. de C.V.
Phone: +(52) 55 5081-0200
FAX: +(52) 55 5081-0202

Puerto Rico, Caribbean

Honeywell Inc.
Phone: +(787) 792-7075
FAX: +(787) 792-0053

Venezuela

Honeywell C.A.
Phone: +(58-212) 273-0511
FAX: +(58-212) 273-0599

This publication does not constitute a contract between Honeywell and its customers. The contents may be changed at any time without notice. It is the customer's responsibility to ensure safe installation and operation of the products. Detailed mounting drawings of all products illustrated are available on request. Copyright 2004 Honeywell International Inc. All Rights Reserved.

Honeywell

Sensing and Control

www.honeywell.com/sensing

Newhouse Industrial Estate

Motherwell ML1 5SB

Scotland, UK

Spine Layout:



Honeywell

Commercial Switches and Sensors

Issue 2/February 2004