

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 1774091

NFS110 Series

Single and
quad output

Total Power: 80 - 110W
Input Voltage: 85 - 264VAC
120 - 370VDC
of Outputs: Single, quad

Special Features

- 7.0 x 4.25 x 1.8 inch package
- Overvoltage and short circuit protection
- 110 W with 20 CFM
- Adjustable outputs
- EN55022, EN55011 conducted emissions level B
- UL, VDE and CSA safety approvals
- CE mark
- Available RoHS compliant
- 2 year warranty


Safety

VDE0805/EN60950/
IEC950/IEC1010
File No. 10401-3336-0213

Licence No. 40014677

UL1950 File No. E136005

CSA C22.2 No. 950
File No. LR41062C



Rev.02.16.07
NFS110 Series
1 of 4

The NFS110 series is a 110 W universal input ac-dc power supply on a 7 x 4.25 inch card. The NFS110 series has four single and three quad output models and has proven itself to be highly reliable and versatile product for a wide range of communication and industrial applications, with a very high peak current capability on each output for drive and motor applications. The NFS110 provides 80 W of output power with free air convection cooling which can be boosted to 110 W with 20 CFM of air. Standard features include overvoltage and short circuit protection. The series, with full international safety approval and the CE mark, meets conducted emissions EN55022 level B. The NFS110 series is designed for use in low power data networking, computer, telecom and industrial applications such as servers, thermal printers, storage devices, vending machines and POS equipment.



Specifications

All specifications are typical at nominal input, full load at 25°C unless otherwise stated

OUTPUT SPECIFICATIONS

Voltage adjustability	+5.1 V o/p on multi's	±3.0%
	5.1 V single output	±3.0%
	12 V single output	12-14 V
	15 V single output	15-18 V
	24 V single output	24-30 V
Line regulation	LL to HL, FL All outputs on all units	±0.1% max.
Overshoot/undershoot	At turn-on	0%
Temperature coefficient	All outputs	±0.02%/°C
Overvoltage protection	Multi o/p 5.1 V only	6.25 V ±0.75 V
	5.1 V single	6.25 V ±0.75 V
	12 V single	15.75 V ±1.0 V
	15 V single	22 V ±1.5 V
	24 V single	33 V ±2.5 V
Output power limit	Primary power limited	Pin max. 160 W Pout min. 110 W
Minimum output current	(See Note 13)	0 A
Short circuit protection	Burst mode operation	

INPUT SPECIFICATIONS

Input voltage range	85-264 Vac 120-370 Vdc	
Input frequency range	47-440 Hz	
Input surge current	230 Vac	35 A
Safety ground leakage current	110 Vac, 50 Hz	0.2 mA, max.
	230 Vac, 50 Hz	0.4 mA, max.

EMC CHARACTERISTICS

Conducted emissions	EN55022, FCC part 15	Level B
Radiated emissions	EN55022, FCC part 15	Level A
ESD air	EN61000-4-2, level 3	Perf. criteria 1
ESD contact	EN61000-4-2, level 4	Perf. criteria 1
Surge	EN61000-4-5, level 3	Perf. criteria 1
Fast transients	EN61000-4-4, level 3	Perf. criteria 1
Radiated immunity	EN61000-4-3, level 3	Perf. criteria 2
Conducted immunity	EN61000-4-6, level 3	Perf. criteria 1

GENERAL SPECIFICATIONS

Hold-up time	110 Vac @ 80 W	35 ms
	110 Vac @ 110 W	17 ms
	230 Vac @ 80 W	140 ms
	230 Vac @ 110 W	100 ms
Efficiency	Multiple outputs	70% typical
	+5.1 V single	70% typical
	12 V and 15 V singles	72% typical
	24 V single	75% typical
Isolation voltage	Input/output	3000 Vac
	Input/chassis	1500 Vac
Switching frequency	At 100 Watts output	20-70 kHz
	At zero load	100-250 kHz
Approvals and standards (See Note 12)	VDE0805, EN60950, IEC950 IEC1010, UL1950 CSA C22.2 No. 950	
Weight	Singles	550 g (19.4 oz)
	Multiple outputs	600 g (21.2 oz)
MTBF (See Note 9)	MIL-HDBK-217E	125,000 hours

ENVIRONMENTAL SPECIFICATIONS

Thermal performance (See Notes 9, 10)	Operating, see curve	0 °C to +70 °C
	Non-operating	-40 °C to +85 °C
	0 °C to +50 °C, amb. convection cooled	80 W
	+50 °C to +70 °C, amb. convection cooled	Derate 2 W/°C
	0 °C to +50 °C, 20 CFM forced air	110 W
	+50 °C to +70 °C, 20 CFM forced air	Derate 2.75 W/°C
	Peak, 0 °C to +50 °C, max. 60 seconds	110 W
	Relative humidity	Non-condensing 5% to 95% RH
	Altitude	Operating 10,000 feet max.
		Non-operating 40,000 feet max.
Vibration (See Note 11)	5-500 Hz	2.4 G approx.

Specifications Contd.

Rev.02.16.07
NFS110 Series
3 of 4

OUTPUT VOLTAGE	OUTPUT CURRENTS			RIPPLE ⁽⁴⁾	TOTAL REGULATION ⁽⁵⁾	MODEL NUMBERS ^(13,14,F)
	MAX ⁽¹⁾	PEAK ⁽²⁾	FAN ⁽³⁾			
+5.1 V	8 A	20 A	10 A	50 mV	±2.0%	NFS110-7601PJ
+12 V	4.5 A	9 A	5 A	120 mV	±3.0%	
-12 V	0.5 A	1.5 A	1 A	120 mV	±3.0%	
-5 V	0.5 A	1.5 A	1 A	50 mV	±3.0%	
+5.1 V (I _A)	8 A	20 A	10 A	50 mV	±2.0%	NFS110-7602PJ ⁽⁶⁾
+24 V (I _B) ⁽⁶⁾	3.5 A	4.5 A	4.5 A	240 mV	+10/-5.0%	
+12 V	4.5 A	9 A	5 A	120 mV	±3.0%	
-12 V	0.5 A	1.5 A	1 A	120 mV	±3.0%	
+5.1 V	8 A	20 A	10 A	50 mV	±2.0%	NFS110-7604PJ
+15 V	4 A	7.5 A	5 A	150 mV	±3.0%	
-15 V	0.5 A	1.5 A	1 A	150 mV	±3.0%	
-5 V	0.5 A	1.5 A	1 A	50 mV	±3.0%	
5.1 V	16 A	22 A	20 A	50 mV	±2.0%	NFS110-7605J ^(7,8)
12 V	7 A	9 A	9 A	120 mV	±2.0%	NFS110-7612J ^(7,8)
15 V	5 A	7.3 A	7.3 A	150 mV	±2.0%	NFS110-7615J ^(7,8)
24 V	3.5 A	4.5 A	4.5 A	240 mV	±2.0%	NFS110-7624J ^(7,8)

Notes

- 1 Convection cooled, 80 W maximum.
- 2 Peak outputs lasting less than 60 seconds with duty cycle less than 10%. Total peak power must not exceed 110 W.
- 3 Forced air, 20 CFM at 1 atmosphere, 110 W maximum.
- 4 Figure is peak-to-peak. Output ripple is measured across a 50 MHz bandwidth using a 12 inch twisted pair terminated with a 47 μ F capacitor.
- 5 Total regulation is defined as the static output regulation at 25 °C, including initial tolerance, line voltage within stated limits and output voltages adjusted to their factory settings.
- 6 To achieve stated regulation on the 24 V output on the NFS110-7602PJ, the following load condition must be true: $I_A / I_B \leq 5$, where:
I_A = +5.1 V output current, and
I_B = +24 V output current
The +24 V output will maintain ±5.0% regulation under the following additional condition: I_A ≤ 5 A.
- 7 Single output models have floating outputs which may be referenced as either positive or negative. Higher voltage supplies may be adjusted over a wide output voltage range, as long as the total output power does not exceed 80 Watts (natural convection) or 110 Watts (forced air).
- 8 Power fail detect not available on single output models.
- 9 Derating curve is application specific for ambient temperatures >50 °C, for optimum reliability no part of the heatsink should exceed 90 °C and no semiconductor case temperature should exceed 100 °C.
- 10 Caution: Allow a minimum of 1 second after disconnecting the power when making thermal measurements.
- 11 Three orthogonal axes, random vibration, 10 minute test for each axis.
- 12 This product is only for inclusion by professional installers within other equipment and must not be operated as a stand alone product.
- 13 Artesyn Technologies recommends a minimum load of 11 W to achieve the design MTBF. See the derating curve on page 3.
- 14 The 'J' suffix indicates that these parts are Pb-free (RoHS 6/6) compliant. TSE RoHS 5/6 (non Pb-free) compliant versions may be available on special request, please contact your local sales representative for details.
- 15 NOTICE: Some models do not support all options. Please contact your local Artesyn representative or use the on-line model number search tool at <http://www.artesyn.com/powergroup/products.htm> to find a suitable alternative.

TRANSIENT RESPONSE

NFS110-7601PJ	+5.1 V (7.5 A to 10 A)	150 mV peak, 1 ms recovery
	+12 V (2.5 A to 5 A)	100 mV peak, 0.5 ms recovery
	-12 V (0.5 A to 1 A)	100 mV peak, 0.5 ms recovery
	-5 V (0.5 A to 1 A)	100 mV peak, 0.5 ms recovery
NFS110-7602PJ	+5.1V (7.5 A to 10 A)	150 mV peak, 1 ms recovery
	+24 V (1.5 A to 3 A)	300 mV peak, 1 ms recovery
	+12 V (2.5 A to 5 A)	100 mV peak, 0.5 ms recovery
	-12 V (0.5 A to 1 A)	100 mV peak, 0.5 ms recovery
NFS110-7604PJ	+5.1 V (7.5 A to 10 A)	150 mV peak, 1 ms recovery
	+15 V (2.5 A to 5 A)	100 mV peak, 0.5 ms recovery
	-15 V (0.5 A to 1 A)	100 mV peak, 0.5 ms recovery
	-5 V (0.5 A to 1 A)	100 mV peak, 0.5 ms recovery
NFS110-7605J	+5.1 V (10 A to 20 A)	250 mV peak, 1 ms recovery
NFS110-7612J	+12 V (4.5 A to 9 A)	360 mV peak, 1 ms recovery
NFS110-7615J	+15 V (3.65 A to 7.3 A)	450 mV peak, 1 ms recovery
NFS110-7624J	+24V (2.25 A to 4.5 A)	720 mV peak, 1 ms recovery

Americas

5810 Van Allen Way
Carlsbad, CA 92008
USA
Telephone: +1 760 930 4600
Facsimile: +1 760 930 0698

Europe (UK)

Waterfront Business Park
Merry Hill, Dudley
West Midlands, DY5 1LX
United Kingdom
Telephone: +44 (0) 1384 842 211
Facsimile: +44 (0) 1384 843 355

Asia (HK)

16th - 17th Floors, Lu Plaza
2 Wing Yip Street, Kwun Tong
Kowloon, Hong Kong
Telephone: +852 2176 3333
Facsimile: +852 2176 3888

For global contact, visit:

www.powerconversion.com

technicalsupport@powerconversion.com

While every precaution has been taken to ensure accuracy and completeness in this literature, Emerson Network Power assumes no responsibility, and disclaims all liability for damages resulting from use of this information or for any errors or omissions.

Emerson Network Power.

The global leader in enabling
business-critical continuity.

- AC Power
- Connectivity
- DC Power
- **Embedded Power**
- Inbound Power
- Integrated Cabinet Solutions
- Outside Plant
- Precision Cooling
- Site Monitoring and Services

EmersonNetworkPower. com

Emerson Network Power and the Emerson Network Power logo are trademarks and service marks of Emerson Electric Co.
©2007 Emerson Electric Co.