





	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△						△				
△						△				
△						△				

RECOMMEND PC BOARD HOLE PATTERN



PART NO.	CODE NO.	2		A	B
A2- 1PA-2.54DSA(71)	CL620-0051-5-71	1	2.24	—	—
A2- 2PA-2.54DSA(71)	CL620-0052-8-71	2	4.78	2.54	2.54
A2- 3PA-2.54DSA(71)	CL620-0053-0-71	3	7.32	5.08	5.08
A2- 4PA-2.54DSA(71)	CL620-0054-3-71	4	9.86	7.62	7.62
A2- 5PA-2.54DSA(71)	CL620-0055-6-71	5	12.40	10.10	10.10
A2- 6PA-2.54DSA(71)	CL620-0056-9-71	6	14.94	12.70	12.70
A2- 7PA-2.54DSA(71)	CL620-0057-1-71	7	17.48	15.24	15.24
A2- 8PA-2.54DSA(71)	CL620-0058-4-71	8	20.02	17.78	17.78
A2- 9PA-2.54DSA(71)	CL620-0059-7-71	9	22.56	20.32	20.32
A2-10PA-2.54DSA(71)	CL620-0060-6-71	10	25.10	22.86	22.86
A2-11PA-2.54DSA(71)	CL620-0061-9-71	11	27.64	25.40	25.40
A2-12PA-2.54DSA(71)	CL620-0062-1-71	12	30.18	27.94	27.94
A2-13PA-2.54DSA(71)	CL620-0063-4-71	13	32.72	30.48	30.48
A2-14PA-2.54DSA(71)	CL620-0064-7-71	14	35.26	33.02	33.02
A2-15PA-2.54DSA(71)	CL620-0065-0-71	15	37.80	35.56	35.56
A2-16PA-2.54DSA(71)	CL620-0066-2-71	16	40.34	38.10	38.10
A2-17PA-2.54DSA(71)	CL620-0067-5-71	17	42.88	40.64	40.64
A2-18PA-2.54DSA(71)	CL620-0068-8-71	18	45.42	43.18	43.18
A2-19PA-2.54DSA(71)	CL620-0069-0-71	19	47.96	45.72	45.72
A2-20PA-2.54DSA(71)	CL620-0070-0-71	20	50.50	48.26	48.26



NOTES 1. THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.
2. NUMBER OF CONTACTS.

1	POLYBUTYLENE TEREPHTHALATE	BLACK	UL94V-0	2	BRASS	CONTACT AREA : GOLD 0.2μm min.	
						DIP AREA : TIN-PLATING 2μm min.	
						UNDER PLATING : NICKEL 2.5μm min.	
NO.	MATERIAL	FINISH, REMARKS		NO.	MATERIAL	FINISH, REMARKS	
CODE NO. (OLD)				DRAWN	DESIGNED	CHECKED	APPROVED
CL				A. SUZUKAWA	T. L. Doi	K. Ogawa	H. Okawa
				05.10.07	05.10.07	05.10.07	05.10.11
DRAWING NO.		PART NO.					
EDC3-018389-21		A2-※※PA-2.54DSA(71)					
SCALE	FREE	CODE NO.		CL 620			
UNITS	mm	HIROSE ELECTRIC CO., LTD		1/1			

TO	PCK			
----	-----	--	--	--