








FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE TABLEFIGURE "A"
RECOMMENDED PCB
MOUNTING PAD PATTERN

mat'l. code				surface		tolerance	projection	product family		
-				ISO 1302		ISO 406 ISO 1101		RIBCAGE		
ltr	ecn	no	dr	date	tolerances unless otherwise specified		INCH/MM	title		
AC	ELX-N-16109	GM		10/15/13	angles	linear		.050 CC VERT. C.C. ASS'Y.		
V	M05-0123	MHT		06/06/05				SUR. MOUNT-POL.		
W	M06-0225	ERE		06/12/06	0'±2'		scale 4:1			
X	M06-0370	MHT		09/26/06	dr	D. SHEAFFER		dwg no		
Y	M08-0053	MHT		02/27/08	enrg	J. OSWALD		sheet 1 of 3 size		
AA	M09-0058	CMR		4/06/09	chr	J. OSWALD		87022 A3		
AB	ELX-N-010200	YO		02/07/12	appd	J. OSWALD		type Product Customer Drawing		
sheet	revision	AC	AC	AC						
index	sheet	1	2	3						


PRODUCT NO. NOTE 3, 9	SIZE	DIM A	DIM B	SPECIAL PACKAGING	TAPE WIDTH PITCH	PCS. PER REEL
87022-X05	2 X 5	.266/6.76	.200/5.08	NOTE 7	24mm 12mm	750
-X10	2 X 10	.516/13.11	.450/11.43	NOTE 7	24mm 12mm	750
-X15	2 X 15	.766/19.46	.700/17.78	NOTE 7	44mm 12mm	500
-X20	2 X 20	1.016/25.81	.950/24.13	NOTE 7	44mm 12mm	500
-X25	2 X 25	1.266/32.16	1.200/30.48	NOTE 7	44mm 12mm	500
-X30	2 X 30	1.516/38.51	1.450/36.83	NO	—	—
-X35	2 X 35	1.766/44.86	1.700/43.18	NO	—	—
-X40	2 X 40	2.016/51.21	1.950/49.53	NO	—	—
-X45	2 X 45	2.266/57.56	2.200/55.88	NO	—	—
87022-X50	2 X 50	2.516/63.91	2.450/63.23	NO	—	—
87022-X25 MIL.	2 X 25	1.266/32.16	1.200/30.48	NO	—	—

NOTE 6

NOTES :

- HOUSING MATERIAL :
LCP GLASS FILLED . FLAME RETARDANT PER UL94V-0.
COLOR : NATURAL
- TERMINAL MATERIAL : BeCu
- TERMINAL PLATING :
3.1 87022-6XX
30u"/.76u MIN GOLD OR GXT OVER Ni ON CONTACT ZONES.
100u"/2.54u MIN Sn. OVER Ni IN SOLDERING ZONES.
OTHERWISE GOLD FLASH OR UNPLATED. MATTE TIN FINISH
AT SOLDERING ZONE.
3.2 87022-1XX
30u"/.76u MIN GOLD OVER Ni ON CONTACT ZONES.
GOLD FLASH OVER Ni IN OTHER ALL ZONES.
- APPLICATION INFORMATION:
A. RECOMMENDED MOUNTING PAD PATTERN IS
SHOWN IN FIGURE "A".
B. MATING PINS TO BE .0176/0.447 TO .0181/0.459 DIA.
C. MATING PIN TIPS TO BE IN TRUE POSITION TO MATING
GRID WITHIN .008/0.20 DIA.
D. SUGGESTED MATING PIN LENGTH .130/3.30
±.010/0.25.

- LEAD TIPS TO BE ABOVE HEEL, UP TO .007/0.18 MAX.
COPLANARITY TO BE MEASURED AT LOWEST POINT (HEEL).
- SOLDERTAIL SHALL BE FINISHED IN ACCORDANCE WITH MIL-STD-1276.
HOT SOLDER DIP (FINISH 51) OR FUSED (REFLOWED) TIN LEAD PLATE
(FINISH 34). 100u"/2.54u MIN.





- ADD "TR" TO END OF DASH NUMBER FOR TAPE AND REEL PACKAGING
WITH CAP. TOOLED ONLY FOR NOTED CONNECTORS.
- ADD "CT" TO END OF DASH NUMBER FOR CONNECTOR WITH
VACUUM CAP IN TUBE.
- ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 20 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW
OVEN. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.
- PRODUCT SPEC PER BUS-12-087.

mat'l. code				surface	tolerance	projection	product family		
—				ISO 1302 ✓	ISO 406 ISO 1101	⊕	RIBCAGE		
ltr	ecn	no	dr	date	tolerances unless otherwise specified	INCH/MM scale 4:1	title		
AC					angles		.050 CC VERT. C.C. ASS'Y.		
					linear		SUR. MOUNT-POL.		
					0°±2'		dwg no		
					dr	D. SHEAFFER	12/6/88	sheet 2 of 3	size
					enrg	J. OSWALD	12/6/88	87022	A3
					chr	J. OSWALD	12/6/88	type Product Customer Drawing	
					appd	J. OSWALD	12/6/88		
sheet	revision								
index	sheet								




FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE TABLE

SECTION A-A



SECTION B-B

mat'l. code		surface		tolerance	projection	product family	
-		ISO 1302 ✓		ISO 406 ISO 1101		RIBCAGE	
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
AC					angles	.XX±.01/0.3	.050 CC VERT. C.C. ASS'Y. SUR. MOUNT-POL.
					linear	.XXX±.005/0.13	
					0°±2'	.XXX±.0020/0.051	
				dr	D. SHEAFFER	12/6/88	dwg no
				enr	J. OSWALD	12/6/88	
				chr	J. OSWALD	12/6/88	type
				app	J. OSWALD	12/6/88	
sheet	revision						Product Customer Drawing
index	sheet						