







YM = date code



P.C. LAYOUT



Y	Manufacturing year
8	2008
9	2009
0	2010
1	2011
2	2012

M	Manufacturing month
1	January
...	...
9	September
0	October
N	November
D	December

x	Code
0	hexadecimal real
1	hexadecimal inverse




Tolerances:			Date	Name	SMR 13x16 T
			02/09	dr	
			knitter-switch		30 17 24
Tolerances	10/11	dr			
Date code	03/10	dr			Page
Modifications	Date	Name			1/2


Specifications:

Contact rating:	max.: non-switching: 100mA, 50V DC
	switching: 100mA, 5V DC
	min.: 1µA, 20mV AC or DC
Contact resistance:	200mOhm max. at 1.5mA; 0.2mV AC (1kHz)
Insulation resistance:	1 000MOhm min. at 100V DC
Dielectric strength:	250V AC for 1 minute
Operating temperature:	-25°C to +75°C
Storage temperature:	-40°C to +85°C
Mechanical life:	20 000 cycles min.
Operating force:	24.5mN.m max.
Soldering conditions:	reflow soldering: see soldering profile
Material:	Terminal: phosphor bronze, gold over nickel plated
	Base: liquid crystal polymer, black
	Frame: stainless steel
	Rotor: polyamide resin, white
	Fixed contact: phosphor bronze, gold over nickel plated
	Movable contact: beryllium copper, gold over nickel plated

Soldering conditions:



Packaging:



Packaging unit: 2 000 pcs. / tape



Tolerances:			Date	Name	SMR 13x16 T		
			02/09	dr			
					knitter-switch		
					30 17 24		
Modifications	Date	Name					Page 2/2