

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

74162-0454

Status:

Active

Overview:

C-Grid® Products

Description:

2.54mm Pitch C-Grid® Receptacle, Right Angle, Through Hole, Dual Row, Shrouded, Version A, High-Temperature, 54 Circuits, 0.80µm Gold (Au)

Documents:

3D Model

Drawing (PDF)

Product Specification PS-74162-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Overview

Product Name

UPC

PCB Receptacles

74162

Board-to-Board, Signal

C-Grid® Products

C-Grid®

883906879686

Physical

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

Flammability

Glow-Wire Compliant

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Polarized to Mating Part

Polarized to PCB

Robotic Placement

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

54

54

Black

50

94V-0

No

No

None

Yes

Phosphor Bronze

Gold

Tin

High Performance Thermoplastic

10.686/g

2

Right Angle

No

None

3.18mm

Tube

2.54mm

2.54mm

0.762µm

No

No

None

No

No

-40°C to +105°C

Through Hole


Electrical

Current - Maximum per Contact

Grounding to PCB

2.5A

No



EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

74162Series

Voltage - Maximum	250V
-------------------	------

Solder Process Data

Duration at Max. Process Temperature (seconds)	5
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Product Specification	PS-74162-001
Sales Drawing	SD-74162-001

This document was generated on 07/11/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

74162-0454