



Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207
Tel: 1-800-52 ALPHA (25742), Web: www.alphawire.com

Customer Specification

PART NO. 45132

Construction

		Diameters (In)						
1) Component 1	2 X 1 PAIR							
a) Conductor	18 (16/30) AWG TC	0.047						
b) Insulation	0.016" Wall, Nom. TPE	0.079						
(1) Color Code	Alpha Wire Color Code B							
Pair	Color	Pair	Color	Pair	Color			
1	WHITE-BLACK	2	WHITE-BROWN					
c) Pair	2/Cond Cabled Together							
(1) Twists:	5.3 Twists/foot (min)							
2) Cable Assembly	2 Components Cabled							
a) Twists:	4.0 Twists/foot (min)							
b) Core Wrap	Nonwoven Polyester Tape, 25% Overlap, Min.							
3) Shield:	A/P/A Tape, 25% Overlap, Min.							
a) Drain Wire	18 (16/30) AWG TC							
b) Braid	TC,70% Coverage, Min.							
4) Jacket	0.045" Wall, Nom.,TPE	0.381 (0.395 Max.)						
a) Color(s)	Slate, Black, Yellow, Orange, Blue, Green, Red, Sand Beige, White							
b) Ripcord	1 End 810 Denier Nylon							
c) Print	ALPHA WIRE-* P/N 45132 2PR 18 AWG XTRAGUARD(R) 4 (UL) TYPE PLTC 105C OR AWM 20237 125C 300 VOLTS -- LLXXXXX CSA AWM I/II A/B 125C 300 VOLTS FT1 P-07-KA070017-MSHA CE (SEQ FOOTAGE) * = Factory Code [Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]							

Applicable Specifications

1) UL	AWM/STYLE 20237	125°C / 300 V _{RMS}
	PLTC	105°C
2) CSA International	AWM I/II A/B	125°C / 300 V _{RMS}
	FT1	
3) Other	PENNSYLVANIA BUREAU OF MINE SAFETY APPROVED	
4) CE:	EU Low Voltage Directive 2006/95/EC	

Environmental

1) EU Directive 2002/95/EC(RoHS):	All materials used in the manufacture of this part are compliant with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment under the now annulled Exemption 9A which allowed Deca-BDE. Alpha Wire is working to completely remove PBDE's from all products. Consult Alpha Wire's web site for compliance Date of Manufacture.
2) California Proposition 65:	The outer surface materials used in the manufacture of this part meet the requirements of California Proposition 65.

Properties

Physical & Mechanical Properties	
1) Temperature Range	-50 to 125°C
2) Bend Radius	10X Cable Diameter
3) Pull Tension	68 Lbs, Maximum
4) Sunlight Resistance	Yes
Electrical Properties	(For Engineering purposes only)
1) Voltage Rating	300 V _{RMS}
2) Mutual Capacitance	22.2 pf/ft @1 kHz, Nominal
3) Ground Capacitance	40 pf/ft @1 kHz, Nominal
4) Characteristic Impedance	67
5) Inductance	0.18 µH/ft, Nominal
6) Conductor DCR	7.3 /1000ft @20°C, Nominal
7) OA Shield DCR	2.28 /1000ft @20°C, Nominal

Other

Packaging	Flange x Traverse x Barrel (inches)
a) 1000 FT	20 x 11 x 8 Continuous length
b) 500 FT	16 x 11 x 8 Continuous length
c) Bulk(Made-to-order)	
<i>[Spool dimensions may vary slightly]</i>	

www.alphawire.com

Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207
Tel: 1-800-52 ALPHA (25742)

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure there accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Alpha Wire:](#)

[45132 BK002](#)