

REVISIONS




P	LTR	DESCRIPTION	DATE	DMN	APVD
A		REVISED	16FEB2010	T.K	E.T
B		REVISED PER ECO-15-000365	09JAN2015	H.W	J.Y

LOC DIST




J

1 MATERIAL: HOUSIN: THERMOPLASTIC (UL 94V-0) BLACK.
CONTACT: COPPER ALLOY
SOLDER PEG: COPPER ALLOY

2 FINISH: CONTACT: Au PL. CONTACT AREA.
TIN PL. AT TINE AREA, OVER Ni UNDER PL.
SOLDER PEG: TIN PL., OVER Ni UNDER PL.



DETAIL J
(SCALE 4:1)




-2 ; AS SHOWN

0.0003 MIN.	51.2	50.6	44.6	43.6	42.07	38.63	36.83	29	60	1-5179656-2
0.00076 MIN.	51.2	50.6	44.6	43.6	42.07	38.63	36.83	29	60	2-5179656-2
0.0003 MIN.	63.9	63.3	57.3	56.3	54.77	51.33	49.53	39	80	5179656-3
0.0003 MIN.	51.2	50.6	44.6	43.6	42.07	38.63	36.83	29	60	5179656-2
Au PL. THICKNESS	G	F	E	D	C	B	A	n	POS	P/N

DMN	ROY HAO	30AUG04	NAME	Tyco Electronics AMP K.K.
CHK	STEVEN YAO	30AUG04	NAME	Kowosaki, Japon

THIS DRAWING IS A CONTROLLED DOCUMENT.
DIMENSIONS: mm
TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± 0.2
1 PLC ± 0.2
2 PLC ± 0.2
3 PLC ± 0.2
4 PLC ± 0.2
FINISH ± 3

RECOMMENDED P.C.B LAYOUT
(CONNECTOR MOUNT SIDE)

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:									
mm											
											
0 PLC		± 0.2									
1 PLC		± 0.2									
2 PLC		± 0.2									
3 PLC		± 0.2									
4. PLC		± 0.2									
ANGLES		± 3°									
FINISH											
											
MATERIAL											

APVD	I. ENOMOTO		30AUG04	NAME								
PRODUCT SPEC				AMP FH CONNECTOR								
108-60042				PLUG, SMT, WITH SOLDER PEG								
APPLICATION SPEC												
WEIGHT				SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO					
				A3	00779	G=5179656	-					
CUSTOMER DRAWING				SCALE		NTS	SHEET	1	OF	1	REV	B