





- ? [Circuit Board Indicators](#)
- ? [Panel Mount Indicators](#)
- ? [Solid State Lighting](#)
- ? [Traffic Signals](#)
- ? [Vehicle Lighting](#)
- ? [Rail Obstruction Lighting](#)
- ? [Hazardous Area Lighting](#)
- ? [Heliport Lighting](#)



Region:

Product Line:

Circuit Board Indicators



Check stock with our distributors now.


5973405602F

Please note that the stock check is **only applicable** to products *within* **Circuit Board Indicators** and **Panel Mount Indicators**.




Please select a Product Line to search.

Circuit Board Indicators



Part No.:

Text Search:

[Dialight Corporate Video](#)

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp.

[View PDF File](#)

[Application Notes](#)
[FAQs](#)

[Dialight Ltd \(UK\)](#)
[Dialight Garufo](#)
[Dialight BLP](#)
[LumiDrives](#)

menu rendered

Circuit Board Indicators - Surface Mount Indicators	
P/N#	0805 Single Color
5973405602F	

Description

Reverse Current	100 @ Vr =5V
Forward Current	25 mA
Continuous	100 mA
Forward Current Pulse	from 50 $^{\circ}$ @ .4mA/ $^{\circ}$ C
Derating	5 V
Reverse Voltage	260 $^{\circ}$ for 5 sec
Solder Temp	-30~+85 $^{\circ}$ C
Operating Temp	-25~+75 $^{\circ}$ C
Storage Temp	585
Peak Wave Length	



Operating Characteristics	
LED Position	
Color	
Lamp Type	
LED Type	
Intensity Min (mcd)	
Intensity Typ (mcd)	
Intensity Max (mcd)	
Fwd Voltage Min	
Fwd Voltage Typ	
Fwd Voltage Max	
Dom Wavelength Min (nm)	
Dom Wavelength Typ (nm)	
Dom Wavelength Max (nm)	
Power Dissipation Max (mW)	
Backlighting	
Pitch Between Vertical	
Pitch Between Horizontal	
Lum Intensity Min	
Lum Intensity Typ	
Lum Intensity Max	

Distributor Stock Check

Check stock with our distributors now.

5973405602F

