

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0460152204

Status:

Obsolete

Overview:

minifit_plus_hcs

Description:

4.20mm (.165") Pitch Mini-Fit® Plus HCS Header, Dual Row, Vertical, 22 Circuits, without Snap-in Plastic Peg PCB Lock, with Drain Holes, PA Polyamide Nylon 6/6, UL 94V-2, Tin (Sn) 1.27µm (50µ") Over Nickel (Ni) Plating

Documents:

[Drawing \(PDF\)](#)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Comments

Overview

Product Name

PCB Headers

46015

Power, Wire-to-Board

Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 Mini-Fit Plus® HCS Crimp Terminal Crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current de-rating information.

minifit_plus_hcs

Mini-Fit® Plus HCS

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Glow-Wire Compliant

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Number of Rows

Orientation

PC Tail Length

PCB Locator

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Polarized to PCB

Shrouded

Stackable

Surface Mount Compatible (SMC)

No

22

22

Natural

75

No

94V-2

No

No

None

Yes

Copper Alloy

Tin

Tin

Nylon

2

Vertical

1.80mm (.071")

Yes

None

1.78mm (.070")

Tray

4.20mm (.165")

2.540µm (100µ")

1.270µm (50µ")

Yes

Yes

Fully

No

No



Series

image - Reference only

EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

46015Series

Mates With

5557 Mini-Fit Jr.™ Receptacle Housing

Temperature Range - Operating
Termination Interface: Style

-40°C to +105°C
Through Hole

Electrical

Current - Maximum per Contact
Voltage - Maximum

13A
600V

Material Info

This document was generated on 05/11/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION