

## Series AM15E-IZ

### 15 Watt | DC-DC Converter



#### FEATURES:

- RoHS compliant
- 2:1 input range
- Low ripple and noise
- Remote On/Off control
- Power modules for PCB mounting
- Regulated output
- Operating temperature range: -40 to +85°C
- Synchronous rectifier



#### Models Single output

| Model            | Input Voltage (V) | Output Voltage (V) | Output Current max (A) | Max. Capacitive load (μF) | Ripple & Noise typ | Isolation (VDC) | Efficiency (%) |
|------------------|-------------------|--------------------|------------------------|---------------------------|--------------------|-----------------|----------------|
| AM15E-1203SIZ    | 9-18              | 3.3                | 4                      | 2000                      | 80mV p-p           | 1500            | 79             |
| AM15E-1205SIZ    | 9-18              | 5                  | 3                      | 1800                      | 80mV p-p           | 1500            | 83             |
| AM15E-1212SIZ    | 9-18              | 12                 | 1.25                   | 680                       | 120mVp-p           | 1500            | 85             |
| AM15E-1215SIZ    | 9-18              | 15                 | 1                      | 470                       | 150mVp-p           | 1500            | 85             |
| AM15E-2403SIZ    | 18-36             | 3.3                | 4                      | 2000                      | 80mV p-p           | 1500            | 81             |
| AM15E-2405SIZ    | 18-36             | 5                  | 3                      | 3300                      | 80mV p-p           | 1500            | 83             |
| AM15E-2412SIZ    | 18-36             | 12                 | 1.25                   | 680                       | 120mVp-p           | 1500            | 88             |
| AM15E-2415SIZ    | 18-36             | 15                 | 1                      | 470                       | 150mVp-p           | 1500            | 87             |
| AM15E-4803SIZ    | 36-75             | 3.3                | 4                      | 2000                      | 80mV p-p           | 1500            | 81             |
| AM15E-4805SIZ    | 36-75             | 5                  | 3                      | 3300                      | 80mV p-p           | 1500            | 83             |
| AM15E-4812SIZ    | 36-75             | 12                 | 1.25                   | 680                       | 120mVp-p           | 1500            | 88             |
| AM15E-4815SIZ    | 36-75             | 15                 | 1                      | 470                       | 150mVp-p           | 1500            | 87             |
|                  |                   |                    |                        |                           |                    |                 |                |
| AM15E-1203SH30IZ | 9-18              | 3.3                | 4                      | 8100                      | 80mV p-p           | 3000            | 74             |
| AM15E-1205SH30IZ | 9-18              | 5                  | 3                      | 4700                      | 80mV p-p           | 3000            | 78             |
| AM15E-1212SH30IZ | 9-18              | 12                 | 1.25                   | 680                       | 120mVp-p           | 3000            | 82             |
| AM15E-1215SH30IZ | 9-18              | 15                 | 1                      | 470                       | 150mVp-p           | 3000            | 83             |
| AM15E-2403SH30IZ | 18-36             | 3.3                | 4                      | 8100                      | 80mV p-p           | 3000            | 75             |
| AM15E-2405SH30IZ | 18-36             | 5                  | 3                      | 4700                      | 80mV p-p           | 3000            | 77             |
| AM15E-2412SH30IZ | 18-36             | 12                 | 1.25                   | 680                       | 120mVp-p           | 3000            | 84             |
| AM15E-2415SH30IZ | 18-36             | 15                 | 1                      | 470                       | 150mVp-p           | 3000            | 83             |
| AM15E-4803SH30IZ | 36-75             | 3.3                | 4                      | 8100                      | 80mV p-p           | 3000            | 75             |
| AM15E-4805SH30IZ | 36-75             | 5                  | 3                      | 4700                      | 80mV p-p           | 3000            | 76             |
| AM15E-4812SH30IZ | 36-75             | 12                 | 1.25                   | 680                       | 120mVp-p           | 3000            | 85             |
| AM15E-4815SH30IZ | 36-75             | 15                 | 1                      | 470                       | 150mVp-p           | 3000            | 85             |

#### Models Dual output

| Model            | Input Voltage (V) | Output Voltage (V) | Output Current max (A) | Max. Capacitive load (μF) | Ripple & Noise typ | Isolation (VDC) | Efficiency (%) |
|------------------|-------------------|--------------------|------------------------|---------------------------|--------------------|-----------------|----------------|
| AM15E-1205DIZ    | 9-18              | ±5                 | ±1.5                   | ±330                      | 50mVp-p            | 1500            | 85             |
| AM15E-1212DIZ    | 9-18              | ±12                | ±0.62                  | ±220                      | 120mVp-p           | 1500            | 85             |
| AM15E-1215DIZ    | 9-18              | ±15                | ±0.5                   | ±200                      | 150mVp-p           | 1500            | 85             |
| AM15E-2405DIZ    | 18-36             | ±5                 | ±1.5                   | ±330                      | 50mVp-p            | 1500            | 83             |
| AM15E-2412DIZ    | 18-36             | ±12                | ±0.62                  | ±220                      | 120mVp-p           | 1500            | 88             |
| AM15E-2415DIZ    | 18-36             | ±15                | ±0.5                   | ±200                      | 150mVp-p           | 1500            | 87             |
| AM15E-4805DIZ    | 36-75             | ±5                 | ±1.5                   | ±330                      | 50mVp-p            | 1500            | 83             |
| AM15E-4812DIZ    | 36-75             | ±12                | ±0.62                  | ±220                      | 120mVp-p           | 1500            | 88             |
| AM15E-4815DIZ    | 36-75             | ±15                | ±0.5                   | ±200                      | 150mVp-p           | 1500            | 87             |
|                  |                   |                    |                        |                           |                    |                 |                |
| AM15E-1205DH30IZ | 9-18              | ±5                 | ±1.5                   | ±2300                     | 50mVp-p            | 3000            | 78             |
| AM15E-1212DH30IZ | 9-18              | ±12                | ±0.62                  | ±340                      | 120mVp-p           | 3000            | 82             |

### Models

#### Dual output (continued)

| Model            | Input Voltage (V) | Output Voltage (V) | Output Current max (A) | Max. Capacitive load (μF) | Ripple & Noise typ | Isolation (VDC) | Efficiency (%) |
|------------------|-------------------|--------------------|------------------------|---------------------------|--------------------|-----------------|----------------|
| AM15E-1215DH30IZ | 9-18              | ±15                | ±0.5                   | ±230                      | 150mVp-p           | 3000            | 81             |
| AM15E-2405DH30IZ | 18-36             | ±5                 | ±1.5                   | ±2300                     | 50mVp-p            | 3000            | 80             |
| AM15E-2412DH30IZ | 18-36             | ±12                | ±0.62                  | ±340                      | 120mVp-p           | 3000            | 82             |
| AM15E-2415DH30IZ | 18-36             | ±15                | ±0.5                   | ±230                      | 150mVp-p           | 3000            | 84             |
| AM15E-4805DH30IZ | 36-75             | ±5                 | ±1.5                   | ±2300                     | 50mVp-p            | 3000            | 76             |
| AM15E-4812DH30IZ | 36-75             | ±12                | ±0.62                  | ±340                      | 120mVp-p           | 3000            | 83             |
| AM15E-4815DH30IZ | 36-75             | ±15                | ±0.5                   | ±230                      | 150mVp-p           | 3000            | 85             |

NOTE: All specifications in this datasheet are measured at an ambient temperature of 25°C, humidity<75%, nominal input voltage and at rated output load unless otherwise specified.

### Input Specifications

| Parameters                            | Nominal        | Typical                                                                    | Maximum | Units |
|---------------------------------------|----------------|----------------------------------------------------------------------------|---------|-------|
| Voltage range                         | 12             | 9-18                                                                       |         | VDC   |
|                                       | 24             | 18-36                                                                      |         |       |
|                                       | 48             | 37-75                                                                      |         |       |
| Filter                                | π (Pi) Network |                                                                            |         |       |
| Remote On/Off Control                 | On             | 3.5 to 12VDC or open circuit                                               |         |       |
|                                       | Off            | 0 to 1.2VDC or short circuit between pin 2 and 4; typical idle current 3mA |         |       |
| Absolute Maximum Rating               | 12 Vin         |                                                                            | 25      | VDC   |
|                                       | 24 Vin         |                                                                            | 50      |       |
|                                       | 48 Vin         |                                                                            | 100     |       |
| Permissible absolute maximum duration |                |                                                                            | 2       | h     |
| Recommended Input Fuse (slow blow)    | 12 Vin         | 4A/250V                                                                    |         |       |
|                                       | 24 Vin         | 2A/250V                                                                    |         |       |
|                                       | 48 Vin         | 1A/250V                                                                    |         |       |

### Isolation Specifications

| Parameters         | Conditions | Typical     | Maximum | Units |
|--------------------|------------|-------------|---------|-------|
| Tested I/O voltage | 3 sec      | 1500 & 3000 |         | VDC   |
| Resistance         |            | > 1000      |         | MOhm  |
| Capacitance        |            | 1000        |         | pF    |

### Output Specifications

| Parameters                       | Conditions                             | Typical | Maximum | Units |
|----------------------------------|----------------------------------------|---------|---------|-------|
| Voltage accuracy                 |                                        | ±2      |         | %     |
| Short Circuit protection         | Continuous                             |         |         |       |
| Short Circuit restart            | Auto recovery                          |         |         |       |
| Over voltage protection          | Zener diode clamp protection           |         |         |       |
| Over load protection             | Over 110% full load with auto-recovery |         |         |       |
| Line voltage regulation          | HL-LL                                  | ±0.5    |         | %     |
| Load voltage regulation (Single) | 0-100%                                 | ±0.5    |         | %     |
| Load voltage regulation (Dual)   | 0-100%                                 | ±2      |         | %     |
| Temperature coefficient          |                                        | ±0.05   |         | %/°C  |
| Transient response recovery time | 25% load step change                   | 300     |         | μS    |

## General Specifications

| Parameters               | Conditions           | Typical                                                | Maximum                  | Units |
|--------------------------|----------------------|--------------------------------------------------------|--------------------------|-------|
| Switching frequency      | 100% load            | 200                                                    |                          | KHz   |
| Operating temperature    | See derating curves  | -40 to +85                                             |                          | °C    |
| Storage temperature      |                      | -55 to +115                                            |                          | °C    |
| Maximum Case temperature |                      |                                                        | 95                       | °C    |
| Cooling                  | Free air convection  |                                                        |                          |       |
| Humidity                 |                      |                                                        | 95                       | %     |
| Case material            | Nickel coated copper |                                                        |                          |       |
| Weight                   |                      | 33                                                     |                          | g     |
| Dimensions (L x W x H)   |                      | 2.00 x 1.00 x 0.40 inches                              | 50.80 x 25.40 x 10.50 mm |       |
| MTBF                     |                      | > 800 000 hrs (MIL-HDBK -217F, Ground Benign, t=+25°C) |                          |       |

## Safety Specifications


| Parameters       |                            |
|------------------|----------------------------|
| Agency approvals | CE                         |
| Standards        | EN 55022, EN 55024 class B |

## Pin Out Specifications


| Pin | Single         | Dual           |
|-----|----------------|----------------|
| 1   | On/Off Control | On/Off Control |
| 2   | -V Input       | -V Input       |
| 3   | +V Input       | +V Input       |
| 4   | -V Output      | -V Output      |
| 5   | No pin         | Common         |
| 6   | +V Output      | +V Output      |

## Derating


### 1500VDC Isolation



### 3000VDC Isolation




## Dimensions




## Block diagram

### Single Output




### Dual Output




## Control ON/OFF pin connection example:

### Single Output



### Dual Output




The converter output can be disabled by moving SW to position "a". When SW is in position "b", the converter operates normally.

The SW can be replaced by a NPN transistor with connection as follows:

**Note: The control voltage is referenced to negative input (-Vi)**

## Digital Control Circuit:



**NOTE:** 1. Datasheets are updated as needed and as such, specifications are subject to change without notice. Once printed or downloaded, datasheets are no longer controlled by Aimtec; refer to [www.aimtec.com](http://www.aimtec.com) for the most current product specifications. 2. Product labels shown, including safety agency certifications on labels, may vary based on the date manufactured. 3. Mechanical drawings and specifications are for reference only. 4. All specifications are measured at an ambient temperature of 25°C, humidity<75%, nominal input voltage and at rated output load unless otherwise specified. 5. Aimtec may not have conducted destructive testing or chemical analysis on all internal components and chemicals at the time of publishing this document. CAS numbers and other limited information are considered proprietary and may not be available for release. 6. This product is not designed for use in critical life support systems, equipment used in hazardous environments, nuclear control systems or other such applications which necessitate specific safety and regulatory standards other than the ones listed in this datasheet. 7. Warranty is in accordance with Aimtec's standard Terms of Sale available at [www.aimtec.com](http://www.aimtec.com).