




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	M	ECR-16-013251	12JUL2017	FL	SY

D


C

B


A



- NOTES:
- △ MATERIAL CONTACTS; PHOSPHORBRONZE
MATERIAL HOUSING; GLASSFILLED POLYESTER (GRAY)
 - △ GENERAL PLATING SPECIFICATION: UNDERPLATING
(ENTIRE CONTACT): 1,27µm NICKEL MIN.AND ACTION
PIN: 0,5µm TIN-LEAD MIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE
SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
 - △ 3 CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 2.
 - △ 4 CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 1.
 - △ 6 CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA
GR-1217-CORE QUALITY LEVEL III,CENTRAL OFFICE APPLICATIONS.
 - △ 6 CONNECTOR LUBRICATED WITH TELCORDIA GR-1217-CORE
APPROVED LUBRICANT.
 - △ 8 ASSEMBLY PRINTED WITH P/N AND DATECODE
THE MARKING CAN APPEAR ON THE FRONT SIDE
OR BACK SIDE.
 - △ 9 HOLE PATTERN FOR FEMALE CONNECTOR TYPE B
125 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
 - △ 10 ROW "f" 13 PLATED THROUGH HOLES FOR UPPERSHIELD
 - △ 11 SHIELD MOUNTED ON CONNECTOR WITH DOUBLE SIDED
ADHESIVE TAPE OR ADHESIVE
 - 12. BASIC P.N. LOWERSHIELD: 338110
 - △ 13 0.76µm MIN GOLD PLATING AT MATING SURFACES.



COMPONENT SIDE AS SHOWN
RECOMMENDED PCB-HOLE LAY-OUT
SCALE 2,5:1



P.C.B. HOLE DIM. ACTION PIN
FOR DETAILS SEE
APPLICATION SPECIFICATION

OBSELETE	△△△13	△	3-352069-0
OBSELETE	△△△6	△	352069-9
	△△4	△	352069-4
	△△3	△	352069-1
FINISH		MATERIAL	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0-PLC ±
1-PLC ±
2-PLC ±
3-PLC ±
4-PLC ±
ANGLES ±
FINISH

±0.2

DWN
D. TRUREN

CHK
-

APVD
-

20JAN97

PRODUCT SPEC
108-19082

APPLICATION SPEC
114-19029

WEIGHT
0.000000

CUSTOMER DRAWING

TE Connectivity

Z-PACK 2MM HM
TYPE B - 25 COLUMNS
PRE-SHIELDED RECEPTACLE

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=352069

RESTRICTED TO
-

SCALE
NTS

SHEET
1 of 1

REV
M