

PNP TRANSISTORS

IC Amps Max	VCEO (sus) Volts Min	Device Type	hFE @ IC Min	Amps	fT MHz	Watts	PD @ TC °C	Case JEDEC
1	120	2N3795	12	0.01	0.5		100	TO-5
	150	2N5281	20	1.0	20		25	TO-5
2	80	2N4999	30	1.0	50	30	50	TO-59
		2N5001	70	1.0	60	30	50	TO-59
		2N5333	30	1.0	30	15	100	TO-5
3	150	SFT5333	50	2.0	100	15	100	TO-5
	60	2N3868	20	2.5	60	6	25	TO-5
5	80	2N5003	30	2.5	60	50	50	TO-59
		2N5005	70	2.5	70	50	50	TO-59
		2N6190	30	2.0	30	10	25	TO-39
		2N6191	60	2.0	30	10	25	TO-39
		2N5151	30	2.5	60	10	50	TO-5
		2N5153	70	2.5	70	10	50	TO-5
	100	2N6192	30	2.0	30	10	25	TO-5
		2N6193	60	2.0	30	10	25	TO-5
	120	SFD5390P†	1000	5.0	30	15	100	TO-33
	150	SFT501	30	2.5	80	10	50	TO-5
		SFT503	50	2.5	80	10	50	TO-5
10	80	2N5007	30	5	35	100	50	TO-61
		2N5009	70	5	40	100	50	TO-61
		2N6182	30	2	30	60	25	TO-59
		2N6183	60	2	30	60	25	TO-59
		2N6186	30	2	30	60	25	TO-59
		2N6187	60	2	30	60	25	TO-59
		SFT8200	50	5	100	10	25	TO-5
	100	2N6184	30	2	30	60	25	TO-59
		2N6185	60	2	30	60	25	TO-59
		2N6188	30	2	30	60	25	TO-59
		2N6189	60	2	30	60	25	TO-59
30	90	SPT5330	40	10	80	80	100	TO-61
100	150	SFT1001	10	50	50	200	25	TO-3*
		SFT1003	25	50	50	200	25	TO-3*

HIGH VOLTAGE PNP TRANSISTORS

IC (cont.) Amps Max	VCEO (sus) Volts Max	Device Type	hFE @ IC Min	Amps	fT MHz	Watts	PD @ TC °C	Case JEDEC
0.5	250	2N4931	20	0.01	20	1	25	TO-5
	300	2N3743	25	0.03	30	1	25	TO-5
1.0	300	2N5282	20	0.001	20	2	25	TO-5
		2N5091	20	0.01	20	2	25	TO-5
	350	2N5093	20	0.1	20	2	25	TO-5
	400	2N5094	20	0.1	20	2	100	TO-5
	450	2N5096	20	0.1	20	2	100	TO-5
3.0	400	SFT6900	35	0.5	25	5	25	TO-5

* TO - 3 with 60 Mil Pins

Contact SSDI for higher voltage units.

†Darlington