

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
© COPYRIGHT - By -		ALL RIGHTS RESERVED.	
DESCRIPTION	MATERIAL	FINISH	
MODULE ASSEMBLY	EPOXY	COLOR: BLACK	
GROMMET	FLUORSILICONE RUBBER	COLOR: BLUE	
CONTACT SOCKET	BERYLLIUM COPPER PER QQ-C-533	GOLD PLATE PER MIL-G-45204	
RETAINING CLIP	BERYLLIUM COPPER PER QQ-C-533 OR STAINLESS STEEL PER QQ-S-766	NONE	
CONTACTS	COPPER ALLOY PER MIL-C-39029/1	GOLD PLATE PER MIL-G-45204	
SEALING PLUGS	F.E.P. PER MIL-P-19468	COLOR: BLACK	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DF	AO		D	REVISED PER ECD-11-011660	08JUL11	PY	DE

D

C

B




















A

D

C

B

A



BUSSING ARRANGEMENTS 3

- 3 BUSSING ARRANGEMENT OUTLINE DENOTES INTERNAL ARRANGEMENT OF CONTACT SOCKETS.
- 2 MARK MODULE ASSEMBLY WITH CUSTOMER PART NO., MILITARY PART NO. IF REQUIRED .060 MINIMUM HIGH CHARACTERS AT APPROXIMATE AREA SHOWN.
- 1 MARK MODULE ASSEMBLY WITH "AMP", AMP PART NO. AND DATE CODE .060 MINIMUM HIGH CHARACTERS AT APPROXIMATE AREA SHOWN.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	J. MECK	3-10-93	TE Connectivity		
		CHK	R. RYAN	3-31-93			
		APVD	R. RYAN	3-31-93	NAME		
		PRODUCT SPEC			MODULE ASSY, FEED-BACK, SIZE 21, TJ		
		APPLICATION SPEC			-		
		WEIGHT			SIZE	CAGE CODE	DRAWING NO
		-			A2	00779	C=592629
		CUSTOMER DRAWING			SCALE	SHEET	REV
					2: 1	1 of 2	D

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

DF

AO

-

SEE SHEET 1

-

-

-

D

C

B

A

MRTB21D43

MRTB21D39

M81714/17-D30

M81714/17-D45

M81714/17-D36

M81714/17-D43

M81714/17-D42

M81714/17-D41

MRTB21D42

MRTB21D44

MRTB21D37

MRTB21D36

MRTB21D35

MRTB21D34

MRTB21D32

MRTB21D31

MRTB21D30

G383962-1

77A112809-2

M81714/17-D44

M81714/17-D40

M81714/17-D39

M81714/17-D38

M81714/17-D37

M81714/17-D35

M81714/17-D34

M81714/17-D33

M81714/17-D32

M81714/17-D31

MARKING

46

45

44

43

42

40

39

38

37

36

35

34

33

32

31

30

BUSSING

ARRANGEMENTS

SEALING

PLUG

QTY 2

CONTACTS

QTY 11

PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

INCHES

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± -

FINISH -

DWN

J. MECK

3-10-93

CHK

R. RYAN

3-31-93

APVD

R. RYAN

3-31-93

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

TE

TE Connectivity

NAME

-

MODULE ASSY, FEED-BACK, SIZE 21, TJ

-

SIZE

A2

CAGE CODE

00779

DRAWING NO

C=592629

RESTRICTED TO

-

SCALE

2: 1

SHEET

2 of 2

REV

D

592629

1471-9 (3/11)