


## LTA-Series




The LTA-Series Mini Tippet Snap-in rocker switches are illuminated, single pole and double-insulated. These AC rated switches are also suitable for low voltage DC applications. A variety of actuators, colors and terminations can be specified with ratings up to 20 amps.

## Specifications




- Certifications\*: UL, CSA
- Dielectric Strength: 1,000V (minimum)
- Insulation Resistance: 100 Megohms (minimum)
- Base Material: Nylon
- Actuator Material: Nylon or Polycarbonate
- Bezel Material: Nylon

\* Due to ongoing technological advances, consult factory for certification specifics.

## Dimensional Specifications: in. [mm]



|                 |            |                 |                                              |
|-----------------|------------|-----------------|----------------------------------------------|
|                 |            |                 |                                              |
| .250 TAB (Q.C.) | SOLDER LUG | .187 TAB (Q.C.) | INTEGRATED WIRE LEAD (no exposed conductors) |
| TERMINAL TYPE   |            |                 |                                              |



| SERIES             | RATING                  | TERMINATION              | ACTUATOR COLOR                | LENS COLOR <sup>2,3</sup>  |
|--------------------|-------------------------|--------------------------|-------------------------------|----------------------------|
| <b>LTA</b>         | <b>20</b>               | <b>1</b>                 | <b>-</b>                      | <b>T</b>                   |
| <b>OFF-NONE-ON</b> | <b>5A 250VAC</b>        | <b>0 SOLDER LUG</b>      | <b>ROCKER</b>                 | <b>A AMBER</b>             |
| <b>SINGLE POLE</b> | <b>10A 125VAC</b>       | <b>1 .250 TAB (QC)</b>   | <b>A AMBER</b>                | <b>C CLEAR</b>             |
|                    | <b>1/2HP 125-250VAC</b> | <b>3 .187 TAB (QC)</b>   | <b>C CLEAR</b>                | <b>G GREEN</b>             |
|                    | <b>5A 250VAC</b>        | <b>5 WIRE LEAD</b>       | <b>G GREEN<sup>3</sup></b>    | <b>LU BLUE</b>             |
|                    | <b>10A 125VAC</b>       |                          | <b>R RED</b>                  | <b>R RED</b>               |
|                    | <b>5A (TUNGSTEN)</b>    |                          |                               |                            |
|                    | <b>125VAC L</b>         |                          |                               |                            |
|                    | <b>20 10A 250VAC</b>    | <b>ACTUATOR STYLE</b>    | <b>PADDLE<sup>1</sup></b>     | <b>LAMP VOLTAGE</b>        |
|                    | <b>15A 125VAC</b>       | <b>P PADDLE</b>          | <b>B BLACK</b>                | <b>6V 6 VOLT/</b>          |
|                    | <b>3/4HP 125-250VAC</b> | <b>PS PADDLE - SHORT</b> | <b>W WHITE</b>                | <b>INCANDESCENT</b>        |
|                    | <b>21 10A 250VAC</b>    | <b>T LIGHTED ROCKER</b>  |                               | <b>12V 12 VOLT/</b>        |
|                    | <b>15A 125VAC</b>       |                          |                               | <b>INCANDESCENT</b>        |
|                    | <b>22 10A 250VAC</b>    |                          | <b>BASE COLOR<sup>1</sup></b> | <b>18V 18 VOLT/</b>        |
|                    | <b>15A 125VAC</b>       |                          | <b>B BLACK</b>                | <b>INCANDESCENT</b>        |
|                    | <b>20A 125-250VAC H</b> |                          | <b>W WHITE</b>                | <b>24V 24 VOLT/</b>        |
|                    | <b>3/4HP 125-250VAC</b> |                          |                               | <b>INCANDESCENT</b>        |
|                    |                         |                          |                               | <b>28V 28 VOLT/</b>        |
|                    |                         |                          |                               | <b>INCANDESCENT</b>        |
|                    |                         |                          |                               | <b>125N 125 VOLT/ NEON</b> |
|                    |                         |                          |                               | <b>250N 250 VOLT/ NEON</b> |

## NOTES:

Shading indicates standard configurations. Stainless steel bezels are available. Add suffix "BEZEL" to the end of the catalog number. (ex.) LTA201-TR-B/12V/BEZEL

Imprinting is available. Please specify when ordering.

Panel Cut-Out Recommendations: For sheet metal panels, switch must enter panel in same direction as the punch. (Burr on bottom.) Test cut hole in actual material.

<sup>1</sup> Custom colors are available. Consult factory.

<sup>2</sup> Neon lamps (125 volt or 250 volt) not recommended with green or blue colored indicators.

<sup>3</sup> Specify lens color only if actuator style is P or PS.