

# P6KE6.8CA Series

## 600 Watt Peak Power Surmetic™ -40 Zener Transient Voltage Suppressors

### Bidirectional\*

The P6KE6.8CA series is designed to protect voltage sensitive components from high voltage, high energy transients. They have excellent clamping capability, high surge capability, low zener impedance and fast response time. These devices are ON Semiconductor's exclusive, cost-effective, highly reliable Surmetic axial leaded package and is ideally-suited for use in communication systems, numerical controls, process controls, medical equipment, business machines, power supplies and many other industrial/consumer applications.

#### Specification Features:

- Working Peak Reverse Voltage Range – 5.8 to 171 V
- Peak Power – 600 Watts @ 1 ms
- ESD Rating of class 3 (>16 KV) per Human Body Model
- Maximum Clamp Voltage @ Peak Pulse Current
- Low Leakage < 5  $\mu$ A above 10 V
- Maximum Temperature Coefficient Specified
- UL 497B for Isolated Loop Circuit Protection
- Response Time is Typically < 1 ns

#### Mechanical Characteristics:

**CASE:** Void-free, Transfer-molded, Thermosetting plastic

**FINISH:** All external surfaces are corrosion resistant and leads are readily solderable

**MAXIMUM LEAD TEMPERATURE FOR SOLDERING PURPOSES:** 230°C, 1/16" from the case for 10 seconds

**POLARITY:** Cathode band does not imply polarity

**MOUNTING POSITION:** Any

#### MAXIMUM RATINGS

| Rating                                                                                                                         | Symbol          | Value        | Unit  |
|--------------------------------------------------------------------------------------------------------------------------------|-----------------|--------------|-------|
| Peak Power Dissipation (Note 1.)<br>@ $T_L \leq 25^\circ\text{C}$                                                              | $P_{PK}$        | 600          | Watts |
| Steady State Power Dissipation<br>@ $T_L \leq 75^\circ\text{C}$ , Lead Length = 3/8"<br>Derated above $T_L = 75^\circ\text{C}$ | $P_D$           | 5            | Watts |
|                                                                                                                                |                 | 50           | mW/°C |
| Thermal Resistance,<br>Junction-to-Lead                                                                                        | $R_{\theta JL}$ | 20           | °C/W  |
| Operating and Storage<br>Temperature Range                                                                                     | $T_J, T_{stg}$  | - 55 to +175 | °C    |


1. Nonrepetitive current pulse per Figure 3 and derated above  $T_A = 25^\circ\text{C}$  per Figure 2.

\*Please see P6KE6.8A – P6KE200A for Unidirectional devices.



ON Semiconductor®

<http://onsemi.com>



AXIAL LEAD  
CASE 17  
PLASTIC



L = Assembly Location  
P6KExxxCA = ON Device Code  
YY = Year  
WW = Work Week

#### ORDERING INFORMATION

| Device       | Package    | Shipping         |
|--------------|------------|------------------|
| P6KExxxCA    | Axial Lead | 1000 Units/Box   |
| P6KExxxCARL* | Axial Lead | 4000/Tape & Reel |


\*P6KE170CA Not Available in 4000/Tape & Reel

## P6KE6.8CA Series

### ELECTRICAL CHARACTERISTICS

( $T_A = 25^\circ\text{C}$  unless otherwise noted)

| Symbol          | Parameter                                   |
|-----------------|---------------------------------------------|
| $I_{PP}$        | Maximum Reverse Peak Pulse Current          |
| $V_C$           | Clamping Voltage @ $I_{PP}$                 |
| $V_{RWM}$       | Working Peak Reverse Voltage                |
| $I_R$           | Maximum Reverse Leakage Current @ $V_{RWM}$ |
| $V_{BR}$        | Breakdown Voltage @ $I_T$                   |
| $I_T$           | Test Current                                |
| $\Theta V_{BR}$ | Maximum Temperature Variation of $V_{BR}$   |



## P6KE6.8CA Series

### ELECTRICAL CHARACTERISTICS (T<sub>A</sub> = 25°C unless otherwise noted.)

| Device     | Device Marking | V <sub>RWM</sub><br>(Note 1) | I <sub>R</sub> @ V <sub>RWM</sub> | Breakdown Voltage                |       |      |                  | V <sub>C</sub> @ I <sub>PP</sub> (Note 3) |                 | θV <sub>BR</sub> |
|------------|----------------|------------------------------|-----------------------------------|----------------------------------|-------|------|------------------|-------------------------------------------|-----------------|------------------|
|            |                |                              |                                   | V <sub>BR</sub> (Note 2) (Volts) |       |      | @ I <sub>T</sub> | V <sub>C</sub>                            | I <sub>PP</sub> |                  |
|            |                | (Volts)                      | (μA)                              | Min                              | Nom   | Max  | (mA)             | (Volts)                                   | (A)             | (%/°C)           |
| P6KE6.8CA  | P6KE6.8CA      | 5.8                          | 1000                              | 6.45                             | 6.80  | 7.14 | 10               | 10.5                                      | 57              | 0.057            |
| P6KE7.5CA  | P6KE7.5CA      | 6.4                          | 500                               | 7.13                             | 7.51  | 7.88 | 10               | 11.3                                      | 53              | 0.061            |
| P6KE8.2CA  | P6KE8.2CA      | 7.02                         | 200                               | 7.79                             | 8.2   | 8.61 | 10               | 12.1                                      | 50              | 0.065            |
| P6KE9.1CA  | P6KE9.1CA      | 7.78                         | 50                                | 8.65                             | 9.1   | 9.55 | 1                | 13.4                                      | 45              | 0.068            |
| P6KE10CA   | P6KE10CA       | 8.55                         | 10                                | 9.5                              | 10    | 10.5 | 1                | 14.5                                      | 41              | 0.073            |
| P6KE11CA   | P6KE11CA       | 9.4                          | 5                                 | 10.5                             | 11.05 | 11.6 | 1                | 15.6                                      | 38              | 0.075            |
| P6KE12CA   | P6KE12CA       | 10.2                         | 5                                 | 11.4                             | 12    | 12.6 | 1                | 16.7                                      | 36              | 0.078            |
| P6KE13CA   | P6KE13CA       | 11.1                         | 5                                 | 12.4                             | 13.05 | 13.7 | 1                | 18.2                                      | 33              | 0.081            |
| P6KE15CA   | P6KE15CA       | 12.8                         | 5                                 | 14.3                             | 15.05 | 15.8 | 1                | 21.2                                      | 28              | 0.084            |
| P6KE16CA   | P6KE16CA       | 13.6                         | 5                                 | 15.2                             | 16    | 16.8 | 1                | 22.5                                      | 27              | 0.086            |
| P6KE18CA   | P6KE18CA       | 15.3                         | 5                                 | 17.1                             | 18    | 18.9 | 1                | 25.2                                      | 24              | 0.088            |
| P6KE20CA   | P6KE20CA       | 17.1                         | 5                                 | 19                               | 20    | 21   | 1                | 27.7                                      | 22              | 0.09             |
| P6KE22CA   | P6KE22CA       | 18.8                         | 5                                 | 20.9                             | 22    | 23.1 | 1                | 30.6                                      | 20              | 0.092            |
| P6KE24CA   | P6KE24CA       | 20.5                         | 5                                 | 22.8                             | 24    | 25.2 | 1                | 33.2                                      | 18              | 0.094            |
| P6KE27CA   | P6KE27CA       | 23.1                         | 5                                 | 25.7                             | 27.05 | 28.4 | 1                | 37.5                                      | 16              | 0.096            |
| P6KE30CA   | P6KE30CA       | 25.6                         | 5                                 | 28.5                             | 30    | 31.5 | 1                | 41.4                                      | 14.4            | 0.097            |
| P6KE33CA   | P6KE33CA       | 28.2                         | 5                                 | 31.4                             | 33.05 | 34.7 | 1                | 45.7                                      | 13.2            | 0.098            |
| P6KE36CA   | P6KE36CA       | 30.8                         | 5                                 | 34.2                             | 36    | 37.8 | 1                | 49.9                                      | 12              | 0.099            |
| P6KE39CA   | P6KE39CA       | 33.3                         | 5                                 | 37.1                             | 39.05 | 41   | 1                | 53.9                                      | 11.2            | 0.1              |
| P6KE43CA   | P6KE43CA       | 36.8                         | 5                                 | 40.9                             | 43.05 | 45.2 | 1                | 59.3                                      | 10.1            | 0.101            |
| P6KE47CA   | P6KE47CA       | 40.2                         | 5                                 | 44.7                             | 47.05 | 49.4 | 1                | 64.8                                      | 9.3             | 0.101            |
| P6KE51CA   | P6KE51CA       | 43.6                         | 5                                 | 48.5                             | 51.05 | 53.6 | 1                | 70.1                                      | 8.6             | 0.102            |
| P6KE56CA   | P6KE56CA       | 47.8                         | 5                                 | 53.2                             | 56    | 58.8 | 1                | 77                                        | 7.8             | 0.103            |
| P6KE62CA   | P6KE62CA       | 53                           | 5                                 | 58.9                             | 62    | 65.1 | 1                | 85                                        | 7.1             | 0.104            |
| P6KE68CA   | P6KE68CA       | 58.1                         | 5                                 | 64.6                             | 68    | 71.4 | 1                | 92                                        | 6.5             | 0.104            |
| P6KE75CA   | P6KE75CA       | 64.1                         | 5                                 | 71.3                             | 75.05 | 78.8 | 1                | 103                                       | 5.8             | 0.105            |
| P6KE82CA   | P6KE82CA       | 70.1                         | 5                                 | 77.9                             | 82    | 86.1 | 1                | 113                                       | 5.3             | 0.105            |
| P6KE91CA   | P6KE91CA       | 77.8                         | 5                                 | 86.5                             | 91    | 95.5 | 1                | 125                                       | 4.8             | 0.106            |
| P6KE100CA  | P6KE100CA      | 85.5                         | 5                                 | 95                               | 100   | 105  | 1                | 137                                       | 4.4             | 0.106            |
| P6KE110CA  | P6KE110CA      | 94                           | 5                                 | 105                              | 110.5 | 116  | 1                | 152                                       | 4               | 0.107            |
| P6KE120CA  | P6KE120CA      | 102                          | 5                                 | 114                              | 120   | 126  | 1                | 165                                       | 3.6             | 0.107            |
| P6KE130CA  | P6KE130CA      | 111                          | 5                                 | 124                              | 130.5 | 137  | 1                | 179                                       | 3.3             | 0.107            |
| P6KE150CA  | P6KE150CA      | 128                          | 5                                 | 143                              | 150.5 | 158  | 1                | 207                                       | 2.9             | 0.108            |
| P6KE160CA  | P6KE160CA      | 136                          | 5                                 | 152                              | 160   | 168  | 1                | 219                                       | 2.7             | 0.108            |
| P6KE170CA* | P6KE170CA*     | 145                          | 5                                 | 162                              | 170.5 | 179  | 1                | 234                                       | 2.6             | 0.108            |
| P6KE180CA  | P6KE180CA      | 154                          | 5                                 | 171                              | 180   | 189  | 1                | 246                                       | 2.4             | 0.108            |
| P6KE200CA  | P6KE200CA      | 171                          | 5                                 | 190                              | 200   | 210  | 1                | 274                                       | 2.2             | 0.108            |

1. A transient suppressor is normally selected according to the maximum working peak reverse voltage (V<sub>RWM</sub>), which should be equal to or greater than the dc or continuous peak operating voltage level.

2. V<sub>BR</sub> measured at pulse test current I<sub>T</sub> at an ambient temperature of 25°C.

3. Surge current waveform per Figure 3 and derate per Figures 1 and 2.

\*Not Available in the 4,000/Tape & Reel.

## P6KE6.8CA Series




Figure 1. Pulse Rating Curve




Figure 2. Pulse Derating Curve




Figure 3. Pulse Waveform




Figure 4. Steady State Power Derating




Figure 5. Typical Derating Factor for Duty Cycle

## APPLICATION NOTES

### RESPONSE TIME

In most applications, the transient suppressor device is placed in parallel with the equipment or component to be protected. In this situation, there is a time delay associated with the capacitance of the device and an overshoot condition associated with the inductance of the device and the inductance of the connection method. The capacitance effect is of minor importance in the parallel protection scheme because it only produces a time delay in the transition from the operating voltage to the clamp voltage as shown in Figure 6.

The inductive effects in the device are due to actual turn-on time (time required for the device to go from zero current to full current) and lead inductance. This inductive effect produces an overshoot in the voltage across the equipment or component being protected as shown in Figure 7. Minimizing this overshoot is very important in the application, since the main purpose for adding a transient suppressor is to clamp voltage spikes. The P6KE6.8A series has very good response time, typically  $< 1$  ns and negligible inductance. However, external inductive effects could produce unacceptable overshoot. Proper circuit layout,

minimum lead lengths and placing the suppressor device as close as possible to the equipment or components to be protected will minimize this overshoot.

Some input impedance represented by  $Z_{in}$  is essential to prevent overstress of the protection device. This impedance should be as high as possible, without restricting the circuit operation.

### DUTY CYCLE DERATING

The data of Figure 1 applies for non-repetitive conditions and at a lead temperature of  $25^{\circ}\text{C}$ . If the duty cycle increases, the peak power must be reduced as indicated by the curves of Figure 5. Average power must be derated as the lead or ambient temperature rises above  $25^{\circ}\text{C}$ . The average power derating curve normally given on data sheets may be normalized and used for this purpose.

At first glance the derating curves of Figure 5 appear to be in error as the 10 ms pulse has a higher derating factor than the 10  $\mu\text{s}$  pulse. However, when the derating factor for a given pulse of Figure 5 is multiplied by the peak power value of Figure 1 for the same pulse, the results follow the expected trend.

### TYPICAL PROTECTION CIRCUIT





Figure 6.




Figure 7.

## P6KE6.8CA Series

### UL RECOGNITION\*

The entire series including the bidirectional CA suffix has *Underwriters Laboratory Recognition* for the classification of protectors (QGV2) under the UL standard for safety 497B and File #E 116110. Many competitors only have one or two devices recognized or have recognition in a non-protective category. Some competitors have no recognition at all. With the UL497B recognition, our parts successfully passed several tests including Strike Voltage

Breakdown test, Endurance Conditioning, Temperature test, Dielectric Voltage-Withstand test, Discharge test and several more.


Whereas, some competitors have only passed a flammability test for the package material, we have been recognized for much more to be included in their protector category.

\*Applies to P6KE6.8A, CA – P6KE200A, CA.

# Transient Voltage Suppressors – Axial Leaded

## 600 Watt Peak Power Surmetic™ –40

SURMETIC 40  
CASE 17-02  
ISSUE C



NOTES:

1. CONTROLLING DIMENSION: INCH
2. LEAD FINISH AND DIAMETER UNCONTROLLED IN DIM F.
3. FOR BIDIRECTIONAL DIODE, CATHODE BAND DOES NOT IMPLY POLARITY

| DIM | INCHES |       | MILLIMETERS |       |
|-----|--------|-------|-------------|-------|
|     | MIN    | MAX   | MIN         | MAX   |
| A   | 0.330  | 0.350 | 8.38        | 8.89  |
| B   | 0.130  | 0.145 | 3.30        | 3.68  |
| D   | 0.037  | 0.043 | 0.94        | 1.09  |
| K   | ---    | 0.050 | ---         | 1.27  |
| F   | 1.000  | 1.250 | 25.40       | 31.75 |

## P6KE6.8CA Series

SURMETIC is a trademark of Semiconductor Components Industries, LLC.

**ON Semiconductor** and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer.

### PUBLICATION ORDERING INFORMATION

#### Literature Fulfillment:

Literature Distribution Center for ON Semiconductor  
P.O. Box 5163, Denver, Colorado 80217 USA  
**Phone:** 303-675-2175 or 800-344-3860 Toll Free USA/Canada  
**Fax:** 303-675-2176 or 800-344-3867 Toll Free USA/Canada  
**Email:** ONlit@hibbertco.com

**N. American Technical Support:** 800-282-9855 Toll Free USA/Canada

**JAPAN:** ON Semiconductor, Japan Customer Focus Center  
4-32-1 Nishi-Gotanda, Shinagawa-ku, Tokyo, Japan 141-0031  
**Phone:** 81-3-5740-2700  
**Email:** r14525@onsemi.com

**ON Semiconductor Website:** <http://onsemi.com>

For additional information, please contact your local Sales Representative.