




D2SB05-D2SB80

Single Phase 2.0AMPS. Glass Passivated Bridge Rectifiers

GBL

Features


- ✧ UL Recognized File # E-326243
- ✧ Glass passivated junction
- ✧ Ideal for printed circuit board
- ✧ High case dielectric strength
- ✧ Plastic material has Underwriters laboratory flammability Classification 94V-0
- ✧ High surge current capability
- ✧ High temperature soldering guaranteed:
260°C/10 seconds / .375", (9.5mm)
lead lengths.
- ✧ Green compound with suffix "G" on packing code & prefix "G" on datecode



Mechanical Data

- ✧ Case: Molded plastic body
- ✧ Terminals: Pure tin plated, lead free, solderable per MIL-STD-202, Method 208
- ✧ Weight: 2.0 grams
- ✧ Mounting position: Any

Dimensions in inches and (millimeters)



Marking Diagram

- D2SBXX = Specific Device Code
G = Green Compound
Y = Year
WW = Work Week

Maximum Ratings and Electrical Characteristics

Rating at 25 °C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	Symbol	D2SB 05	D2SB 10	D2SB 20	D2SB 40	D2SB 60	D2SB 80	Unit
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	50	100	200	400	600	800	V
Maximum RMS Voltage	V_{RMS}	35	70	140	280	420	560	V
Maximum DC Blocking Voltage	V_{DC}	50	100	200	400	600	800	V
Maximum Average Forward Rectified Current @ $T_A=50^\circ\text{C}$	$I_{F(AV)}$	2						A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	I_{FSM}	80						A
Rating of fusing ($t<8.3\text{ms}$) ($t<10\text{ms}$)	I^2T	27 32						A ² S
Maximum Instantaneous Forward Voltage (Note 1) @ 2 A	V_F	1.1						V
Maximum DC Reverse Current at Rated DC Block Voltage @ $T_A=25^\circ\text{C}$ @ $T_A=125^\circ\text{C}$	I_R	10 500						uA
Typical Thermal Resistance	$R_{\theta JA}$ $R_{\theta JL}$	47 10						°C/W
Operating Temperature Range	T_J	- 55 to + 150						°C
Storage Temperature Range	T_{STG}	- 55 to + 150						°C

Note 1 : Pulse Test with PW=300 usec, 1% Duty Cycle

RATINGS AND CHARACTERISTIC CURVES (D2SB05 THRU D2SB80)

FIG.1 MAXIMUM FORWARD CURRENT DERATING CURVE




FIG. 2 TYPICAL REVERSE CHARACTERISTICS PER BRIDGE ELEMENT




FIG. 3 MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT PER BRIDGE ELEMENT




FIG. 4 TYPICAL JUNCTION CAPACITANCE




FIG. 5 TYPICAL FORWARD CHARACTERISTICS PER BRIDGE ELEMENT

