




PCB Layout, Component side, PCB thickness 1,6 mm

Mating Cycles	500
Filter type	C
Capacitance	3900pf±20%
Working Voltage	100v
Current Rating	7.5A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION (dB)
5	6dB
10	11dB
50	25dB
100	35dB
500	35dB
1000	32dB



							Dat.	Name		D-Sub, male, straight, 25 Poles, turned solder pins, tin plated shell with dimples, spacer nuts and board-locks	Mo?Ms lab/ Scale 1.5:1	
						Detail.	8-JUL-02	CV				
						Insp.						All Dim. in mm
						Stand.						Orig. Size DIN A 4
09643227246	M3		33423	06/02/06	JMDR	HARTING EURL F-95972 Paris				TB 0964322724x	Blatt / Page 2 / 3	
09643227245	UNC 4-40		31058	8-JUL-02	CV							
Part number	Nut thread		Mod.	Dat.	Name							