







REVISIONS		
ISS	ZONE	DESCRIPTION\PER REQUEST\DATE



RECOMMENDED CABLE STRIPPING DIM'S



RECOMMENDED MOUNTING HOLE



- NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)
1. BRASS PER QQ-B-626
  2. PHOSPHOR BRONZE PER QQ-B-750
  3. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
  4. NICKEL PL. 200 MIN. THICK OVER COPPER STRIKE
  5. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
  6. TEFLON MIL-P-19468
  7. JIS H 3250, C 2700

1. CRIMPED FERRULE  
HEX CRIMP SIZE .128"
2. CONTACT PIN TO SOLDER

NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.
8	FERRULE	NOTE 7	NOTE 3	1	FR-39/32X95
7	CONTACT PIN	NOTE 1	NOTE 5	1	FME1121A4-4-15/06
6	HEX NUT	NOTE 1	NOTE 3	1	HN14-7/16-28X25
5	LOCK WASHER	NOTE 2	NOTE 4	1	LW-1372/1119X05
4	BARREL	NOTE 1	NOTE 3	1	FME87051202-4-27/17
3	LOCK RING	NOTE 1	NOTE 3	1	FME1121A3-3-B
2	INSULATOR	NOTE 6	NATURAL	1	FME1121A4-2T-50
1	BODY	NOTE 1	NOTE 3	1	FME1421A2-1

DIMENSIONS ARE IN MILLIMETERS			PART NO.	
UNLESS OTHERWISE SPECIFIED TOLERANCES			FME1421A2-NT3G-5-50	
0.5-6	= ±0.2	APPROVED	DATE	
6-30	= ±0.4	CHECKED	DATE	
30-120	= ±0.6	DRAWN	DATE	
120-315	= ±1	FILE NO.	DATE	
315-1000	= ±1.6		DATE	
1000-2000	= ±2.4		DATE	

<h1>Amphenol</h1>		TITLE	FME BULKHEAD CRIMP PLUG (FOR RG-174/U,188A/U,316/U)
		DRAWING NO.	KJ-FME1421A2-NT3G-316U-50
		ITEM NO.	