


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		S	REVISED PER ECO-12-021696	28FEB2012	CJV	CWR



1. GOLD PLATING MAY NOT APPEAR ON CARRIER STRIP.
2. GOLD PLATING PER MIL-G-45204.
NICKEL PLATING PER QQ-N-290.
TIN PLATING PER MIL-T-10727.
3. GOLD PLATED IN LOCALIZED GOLD PLATE AREA AS FOLLOWS:
.000030 MIN GOLD IN MATED AREA, GOLD FLASH ON REMAINDER OF
LOCALIZED GOLD PLATE AREA, .000100 MIN MATTE TIN IN ZONE 1,
ALL OVER .000050 MIN NICKEL UNDERPLATE.
OR
GOLD FLASH OVER PALLADIUM-NICKEL PLATE, .000030 MIN TOTAL
IN MATED AREA, GOLD FLASH ON REMAINDER OF LOCALIZED GOLD
PLATE AREA, .000100 MIN MATTE TIN IN ZONE 1, ALL OVER
.000050 MIN NICKEL UNDERPLATE.
4. GOLD PLATED IN LOCALIZED GOLD PLATED AREA, GOLD FLASH IN
MATED AREA, TIN PLATED WIRE BARREL, OVER .000030 NICKEL.
5. GOLD PLATED IN LOCALIZED GOLD PLATED AREA, .000030 GOLD IN
MATED AREA, TIN PLATED WIRE BARREL, OVER .000030 NICKEL.
6. .046 MAX DIA CONDUCTOR (UP TO 18 AWG).

OBSOLETE OBSOLETE	SMALL PACK	3	LOOSE PIECE	66570-8
	STANDARD	5	STRIP	66570-6
	STANDARD	4	STRIP	66570-4
	STANDARD	3	LOOSE PIECE	66570-3
	STANDARD	3	STRIP	66570-2
PACKAGING TYPE		FINISH	TYPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009		DWN S.WELDON 9-9-86	 TE Connectivity					
		CHK C.RICHARD 9-9-86						
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD —	NAME PIN CONTACT, SIZE 20 DF, WITH SOLDER CUP, AMPLIMATE					
	0 PLC ± —	PRODUCT SPEC —						
	1 PLC ± —	—						
	2 PLC ± —	APPLICATION SPEC						
	3 PLC ± .005	—						
	4 PLC ± —	—						
ANGLES	± —	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
MATERIAL BRASS PER MIL-C-50	FINISH SEE TABLE	WEIGHT —	A2	00779	G-66570	—		
CUSTOMER DRAWING			SCALE	10:1	SHEET	1 of 1	REV	S