


THIS DRAWING IS UNPUBLISHED; RELEASED FOR PUBLICATION

© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
✓	✓		L	REDRAWN & REVISED PER ECN R-1451	7-30-85
✓	✓		M	REV. ECN R-1946	3-4-86
✓	✓		N	OBSOLETE -3 PER R-2760	3-4-87
✓	✓		P	REV PER ECN DF-5920	11-25-92
✓	✓		R	REV PER OH14-0241-05	04-05



1. REELED FOR USE WITH STANDARD APPLICATORS.

2. PLATED WITH .000100 MIN SILVER PER QQ-S-365.

3. PLATED WITH .000015 MIN GOLD PER MIL-G-45204 IN THE LOCALIZED GOLD PLATE AREA, GOLD FLASH ON THE REMAINDER, OVER .000030 MIN NICKEL PER QQ-N-290.

4. PLATED WITH .000030 MIN GOLD PER MIL-G-45204 IN THE LOCALIZED GOLD PLATE AREA, GOLD FLASH ON THE REMAINDER, OVER .000030 MIN NICKEL PER QQ-N-290.

5. PLATED WITH .000050 MIN 93-7% TIN-LEAD ALLOY OVER .000030 MIN NICKEL PER QQ-N-290.

6. WIRE RANGE = 10 AWG.

7. INSULATION RANGE = .190 - .220 DIA.

8. PLATED WITH .000050 MIN TIN PER ASTM-B-545 OVER .000030 MIN NICKEL PER QQ-N-290.

BLACK	2	66254-6	66260-5
NATURAL	2	66254-4	66260-4
BLACK	3	66254-5	66260-3
BLACK	4	66254-2	66260-2
BLACK	5	66254-1	66260-1
TERMINAL LATCH COLOR	FINISH	STRIP ASS'Y P/N REF	LOOSE PIECE P/N ASS'Y

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.010 ANGLES ±.010	CONTRACT NO DR <i>Rick Rohrbach</i> 9-27-85 CHK <i>Larry J. Lawrence</i> 10-25-85 APPD <i>Ed. Bolash</i> 10-25-85 APPD <i>James E. Smith</i> 10-27-85	AMP AMP INCORPORATED Harrisburg, Pa. 17105	
MATERIAL SEE CALLOUT	NAME MALE TYPE XII GROUND CONTACT LOOSE PIECE ASS'Y	DRAWING NO 66260	
FINISH SEE DASH NO	DSGN APPD OTHER APPD	SIZE C	FSCM NO 00779
SCALE NTS		SHEET	