




Fig. 1




Fig. 2




Fig. 3





Fig. 4

- Series 41X double row strip sockets are on .100" grid.
- Various solder tails available: standard length, long for multi-layer boards, very low and ultra low profile. Using Mill-Max #1001, 0134, 0501 or 1534 pins (See pages 132, 133, 136) for details.
- Hi-Rel, 4-finger BeCu #12 & #30 contacts are rated at 3 amps. See page 218 for details.
- Insulators are high temp. thermoplastic.



Ordering Information

Fig. 1

Series 410...001

Standard Solder Tail

410-XX-2_-41-001000

Specify # of pins

02-64

Fig. 2

Series 411...001

Long Solder Tail

411-13-2_-41-001000

Specify # of pins

02-64

Fig. 3

Series 415...001

Very Low Profile

415-XX-2_-41-001000

Specify # of pins

02-64

Fig. 4

Series 415...003

Ultra Low Profile

415-XX-2_-41-003000

Specify # of pins

02-72

For Electrical,
Mechanical & Environmental
Data, See pg. 4

XX=Plating Code
See Below

For RoHS compliance
select ◇ plating code.

SPECIFY PLATING CODE XX=	13◇	93	43◇
Sleeve (Pin)	10μ" Au	200μ" Sn/Pb	200μ" Sn
Contact (Clip)	30μ" Au	30μ" Au	30μ" Au

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[P410-93-220-41-001000](#)