






PRODUCT NO
SEE TABLE




mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101	projection INCH/MM	product family MODJACK	
ltr	ecn no	dr	date	tolerances unless otherwise specified				title	
A	V71847	RHG	1/7/98	angles		.XX±.01/.3		NETJACK II, RJ45 SMT	
B	V91920	BKB	8/25/99	linear		.XXX±.005/.13		SINGLE PORT ASSY, SNAP PEG	
C	V92060	LP	10/20/99	0°±2'		.XXXX±.0020/.051	scale 1:1	sheet 1 of 3 size	
D	V00462	CEK	1/27/00	dr	R. GRAPE	1/5/98	FCI	dwg no	
E	V12718	LP	1/22/02	enfr	B. MARSHALL	1/5/98		74328	
F	M05-0074	ERE	4/22/05	chr	B. MARSHALL	1/5/98		A3	
G	M06-0288	AGS	7/28/06	appd	B. MARSHALL	1/5/98		type Product Customer Drawing	
sheet	revision	G	G	G					
index	sheet	1	2	3					

PRODUCT NO
74328-50YXXX
74328-50YXXXLF

NET JACK MAGNETICS
OPTION CODE-XXX
SEE GES-12-020


SPRING OPTION Y	DESCRIPTION (SEE SHEET 4 FOR OPTIONAL VIEWS)
1	SPRING ON TOP,BOTTOM AND BOTH SIDES
2	NO SPRINGS
3	SPRINGS ON TOP AND BOTTOM
4	SPRINGS ON TOP,BOTTOM AND 1 PER SIDE (STAGGERED)
5	SAME AS OPTION 4 EXCEPT OPPOSITE STAGGER



RECOMMENDED PANEL OPENING

NOTES :

1. RECOMMENDED PCB THICKNESS 1.57 [0.062].
2. HOUSING MATL: HIGH TEMP. THERMOPLASTIC, COLOR BLACK, UL94V-0.
3. CONTACT MATL: COPPER ALLOY
MATING AREA PLATING: 1.27uM/50u" MIN Au OVER Ni.
SOLDER AREA PLATING: 2.54uM/100u" MIN TIN LEAD OVER Ni.
LEAD FREE OPTION:
SOLDER AREA PLATING: 2.54uM/100u" MIN PURE TIN OVER Ni.
4. SHIELDING MAT'L: TIN PLATED COPPER ALLOY.
5. ALL DIMENSIONS IN MILLIMETERS AND INCHES.
6. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH ASME Y14.5M 1994.
7. LF SUFFIX AT THE END OF PART NUMBERS IS LEAD FREE.
8. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.
9. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.



RECOMMENDED P.C.B. LAYOUT
AS VIEWED FROM TOP SIDE (COMPONENT SIDE)

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family MODJACK
ltr	ecn	no	dr	date	tolerances unless otherwise specified	scale 1:1 FCI	title
G					angles linear .XX±.01/.3		NETJACK II, RJ45 SMT
					0'±2' .xxx±.005/.13		SINGLE PORT ASSY, SNAP PEG
					.xxxx±.0020/.051		dwg no sheet2 of 3 size
			dr	R. GRAPE	1/5/98		74328 A3
			enr	B. MARSHALL	1/5/98		
			chr	B. MARSHALL	1/5/98		
			app	B. MARSHALL	1/5/98		
sheet index	revision sheet						type Product Customer Drawing




FCIconnect.com

Copyright FCI


PRODUCT NO

SEE TABLE


SPRING OPTION Y CONFIGURATIONS




OPTION 1




OPTION 2



OPTION 3



OPTION 4



OPTION 5

mat'l. code				surface ISO 1302	tolerance ISO 406 ISO 1101	projection 	product family MODJACK
ltr	ecn	no	dr	date	tolerances unless otherwise specified	INCH/MM scale 1:1 	title
G					angles linear		NETJACK II, RJ45 SMT
					0°±2° linear		SINGLE PORT ASSY, SNAP PEG
					dr R. GRAPE 1/5/98		dwg no sheet 3 of 3 size
					enrg B. MARSHALL 1/5/98		74328 A3
					chr B. MARSHALL 1/5/98		
					appd B. MARSHALL 1/5/98		type Product Customer Drawing
sheet index	revision sheet						

form: A3