





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		CI	REVISED PER ECO-12-007964	02MAY2012	KH	MS



- 1 MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
TERMINAL: COPPER ALLOY, TIN PLATED.
- 2 SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
- 3 RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC.FILE N° E60677.
- 4 IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY
WITH IEC 998-1/998-2-1.
- 5 NOT CUMULATIVE TOLERANCE.




282816-2 AS SHOWN



125	13	1-282816-3
115	12	1-282816-2
105	11	1-282816-1
95	10	1-282816-0
85	9	282816-9
75	8	282816-8
65	7	282816-7
55	6	282816-6
45	5	282816-5
35	4	282816-4
25	3	282816-3
15	2	282816-2

RECOMMENDED PC BOARD LAYOUT



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±.2

1 PLC ±.2

2 PLC ±.25

3 PLC ±.

4 PLC ±.

ANGLES ±2

FINISH

DWN E. ZANOLINI 25JUL2001

CHK D. BIEVENOUR 25JUL2001

APVD D. BIEVENOUR 25JUL2001

PRODUCT SPEC 108-20166

APPLICATION SPEC 114-20079

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME

TERMINAL BLOCK HEADER ASSEMBLY
90 DEGREE CLOSED ENDS
10mm PITCH

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-282816

SCALE 3:1

SHEET 1 OF 1

REV C1