


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		Y	REVISED PER ECO-12-011709	26JUN2012	RW	SY

D

C

B

A



- 1 .000050 MIN THK NICKEL UNDERPLATE OVER ENTIRE CONTACT.
- 2 .000150 MIN BRIGHT TIN/LEAD OVER ENTIRE CONTACT.
- 3 .000100 MIN THK BRIGHT TIN/LEAD IN ZONE 1.
- 4 GOLD FLASH IN LOCALIZED GOLD PLATE AREA.
- 5 .000015 MIN GOLD IN LOCALIZED GOLD PLATE AREA
- 6 .000030 MIN GOLD IN LOCALIZED GOLD PLATE AREA
- 7. TO BE APPLIED PER AMP APPLICATION SPEC 114-16015.
- 8. RECOMMENDED HOLE SIZE IS .031-.035 DIA.
- 9 FOR SOLDERABILITY SEE AMP PRODUCT SPEC 108-9024.
- 10 .000150 MIN TIN-LEAD IN ZONE 2.
- 11 AREA TO BE UNPLATED (-9 ONLY).
- 12 GOLD FLASH IN ZONE 1. .000150 MIN TIN IN ZONE 3.
- 13 GOLD FLASH IN ZONE 1.
- 14 GOLD PLATING MAY OR MAY NOT BE PRESENT ON THE BOTTOM OF THE CRIMP BARREL IN THIS AREA.

D

C


88997

B

A

				1-88997-4
				1-88997-3
				1-88997-2
				88997-9
				88997-5
				88997-4
				88997-3
				88997-2
FINISH				PART NO

SUPERSEDED BY 88997-5



SECTION D-D

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. MCMASTER 10MAR04	TE Connectivity			
DIMENSIONS: INCHES		CHK S. BOLASH 10MAR04				
		APVD M. WALMSLEY 10MAR04	NAME			
		PRODUCT SPEC 108-9024	CONTACT, SOLDER TAB, FFC, .100 ϕ			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-16015	SIZE A2	CAGE CODE 00779	DRAWING NO C=88997	RESTRICTED TO -
MATERIAL PH. BRONZE .010 THK		FINISH SEE TABLE	WEIGHT -	SCALE 10:1	SHEET 1 OF 1	REV Y
		CUSTOMER DRAWING				