

VC-D2-BU30-PE

Order No.: 1855063

The illustration shows a 50-pos. version



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1855063>

Female contact carrier, for turned crimp contacts, type VC 2, 30-pos. +
PE

Commercial data

EAN	4017918159375
Pack	10 pcs.
Customs tariff	85366990
Weight/Piece	0.04056 KG
Catalog page information	Page 363 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
06/01/2005



[http://
www.download.phoenixcontact.com](http://www.download.phoenixcontact.com)
Please note that the data given
here has been taken from the
online catalog. For comprehensive
information and data, please refer
to the user documentation. The
General Terms and Conditions of
Use apply to Internet downloads.

Technical data

Electrical characteristics

Note	Plug connectors may only be connected/disconnected when under no load.
Rated voltage	250 V
Rated voltage (III/3)	250 V

Rated current	10 A
	10 A
Rated surge voltage	4 kV
Ambient temperature (operation)	-40 °C ... 125 °C
Number of positions	30

Mechanical characteristics

Conductor cross section	0.14 mm ² ... 1.5 mm ² (stranded)
Connection cross section AWG	22 ... 16
Stripping length of the individual wire	8 mm
Conductor cross section stranded max.	1.5 mm ²
Insertion/withdrawal cycles	>= 500

General characteristics

Design	VC2
Connection method	Crimp connection
Inflammability class acc. to UL 94	V0
Pollution degree	2
Surge voltage category	III

Material data

Contact carrier material	PA-GF
--------------------------	-------

Certificates / Approvals



Certification CUL, GOST, UL

CUL

Nominal voltage U _N	250 V
Nominal current I _N	4 A

UL


Nominal voltage U _N	250 V
Nominal current I _N	4 A

Accessories

Item	Designation	Description
Assembly		
1855319	VC-D-AF	Panel mounting flange for screw locking, to fix the contact insert to the housing panel

Diagrams/Drawings

Dimensioned drawing



Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;