




NOTES:

1. MAT'L: NYLON 66 (RMS-01)
2. COLOR: NATURAL
3. FLAME RETARDANT NYLON (RMS-19), AVAILABLE BY SPECIAL ORDER.

PART NO.	"B"	MAX. BUNDLE DIA. "C" LOCKED	BOARD THICKNESS RANGE
*SLCSE-250	.57 (14.5)	.22 (5.6)	1/32-5/64 (0.8-2.0)
SLCSE-370	.71 (18.0)	.35 (8.9)	
SLCSE-500	.83 (21.0)	.47 (12.0)	
SLCSE-750	1.08 (27.5)	.73 (18.4)	
*SLCSE2-250	.57 (14.5)	.22 (5.6)	5/64-5/32 (2.0-4.0)
SLCSE2-370	.71 (18.0)	.35 (8.9)	
SLCSE2-500	.83 (21.0)	.47 (12.0)	
SLCSE2-750	1.08 (27.5)	.73 (18.4)	

PART NO. CODE
 SLCSE - 500 - 8 - 01
 | | | |
 PART# SIZE "A" MAT'L

SUFFIX	"A" ±.015(0.4)
-3	3/16(4.8)
-4	1/4(6.4)
-6	3/8(9.5)
-8	1/2(12.7)
*-10	5/8(15.9)
*-12	3/4(19.1)
*-14	7/8(22.2)
*-16	1.0(25.4)

*PARTS AVAILABLE BY SPECIAL ORDER ONLY

3. FLAME RETARDANT NYLON (RMS-19), AVAILABLE BY SPECIAL ORDER.			TITLE: STANDOFF LOCK CLIP SERIES						DWG IN IN (MM)			
			TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°		FILE # SLCSE		DWN: J.B.		APP:		FINAL	
					MAT'L: SEE NOTES		DT: 02-13-96		DT:		PART #	
C SEE ECN #914 FOR CHANGES SK 01.14.05					RE: RICHCO, INC.		RICHCO INC.		PO BOX 804238,CHICAGO,60680		SEE CHART	
B SEE ECN #818 FOR CHANGES SM 10.01.04												
A CHANGED FILE NUMBER SM 05.31.01												
REV DESCRIPTION ENGR DATE												
											PRINT TYPE CA	