





DESCRIPTION: FEMALE - 0.283 RIGHT ANGLE / MACHINED - ECONOMY



No. OF PINS	DIMENSIONS							
	A	B	C	D	E	F	G	H
9	1.213	0.984	0.642	0.311	0.236	0.756	0.496	0.427
	30.80	24.99	16.30	7.90	5.99	19.20	12.60	10.85
15	1.541	1.312	0.970	0.311	0.236	1.091	0.496	0.427
	39.15	33.32	24.65	7.90	5.99	27.70	12.60	10.85
25	2.087	1.852	1.512	0.311	0.236	1.618	0.496	0.427
	53.00	47.04	38.40	7.90	5.99	41.10	12.60	10.85
37	2.728	2.500	2.157	0.311	0.236	2.256	0.496	0.427
	69.30	63.50	54.80	7.90	5.99	57.30	12.60	10.85
50	2.638	2.406	2.055	0.429	0.240	2.169	0.602	0.527
	67.00	61.11	52.20	10.90	6.10	55.10	15.30	13.39

173-EYY-211RYY1

SERIES _____
POSITIONS _____
E09 _____
E15 _____
E25 _____
E37 _____
E50 _____
GENDER _____
2 = FEMALE _____
TERMINATION _____
1 = PC MOUNTING _____
SHELL PLATING _____
1 = YELLOW CHROMATE (NON-ROHS) _____
HARDWARE OPTIONS _____
00 = NO HARDWARE _____
14 = SHORT BRACKET WITH 4-40 SCREW LOCK _____
24 = SHORT BRACKET WITH 4-40 SCREW _____
PLATING OPTIONS _____
1 = GOLD FLASH _____
2 = 30MICRO-INCH GOLD _____

MATERIAL:

SHELL: STEEL, YELLOW CHROMATE
INSULATOR: UL 94V-O RATED, WHITE PA6T
PROCESS TEMP.: 260° PROCESS TEMPERATURE
CONTACT: BRASS






ELECTRICAL:

CURRENT RATING: 5 AMPS
CONTACT RESISTANCE: 15 mOhms Max.
INSULATION RESISTANCE: 1,000 MOhms min.
VOLTAGE: 500VAC FOR 1 MINUTE
TEMPERATURE: -50° C TO 100° C

DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: WAYNE ROBBINS		DATE: 11-28-05	
			CHECKED:		DATE:	
			SCALE: 1:1	SHEET 1 OF 3	REV 1	
NorComp			DWG NO. 173-EYY-211RYY1			

DESCRIPTION: PCB LAYOUT - MALE & FEMALE



* TYP. ON ALL SIZES
UNLESS NOTED OTHERWISE

DO NOT SCALE FROM DRAWING


	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 03-08-06	
		CHECKED:		DATE:	
NorComp		SCALE: FULL	SHEET 2 OF 3		REV 1
		DWG NO. 173-EYY-211RYY1			

DESCRIPTION: CLINCH NUT HARDWARE

HARDWARE OPTIONS

REPLACE -YY IN LAST 3 DIGITS WITH OPTION CHOSEN


173/174 SERIES



173 / 174 SERIES

14Y = SHORT BRACKET & 4-40 FEMALE HEX SOCKET
24Y = SHORT BRACKET & 4-40 SCREW

175/176 SERIES



175 / 176 SERIES

15Y = LONG BRACKET & 4-40 FEMALE HEX SOCKET
25Y = SHORT BRACKET & 4-40 SCREW

MATERIAL: COLD ROLLED STEEL
PLATING: CLEAR ZINC

DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: PAM JENKINS		DATE: 11-28-05		
		CHECKED:		DATE:		
NorComp			SCALE: 1 : 1	SHEET 3 OF 3		REV 1
			DWG NO. 173-EYY-211RYY1			