






		4	35.56 [1.400]	14	35.69 [1.484]	15	6-146129-3	
		4	33.02 [1.300]	13	33.15 [1.384]	14	6-146129-2	
		4	30.48 [1.200]	12	30.61 [1.284]	13	6-146129-1	
		4	27.94 [1.100]	11	28.07 [1.184]	12	6-146129-0	
		4	25.40 [1.000]	10	27.53 [1.084]	11	5-146129-9	
		4	22.86 [.900]	9	24.99 [.984]	10	5-146129-8	
		4	20.32 [.800]	8	22.45 [.884]	9	5-146129-7	
		4	17.78 [.700]	7	19.91 [.784]	8	5-146129-6	
		4	15.24 [.600]	6	17.37 [.684]	7	5-146129-5	
		4	12.70 [.500]	5	14.83 [.584]	6	5-146129-4	
		4	10.16 [.400]	4	12.29 [.484]	5	5-146129-3	
		4	7.62 [.300]	3	9.75 [.384]	4	5-146129-2	
		4	5.08 [.200]	2	7.21 [.284]	3	5-146129-1	
	5	OBSELETE	2	35.56 [1.400]	14	35.69 [1.484]	15	1-146129-3
	5	SUPERSEDED	2	33.02 [1.300]	13	33.15 [1.384]	14	1-146129-2
2			30.48 [1.200]	12	30.61 [1.284]	13	1-146129-1	
2			27.94 [1.100]	11	28.07 [1.184]	12	1-146129-0	
5	OBSELETE	2	25.40 [1.000]	10	27.53 [1.084]	11	146129-9	
		2	22.86 [.900]	9	24.99 [.984]	10	146129-8	
		2	20.32 [.800]	8	22.45 [.884]	9	146129-7	
5	SUPERSEDED	2	17.78 [.700]	7	19.91 [.784]	8	146129-6	
5	OBSELETE	2	15.24 [.600]	6	17.37 [.684]	7	146129-5	
		2	12.70 [.500]	5	14.83 [.584]	6	146129-4	
		2	10.16 [.400]	4	12.29 [.484]	5	146129-3	
5	SUPERSEDED	2	7.62 [.300]	3	9.75 [.384]	4	146129-2	
		2	5.08 [.200]	2	7.21 [.284]	3	146129-1	
			PLATING	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN J KNAUB 9-30-94		 TE Connectivity	
		CHK G DUBNICZKI 9-30-94			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.13 [005] 3 PLC ± — 4 PLC ± — ANGLES ± — FINISH		NAME	
		APVD G DUBNICZKI 9-30-94 PRODUCT SPEC — APPLICATION SPEC —		SURFACE MOUNT HEADER ASSEMBLY, MOD II, BREAKAWAY, VERTICAL, SINGLE ROW, .100 X.100 C/L .025 SQ.POST	
MATERIAL		WEIGHT		SIZE	RESTRICTED TO
		—		CAGE CODE	—
SEE TABLE		CUSTOMER DRAWING		DRAWING NO	—
				A1 00779	—
				SCALE	10:1
				SHEET	1 OF 1
				REV	—

RECOMMENDED PCB LAYOUT
FOR USE WITH .008 THICK STENCIL