




Compact Size
Panel Mount Indicator, Non-Relampable
Neon and Incandescent Technology
Mounting Hole, Ø 0.310"



All dimensions are in inches



Minimum panel thickness: 0.030"

6" leads with 1/2" strip are standard
 Due to compact size, components (resistors, diodes)
 will be installed in the leads

Storage temperature T_{STG} : -25°C - +80°C
 Ambient temperature T_A : -20°C - +60°C
 Voltage tolerance V_{OP} : ±10%

Part No.	Lens Color	Voltage	Current mA	Rated Life
Neon 115VAC Series				
WL-2150SA1	Red	105-125VAC	1.5mA	25,000 Hrs
WL-2150SA2	Clear	105-125VAC	1.5mA	25,000 Hrs
WL-2150SA3	Amber	105-125VAC	1.5mA	25,000 Hrs
WL-2152SA5	Green	105-125VAC	1.5mA	25,000 Hrs
WL-2152SA6	Blue	105-125VAC	1.5mA	25,000 Hrs
Neon 230VAC Series				
WL-2151SA1	Red	208-250VAC	1.5mA	25,000 Hrs
WL-2151SA2	Clear	208-250VAC	1.5mA	25,000 Hrs
WL-2151SA3	Amber	208-250VAC	1.5mA	25,000 Hrs
WL-2153SA5	Green	208-250VAC	1.5mA	25,000 Hrs
WL-2153SA6	Blue	208-250VAC	1.5mA	25,000 Hrs
Incandescent 12V Series				
WL-2194SA1-12V	Red	12V-14V	80mA	25,000 Hrs
WL-2194SA2-12V	Clear	12V-14V	80mA	25,000 Hrs
WL-2194SA3-12V	Amber	12V-14V	80mA	25,000 Hrs
WL-2194SA5-12V	Green	12V-14V	80mA	25,000 Hrs
Incandescent 28V Series				
WL-2194SA1-28V	Red	24V-28V	40mA	25,000 Hrs
WL-2194SA2-28V	Clear	24V-28V	40mA	25,000 Hrs
WL-2194SA3-28V	Amber	24V-28V	40mA	25,000 Hrs
WL-2194SA5-28V	Green	24V-28V	40mA	25,000 Hrs

Body Material: Nylon, white
 Lens Material: Polycarbonate
 Bezel Finish: Chrome
 Wire Gauge: 18 AWG
 Wire Strip: 1/2"
 Notes: Tinnerman clips available separately.

Certifications: Most Wamco indicators carry Agency approvals. Please contact Wamco for the latest Agency information regarding the specific product series and voltage required.
 Options: Additional options and lens styles available. Please contact Wamco for more information.

Drawn	SC	04/04/12	Compact Size Panel Mount Indicators Neon and Incandescent	Datasheet: WL-215XSAX Series WL-2194SAX-XXX Series	Rev: 1
Checked	EB	04/04/12			
Approved	EB	04/05/12			