




P-Channel 55-V (D-S), 175°C MOSFET

PRODUCT SUMMARY

$V_{(BR)DSS}$ (V)	$r_{DS(on)}$ (Ω)	I_D (A)
-55	0.008	-75 ^a

TO-220AB




G D S

Top View

SUP75P05-08

DRAIN connected to TAB

TO-263




G D S

Top View

SUB75P05-08

175°C Rated
Maximum Junction Temperature
TrenchFET®
Power MOSFETs



P-Channel MOSFET

ABSOLUTE MAXIMUM RATINGS ($T_C = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)

Parameter		Symbol	Limit	Unit
Drain-Source Voltage		V_{DS}	-55	V
Gate-Source Voltage		V_{GS}	± 20	
Continuous Drain Current ($T_J = 175^\circ\text{C}$)	$T_C = 25^\circ\text{C}$	I_D	-75 ^a	A
	$T_C = 150^\circ\text{C}$		-47	
Pulsed Drain Current		I_{DM}	-240	
Avalanche Current		I_{AR}	-75	
Repetitive Avalanche Energy ^b		E_{AR}	280	mJ
Power Dissipation	$T_C = 25^\circ\text{C}$ (TO-220AB and TO-263)		250 ^d	
	$T_A = 125^\circ\text{C}$ (TO-263) ^c		3.7	
Operating Junction and Storage Temperature Range		T_J, T_{stg}	-55 to 175	$^\circ\text{C}$

THERMAL RESISTANCE RATINGS

Parameter		Symbol	Limit	Unit
Junction-to-Ambient	PCB Mount (TO-263) ^c	R_{thJA}	40	$^\circ\text{C/W}$
	Free Air (TO-220AB)	R_{thJA}	62.5	
Junction-to-Case		R_{thJC}	0.6	

Notes:

- Package limited.
- Duty cycle $\leq 1\%$.
- When mounted on 1" square PCB (FR-4 material).
- See SOA curve for voltage derating.







For SPICE model information via the Worldwide Web: <http://www.vishay.com/www/product/spice.htm>







SPECIFICATIONS (T _J = 25 °C UNLESS OTHERWISE NOTED)						
Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Static						
Drain-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0 V, I _D = −250 μA	−55			V
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = −250 μA	−1	−2	−3	
Gate-Body Leakage	I _{GSS}	V _{DS} = 0 V, V _{GS} = ± 20 V			± 100	nA
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = −44 V, V _{GS} = 0 V			−1	μA
		V _{DS} = −44 V, V _{GS} = 0 V, T _J = 125 °C			−50	
		V _{DS} = −44 V, V _{GS} = 0 V, T _J = 175 °C			−700	
On-State Drain Current ^a	I _{D(on)}	V _{DS} = −5 V, V _{GS} = −10 V	−120			A
Drain-Source On-State Resistance ^a	r _{DS(on)}	V _{GS} = −10 V, I _D = −30 A			0.008	Ω
		V _{GS} = −4.5 V, I _D = −20 A			0.013	
		V _{GS} = −10 V, I _D = −30 A, T _J = 125 °C			0.014	
		V _{GS} = −10 V, I _D = −30 A, T _J = 175 °C			0.016	
Forward Transconductance ^a	g _{fs}	V _{DS} = −15 V, I _D = −30 A		75		S
Dynamic ^b						
Input Capacitance	C _{iss}	V _{GS} = 0 V, V _{DS} = −25 V, f = 1 MHz		8500		pF
Output Capacitance	C _{oss}			1220		
Reverse Transfer Capacitance	C _{rss}			915		
Total Gate Charge ^c	Q _g	V _{DS} = −30 V, V _{GS} = −10 V, I _D = −75 A		140	225	nC
Gate-Source Charge ^c	Q _{gs}			30		
Gate-Drain Charge ^c	Q _{gd}			30		
Turn-On Delay Time ^c	t _{d(on)}	V _{DD} = −30 V, R _L = 0.47 Ω I _D ≈ −75 A, V _{GEN} = −10 V, R _G = 2.5 Ω		13	20	ns
Rise Time ^c	t _r			140	225	
Turn-Off Delay Time ^c	t _{d(off)}			115	185	
Fall Time ^c	t _f			175	300	
Source-Drain Diode Ratings and Characteristics (T _C = 25 °C) ^b						
Continuous Current	I _S				−75	A
Pulsed Current	I _{SM}				−240	
Forward Voltage ^a	V _{SD}	I _F = −75 A, V _{GS} = 0 V		−1.1	−1.3	V
Reverse Recovery Time	t _{rr}	I _F = −75 A, di/dt = 100 A/μs		60	120	ns
Peak Reverse Recovery Current	I _{RM(REC)}			2.2	3.5	A
Reverse Recovery Charge	Q _{rr}			0.176	0.21	μC

Notes:

- a. Pulse test; pulse width ≤ 300 μs, duty cycle ≤ 2%.
b. Guaranteed by design, not subject to production testing.
c. Independent of operating temperature.


**TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)**

TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)





THERMAL RATINGS


**Maximum Avalanche and Drain Current
vs. Case Temperature**



Safe Operating Area



Normalized Thermal Transient Impedance, Junction-to-Case





Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.