

ULTRA LOW CAPACITANCE TVS ARRAYS (GIGABIT ETHERNET)

APPLICATIONS

- ✓ Ethernet - 10/100/1000 Base T
- ✓ Cellular Phones
- ✓ Handheld - Wireless Systems
- ✓ Personal Digital Assistant (PDA)
- ✓ USB Interface

IEC COMPATIBILITY (EN61000-4)

- ✓ 61000-4-2 (ESD): Air - 15kv, Contact - 8kw
- ✓ 61000-4-4 (EFT): 40A - 5/50ns

FEATURES



- ✓ 350 Watts Peak Pulse Power Dissipation at ($t_p = 8/20\mu s$)
- ✓ Unidirectional & Bidirectional Configurations
- ✓ Replacement for MLV (0805)
- ✓ Protects One Power or I/O Port
- ✓ ESD Protection > 40 kilovolts
- ✓ Low Clamping Voltage
- ✓ **ULTRA LOW CAPACITANCE 3pF PER DIODE**

MECHANICAL CHARACTERISTICS

- ✓ Molded JEDEC SOD-323
- ✓ Weight 10 milligrams (Approximate)
- ✓ Flammability Rating UL 94V-0
- ✓ Tape and Reel Per EIA Standard 481-1-A
- ✓ Device Marking Code & Polarity Band (*Unidirectional Only*)



CIRCUIT DIAGRAMS



DEVICE CHARACTERISTICS

MAXIMUM RATINGS @ 25°C Unless Otherwise Specified



PARAMETER	SYMBOL	VALUE	UNITS
Operating Temperature	T_J	-55°C to 150°C	°C
Storage Temperature	T_{STG}	-55°C to 150°C	°C

ELECTRICAL CHARACTERISTICS PER LINE @ 25°C Unless Otherwise Specified



PART NUMBER (See Note 1 & Note 2)	DEVICE MARKING	RATED STAND-OFF VOLTAGE V_{WM} VOLTS	MINIMUM BREAKDOWN VOLTAGE @ 1mA $V_{(BR)}$ VOLTS	MAXIMUM CLAMPING VOLTAGE (See Fig. 2) @ $I_P = 1A$ V_C VOLTS	MAXIMUM CLAMPING VOLTAGE (See Fig. 2) @ 8/20 μs V_C @ I_{PP}	MAXIMUM LEAKAGE CURRENT @ V_{WM} I_D μA	TYPICAL CAPACITANCE 0V @ 1 MHz C pF
GBLC03	3	3.3	4.0	7.0	14.6V @ 24A	75	3
GBLC03C	3C	3.3	4.0	7.0	14.6V @ 24A	75	3
GBLC05	5	5.0	6.0	9.8	17.5V @ 20A	5	3
GBLC05C	5C	5.0	6.0	9.8	17.5V @ 20A	5	3
GBLC08	8	8.0	8.5	13.4	21.1V @ 16.6A	2	3
GBLC08C	8C	8.0	8.5	13.4	21.1V @ 16.6A	2	3
GBLC12	2	12.0	13.3	19.0	28.0V @ 12.5A	1	3
GBLC12C	2C	12.0	13.3	19.0	28.0V @ 12.5A	1	3
GBLC15	6	15.0	16.7	24.0	42.0V @ 8.3A	1	3
GBLC15C	6C	15.0	16.7	24.0	42.0V @ 8.3A	1	3
GBLC18	1	18.0	20.0	29.0	50.0V @ 7A	1	3
GBLC18C	1C	18.0	20.0	29.0	50.0V @ 7A	1	3

Note 1: Part numbers with an additional "C" suffix are bidirectional devices, i.e., GBLC05C.

Note 2: For Bidirectional Devices Only: Electrical characteristics apply in both directions.



PACKAGE OUTLINE & DIMENSIONS

PACKAGE OUTLINE 	SOD-323 PACKAGE  PACKAGE DIMENSIONS <table><tr><th rowspan="2">DIM</th><th colspan="2">MILLIMETERS</th><th colspan="2">INCHES</th></tr><tr><th>MIN</th><th>MAX</th><th>MIN</th><th>MAX</th></tr><tr><td>A</td><td>1.60</td><td>1.90</td><td>0.063</td><td>0.075</td></tr><tr><td>B</td><td>1.15</td><td>1.45</td><td>0.045</td><td>0.057</td></tr><tr><td>C</td><td>2.30</td><td>2.70</td><td>0.094</td><td>0.106</td></tr><tr><td>D</td><td>0.90</td><td>1.17</td><td>0.036</td><td>0.046</td></tr><tr><td>E</td><td>0.33</td><td>0.43</td><td>0.013</td><td>0.017</td></tr><tr><td>F</td><td>0.10</td><td>0.15</td><td>0.004</td><td>0.006</td></tr><tr><td>H</td><td>-</td><td>0.10</td><td>-</td><td>0.004</td></tr></table>	DIM	MILLIMETERS		INCHES		MIN	MAX	MIN	MAX	A	1.60	1.90	0.063	0.075	B	1.15	1.45	0.045	0.057	C	2.30	2.70	0.094	0.106	D	0.90	1.17	0.036	0.046	E	0.33	0.43	0.013	0.017	F	0.10	0.15	0.004	0.006	H	-	0.10	-	0.004
DIM	MILLIMETERS		INCHES																																										
	MIN	MAX	MIN	MAX																																									
A	1.60	1.90	0.063	0.075																																									
B	1.15	1.45	0.045	0.057																																									
C	2.30	2.70	0.094	0.106																																									
D	0.90	1.17	0.036	0.046																																									
E	0.33	0.43	0.013	0.017																																									
F	0.10	0.15	0.004	0.006																																									
H	-	0.10	-	0.004																																									
MOUNTING PAD 	NOTES: 1. Controlling Dimensions in Millimeters.																																												

TAPE & REEL PACKAGING:

Surface mount product is taped and reeled in accordance with EIA-481, reel quantities and sizes are as follows:

7 Inch Reel - 3,000 pieces per reel; 13 Inch Reel - Not Available

ProTek Devices
2929 South Fair Lane, Tempe, AZ 85282
Tel: 602-431-8101 Fax: 602-431-2288
E-Mail: sales@protek-tvs.com
Web Site: www.protekdevices.com

COPYRIGHT © ProTek Devices 2001

SPECIFICATIONS: ProTek reserves the right to change the electrical and or mechanical characteristics described herein without notice (except JEDEC).

DESIGN CHANGES: ProTek reserves the right to discontinue product lines without notice, and that the final judgement concerning selection and specifications is the buyer's and that in furnishing engineering and technical assistance, ProTek assumes no responsibility with respect to the selection or specifications of such products.