

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

.19



(C) COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
AA	22	P	LTR	DESCRIPTION	DATE	DWN APVD
		B		REV; EC 067A-0191-98	29JAN99	DLD CMB



- 1 MATERIALS:
HOUSING - PCT POLYESTER, BLACK, IR
REFLOW COMPATIBLE, UL 94V-0.
TERMINALS 0.33 [0.013] THICK PH05
BRONZE PLATED WITH 1.27µm [0.000050]
HARD GOLD IN LOCALIZED AREA AND 3.81µm
[0.000150] THICK TIN-LEAD IN SOLDER
AREA OVER 1.27µm [0.000050] MINIMUM
THICK NICKEL UNDERPLATE.
SHIELD - 0.25 [0.010] THICK COPPER ALLOY
PLATED WITH 2.03µm [0.000080] MINIMUM
TIN-LEAD OVER 2.54µm [0.000100] MINIMUM
COPPER.
- 2 JACK CAVITY CONFORMS TO FCC RULES AND
REGULATIONS,PART 68 SUBPART F.
3. DIMENSIONS ARE NOMINAL UNLESS OTHER-
WISE SPECIFIED.



SUGGESTED PANEL CUTOUT

SUGGESTED PC BOARD LAYOUT
VIEW SHOWN IS TOP (COMPONENT SIDE) OF PC BOARD

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN S. MAYBERRY 21-JUL-93	558070-1 PART NUMBER		
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK B. FOX 03-AUG-93	AMP Incorporated Harrisburg, PA 17105-3608		
		APVD G. REED 03-AUG-93	NAME MODULAR JACK ASSEMBLY, 10 POSITION SIDE ENTRY, LOW PROFILE, FULLY SHIELDED, PANEL GROUND		
	0 PLC ±- 1 PLC ±- 2 PLC ±0.25 [.01] 3 PLC ±0.13 [.005] 4 PLC ±- ANGLES ±- FINISH	PRODUCT SPEC 108-1163	SIZE A2	CAGE CODE 00779	DRAWING NO C-558070
		APPLICATION SPEC 114-2048	WEIGHT -	SCALE 4:1	SHEET 1 OF 1
MATERIAL 1	FINISH 1	CUSTOMER DRAWING		REV B	