



Ruhestellung
free position
Schaltpunkt
operating position
zul. Endstellung
total travel position allowed



A-A
2:1

B-B
2:1


Aufschrift
marking




1006 µ T100
10(14) /400 ~10E3
6(2.5) /400 ~50E3 05

10A 125V AC 1/4HP
10A 250V AC 1/4HP
R44

Herstellort / -jahr / -woche
date code of manufacture:
place / year / week




NC NO



Wechsler 1-polig
single pole changeover

Schalt-Betaetigungskraft 0.8 bis 1.4 N
actuating force 0.8 up to 1.4 N

Differenzweg ≤ 0.7 mm
movement differential

fuer Form und Lage FOR SHAPE AND LOC.		⊙ =		Allgemeintoleranzen UNTOLERANCED DIMENSIONS				Pause COPY	Blatt SHEET 01		TYP K	Zeichn./DRAWING NO. 10060901	Index e
fuer Winkel FOR ANGLE ± 2				PROJEKTION 	Abmasse und Nennmassbereiche Angaben in mm ALL DIMENSIONS ARE IN MILLIMETRES	Laenge LENGTH Radien RADII	Original Din A4		Masstab SCALE 1 : 1 30mm				
						0-6 >6-15 >15-30 >30-70 >70-120 >120 ± 0.1 ± 0.15 ± 0.2 ± 0.3 ± 0.4 ± 0.8 ± 0.2 ± 0.3 ± 0.5 ± 10%							
d	26264	02.09.99	PFU				CAD: NX V6.0		Schnappschalter				
c	22549	24.11.93	GE				gez./DRAWN BY 22.03.13 BCY		Snap action switch				
b	22163	06.05.93	BLE				gepr./CHECKED BY		 MARQUARDT				
	13026	14.01.80	KR	e	85449	15.10.13	BRC						
Ausg. ISSUE	Aenderung REVISION	gez. DRAWN BY		Ausg. ISSUE	Aenderung REVISION	gez. DRAWN BY		Ersatz fuer/REPLACEMENT OF Zg.gl.Nr.v.02.09.1999					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Marquardt:

<u>1006.0901</u>	<u>1006.1206</u>	<u>1005.1218</u>	<u>1005.3605</u>	<u>1006.1001</u>	<u>1005.0408</u>	<u>1005.3906</u>	<u>1006.0711</u>	<u>1005.2808</u>	<u>1005.0409</u>
<u>1005.0505</u>	<u>1005.3901</u>	<u>1005.3802</u>	<u>1006.0704</u>	<u>1005.0907</u>	<u>1005.1214</u>	<u>1006.1505</u>	<u>1005.1401</u>	<u>1005.0708</u>	<u>1006.9804</u>
<u>1005.1136</u>	<u>1006.4402</u>	<u>1005.2812</u>	<u>1005.1008</u>	<u>1006.0201</u>	<u>1005.0304</u>	<u>1005.0808</u>	<u>1005.0901</u>	<u>1005.1801</u>	