

---

# 2SK2393

Silicon N-Channel MOS FET

# HITACHI

---

## Application


High voltage / High speed power switching

## Features

- Low on-resistance, High breakdown voltage
- High speed switching
- Low Drive Current
- No Secondary Breakdown
- Suitable for Switching regulator, Motor Control

## Outline

TO-3PL



Absolute Maximum Ratings (Ta = 25°C)





| Item                                      | Symbol                              | Ratings     | Unit |
|-------------------------------------------|-------------------------------------|-------------|------|
| Drain to source voltage                   | V <sub>DSS</sub>                    | 1500        | V    |
| Gate to source voltage                    | V <sub>GSS</sub>                    | ±20         | V    |
| Drain current                             | I <sub>D</sub>                      | 8           | A    |
| Drain peak current                        | I <sub>D(pulse)</sub> <sup>*1</sup> | 20          | A    |
| Body to drain diode reverse drain current | I <sub>DR</sub>                     | 8           | A    |
| Channel dissipation                       | Pch <sup>*2</sup>                   | 200         | W    |
| Channel temperature                       | Tch                                 | 150         | °C   |
| Storage temperature                       | Tstg                                | −55 to +150 | °C   |

Notes 1. PW ≤ 10 μs, duty cycle ≤ 1 %  
2. Value at Tc = 25 °C


Electrical Characteristics (Ta = 25°C)

| Item                                       | Symbol               | Min  | Typ  | Max | Unit | Test Conditions                                                                 |
|--------------------------------------------|----------------------|------|------|-----|------|---------------------------------------------------------------------------------|
| Drain to source breakdown voltage          | V <sub>(BR)DSS</sub> | 1500 | —    | —   | V    | I <sub>D</sub> = 10 mA, V <sub>GS</sub> = 0 <sup>*1</sup>                       |
| Gate to source leak current                | I <sub>GSS</sub>     | —    | —    | ±1  | μA   | V <sub>GS</sub> = ±20 V, V <sub>DS</sub> = 0                                    |
| Zero gate voltage drain current            | I <sub>DSS</sub>     | —    | —    | 500 | μA   | V <sub>DS</sub> = 1200 V, V <sub>GS</sub> = 0                                   |
| Gate to source cutoff voltage              | V <sub>GS(off)</sub> | 2.0  | —    | 4.0 | V    | I <sub>D</sub> = 1 mA, V <sub>DS</sub> = 10 V                                   |
| Static drain to source on state resistance | R <sub>DS(on)</sub>  | —    | 1.9  | 2.8 | Ω    | I <sub>D</sub> = 4 A<br>V <sub>GS</sub> = 15 V <sup>*1</sup>                    |
| Forward transfer admittance                | y <sub>fs</sub>      | 1.8  | 3.0  | —   | S    | I <sub>D</sub> = 4 A<br>V <sub>DS</sub> = 20 V <sup>*1</sup>                    |
| Input capacitance                          | Ciss                 | —    | 4370 | —   | pF   | V <sub>DS</sub> = 10 V                                                          |
| Output capacitance                         | Coss                 | —    | 560  | —   | pF   | V <sub>GS</sub> = 0                                                             |
| Reverse transfer capacitance               | Crss                 | —    | 200  | —   | pF   | f = 1 MHz                                                                       |
| Turn-on delay time                         | t <sub>d(on)</sub>   | —    | 75   | —   | ns   | I <sub>D</sub> = 4 A                                                            |
| Rise time                                  | t <sub>r</sub>       | —    | 180  | —   | ns   | V <sub>GS</sub> = 10 V                                                          |
| Turn-off delay time                        | t <sub>d(off)</sub>  | —    | 260  | —   | ns   | R <sub>L</sub> = 7.5 Ω                                                          |
| Fall time                                  | t <sub>f</sub>       | —    | 125  | —   | ns   |                                                                                 |
| Body to drain diode forward voltage        | V <sub>DF</sub>      | —    | 0.9  | —   | V    | I <sub>F</sub> = 8 A, V <sub>GS</sub> = 0                                       |
| Body to drain diode reverse recovery time  | t <sub>rr</sub>      | —    | 6.5  | —   | μs   | I <sub>F</sub> = 8 A, V <sub>GS</sub> = 0,<br>di <sub>F</sub> / dt = 100 A / μs |


Note 1. Pulse Test




Drain to Source Saturation Voltage vs. Gate to Source Voltage




Static Drain to Source on State Resistance vs. Drain Current








Static Drain to Source on State Resistance vs. Temperature




Forward Transfer Admittance vs. Drain Current










Switching Time Test Circuit



Waveform



Unit: mm



|                          |        |
|--------------------------|--------|
| Hitachi Code             | TO-3PL |
| JEDEC                    | —      |
| EIAJ                     | —      |
| Weight (reference value) | 9.9 g  |

## Cautions

1. Hitachi neither warrants nor grants licenses of any rights of Hitachi's or any third party's patent, copyright, trademark, or other intellectual property rights for information contained in this document. Hitachi bears no responsibility for problems that may arise with third party's rights, including intellectual property rights, in connection with use of the information contained in this document.
2. Products and product specifications may be subject to change without notice. Confirm that you have received the latest product standards or specifications before final design, purchase or use.
3. Hitachi makes every attempt to ensure that its products are of high quality and reliability. However, contact Hitachi's sales office before using the product in an application that demands especially high quality and reliability or where its failure or malfunction may directly threaten human life or cause risk of bodily injury, such as aerospace, aeronautics, nuclear power, combustion control, transportation, traffic, safety equipment or medical equipment for life support.
4. Design your application so that the product is used within the ranges guaranteed by Hitachi particularly for maximum rating, operating supply voltage range, heat radiation characteristics, installation conditions and other characteristics. Hitachi bears no responsibility for failure or damage when used beyond the guaranteed ranges. Even within the guaranteed ranges, consider normally foreseeable failure rates or failure modes in semiconductor devices and employ systemic measures such as fail-safes, so that the equipment incorporating Hitachi product does not cause bodily injury, fire or other consequential damage due to operation of the Hitachi product.
5. This product is not designed to be radiation resistant.
6. No one is permitted to reproduce or duplicate, in any form, the whole or part of this document without written approval from Hitachi.
7. Contact Hitachi's sales office for any questions regarding this document or Hitachi semiconductor products.

# HITACHI

## Hitachi, Ltd.

Semiconductor & Integrated Circuits.  
Nippon Bldg., 2-6-2, Ohte-machi, Chiyoda-ku, Tokyo 100-0004, Japan  
Tel: Tokyo (03) 3270-2111 Fax: (03) 3270-5109

|     |                  |                                                                                                                       |
|-----|------------------|-----------------------------------------------------------------------------------------------------------------------|
| URL | NorthAmerica     | : <a href="http://semiconductor.hitachi.com/">http://semiconductor.hitachi.com/</a>                                   |
|     | Europe           | : <a href="http://www.hitachi-eu.com/hel/ecg">http://www.hitachi-eu.com/hel/ecg</a>                                   |
|     | Asia (Singapore) | : <a href="http://www.has.hitachi.com.sg/grp3/sicd/index.htm">http://www.has.hitachi.com.sg/grp3/sicd/index.htm</a>   |
|     | Asia (Taiwan)    | : <a href="http://www.hitachi.com.tw/E/Product/SICD_Frame.htm">http://www.hitachi.com.tw/E/Product/SICD_Frame.htm</a> |
|     | Asia (HongKong)  | : <a href="http://www.hitachi.com.hk/eng/bo/grp3/index.htm">http://www.hitachi.com.hk/eng/bo/grp3/index.htm</a>       |
|     | Japan            | : <a href="http://www.hitachi.co.jp/Sicd/indx.htm">http://www.hitachi.co.jp/Sicd/indx.htm</a>                         |

## For further information write to:

|                                                                                                                                            |                                                                                                                                                                                                                                                                                                                                                                                         |
|--------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Hitachi Semiconductor (America) Inc.<br>179 East Tasman Drive,<br>San Jose, CA 95134<br>Tel: <1> (408) 433-1990<br>Fax: <1> (408) 433-0223 | Hitachi Europe GmbH<br>Electronic components Group<br>Dornacher Straße 3<br>D-85622 Feldkirchen, Munich<br>Germany<br>Tel: <49> (89) 9 9180-0<br>Fax: <49> (89) 9 29 30 00<br><br>Hitachi Europe Ltd.<br>Electronic Components Group.<br>Whitebrook Park<br>Lower Cookham Road<br>Maidenhead<br>Berkshire SL6 8YA, United Kingdom<br>Tel: <44> (1628) 585000<br>Fax: <44> (1628) 778322 |
|--------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                                                                                                                                                                                                                                                                                                        |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Hitachi Asia Pte. Ltd.<br>16 Collyer Quay #20-00<br>Hitachi Tower<br>Singapore 049318<br>Tel: 535-2100<br>Fax: 535-1533<br><br>Hitachi Asia Ltd.<br>Taipei Branch Office<br>3F, Hung Kuo Building. No.167,<br>Tun-Hwa North Road, Taipei (105)<br>Tel: <886> (2) 2718-3666<br>Fax: <886> (2) 2718-8180 |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                                                                                                                                                                                                                                                                  |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Hitachi Asia (Hong Kong) Ltd.<br>Group III (Electronic Components)<br>7/F., North Tower, World Finance Centre,<br>Harbour City, Canton Road, Tsim Sha Tsui,<br>Kowloon, Hong Kong<br>Tel: <852> (2) 735 9218<br>Fax: <852> (2) 730 0281<br>Telex: 40815 HITEC HX |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

Copyright ' Hitachi, Ltd., 1999. All rights reserved. Printed in Japan.