

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

—, —, —

© COPYRIGHT — By —

ALL RIGHTS RESERVED.

LOC —

DIST —

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	25FEB11	GSK	RH
	B	ECR-13-005850	10APR2013	TB	PRO

NOTE:

1. PACKAGING ACC. TO TE SPEC.107-18032
BUNDLE EVERY 25 ASSEMBLIES WITH A RUBBER BAND

2. ELECTRICAL TEST CONTAINING "SHORT CIRCUIT TEST, CONTINUITY
AND ACCURATE CAVITY ASSIGNMENT TEST" ACC. TO TE-SPEC.108-18857, SUBSECTION 3.1.1

3 WIRING SCHEDULE AS SHOWN

4. ASSEMBLY IN COLORS BLACK AND WHITE

F2

F3

F1

F4

VIEW A

A

3

2

1

4

3

2

1

4

2083135-1

2083135-1

L

3

2

1

4

3

2

1

4

2083135-1

2083135-1

B

F4

F1

F3

F2

VIEW B

FT	L	—	CABLE LIYY 4xAWG22 UL 2464 WH	4
FT	—	L	CABLE LIYY 4xAWG22 UL 2464 BK	4
PC	8	8	MICRO QUADLOK SYSTEM SOCKET CONTACT	3
PC	2	2	4 POS. LOW VOLTAGE CONN.M.POSITIONER	2
PC	—	2	4 POS. LOW VOLTAGE REC. CONN.HSG BK	1
PC	2	—	4 POS. LOW VOLTAGE REC. CONN.HSG WH	1
UOM	QTY	QTY	DECRPTION	POS.
	2--X	1--X		

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

0

1

2

3

4

PLC

PLC

PLC

PLC

PLC

±

±

±

±

±

—

—

—

—

—

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

±

±

±

±

±

—

—

—

—

—

MATERIAL

—

FINISH

—

DWN
SATHISH KUMAR.G

CHK
R.HOSSAINI

APVD
R.HOSSAINI

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

25FEB2011

—

—

—

—

—

—

—

TE Connectivity

CABLE ASSEMBLY NECTOR S LINE UL 4 POS.,
FEMALE TO FEMALE

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-2083135

RESTRICTED TO

—

CUSTOMER DRAWING

SCALE
NTS

SHEET
1 OF 1

REV
B

WIRING SCHEDULE 3

SIDE A	COLOR	SIDE B
F1	BN	F1
F2	RD	F2
F3	OG	F3
F4	BK	F4

PN	L/ft	TOLERANCES/ft
X-2083135-1	2	+0.06/-0.01
X-2083135-2	4	+0.07/-0.02
X-2083135-3	8	+0.10/-0.03
X-2083135-4	12	+0.12/-0.05
X-2083135-5	16	+0.17/-0.07

1470-19 (3/11)